



REVISIONS					
REV.	ECN#	ZONE	DESCRIPTION	CHANGED BY/DATE	APPROVED BY/DATE
AA	ECN# 2144	ALL	INITIAL RELEASE	A.M. 13MAR14	S.S. 13MAR14

PARAMETER	PERFORMANCE
MODEL NUMBER	FG4500
FREQUENCY	450 MHZ - 470 MHZ
GAIN	UNITY
POLARIZATION	VERTICAL
TERMINATION	N-FEMALE
IMPEDANCE	50 OHM
RADIATION PATTERN	OMNI-DIRECTIONAL
VSWR	<2:1
POWER RATING	100 WATTS
HEIGHT	~510 MM
WEIGHT	415.5 g
OUTDOOR RATED	YES
OPERATING TEMP	-30°C - +85°C
RECOMMENDED MOUNTING BRACKET	FM2 (NOT INCLUDED)



MATERIAL: N/A		THIRD ANGLE PROJECTION	
FINISH: N/A		DO NOT SCALE DRAWING	
APPROVALS		DATE	
DRAWN BY	A.MASCORRO	13MAR14	
ELEC. ENG.	A.MASCORRO	13MAR14	
MECH. ENG.	S.SAFVI	13MAR14	
MFG./OPS.			
		INTERPRET DIMENSIONING AND TOLERANCING IN ACCORDANCE WITH ASME Y14.5M-2009	
		TOLERANCES UNLESS OTHERWISE SPECIFIED	
		DIMENSIONS ARE IN MILLIMETERS	
		ANGLE: ±30°	
		0 PLACE DECIMAL: ±0.5	
		1 PLACE DECIMAL: ±0.25	
		2 PLACE DECIMAL: ±0.13	
		SURFACE ROUGHNESS 1.6/√	



TITLE:		
FG4500		
SIZE	DWG. NO.	REV
A3	FG4500MO	AA
SCALE: 1:3	PREVIOUS#	SHEET 1 OF 1

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION - , -
© Copyright 2022 TE Connectivity Ltd.	ALL RIGHTS RESERVED.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[FG4500](#)