

# 698-960 & 1710-2700 MHz LTE WORLD BAND ANTENNA

Part Numbers: 2372105-1, 2372105-2



## FEATURES & BENEFITS


- Adhesive backing on the PCB simplifies mounting within the device
- Omnidirectional coverage
- Efficient design reduces power usage
- No matching components required

## SPECIFICATIONS


Frequency Range (MHz)	698-960	1710-2700
VSWR	< 2.6:1	< 2.1:1
Efficiency	35%	60%
Average Gain	-4.4dBi	-3.4dBi
Peak Gain	0.3dBi	2.5dBi
Power Handling	10 Watt cw	
Feed Point Impedance	50 ohms unbalanced	
Polarization	Linear	
Size	65 mm x 15 mm x 1.0 mm	
Weight	< 2.9 g	
Mounting	Adhesive Tape	
Mating Connector	MHF-type. Refer to page 5	
Cable (coaxial)	1.13mm Dia. Refer to page5	
Operating Temperature	-40 to +85°C	
Storage Temperature	-40 to +85°C	
Hazardous Materials	A certificate of conformance is available from the product page on TE website.	

RF DATA


VSWR



Return Loss




Efficiency




Data measured in free space and on plastic device enclosure

# RADIATION PATTERN



Data measured in free space and on plastic device enclosure


KEEP OUT AREA



- NOTES**
- 1. Antenna designed to be mounted on plastic cover.
  - 2. Area in blue indicates Keep Out Area.
  - 3. For more information please call TE.


Dimension: mm  
Diagrams is not to scale

DIMENSIONS




Dimensions: mm  
Diagram is not to scale

MATING COMPONENTS TO PART NUMBERS AND DIMENSIONS

2372105-1	150	5.91	1.13	MHF-TYPE PLUG	RECEPTACLE (TE PN: 2337019-1)	
2372105-2	100	3.94	1.13	MHF-TYPE PLUG	RECEPTACLE (TE PN: 2337019-1)	
PART NUMBER	MM	INCH	CABLE (OD)	CONNECTOR TYPE	PART NUMBER	IMAGE
	CABLE LENGTH		mm	(ON CABLE)	MATING COMPONENTS	

PACKAGING



TE TECHNICAL SUPPORT CENTER

USA: +1 (800) 522-6752  
Canada: +1 (905) 475-6222  
Mexico: +52 (0) 55-1106-0800  
Latin/S. America: +54 (0) 11-4733-2200  
Germany: +49 (0) 6251-133-1999  
UK: +44 (0) 800-267666  
France: +33 (0) 1-3420-8686  
Netherlands: +31 (0) 73-6246-999  
China: +86 (0) 400-820-6015  
For phone numbers in other countries, go to [te.com/support-center](http://te.com/support-center)

**te.com**  
TE Connectivity, TE Connectivity (logo) are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.  
The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2020 TE Connectivity Ltd. family of companies All Rights Reserved.  
01/2022

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2372105-1](#)