


COIL: @ 25°C  
 RESISTANCE 1560 OHMS ± 10%  
 NOMINAL VOLTAGE 26.5 VDC  
 MUST OPERATE 14.2 VDC  
 MUST RELEASE 8.0 VDC MAX, 1.37 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's  
 SHOCK 75 g's 6 MS. DURATION  
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 2 MS MAX  
RELEASE TIME 4 MS MAX  
CONTACT BOUNCE 1.5 MS MAX

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1A  
28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 4/25/97 CK. EEPY 4/25/97

COMMUNICATIONS  
 INSTRUMENTS, INC.

CUST. QPL  
 CUST. NO. M39016/15-033L

TYPE JMAWD RELAY

JMAWD-26XL

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[JMAWD-26XL](#)