

ALCOSWITCH ANTI-VANDAL SWITCH SERIES

TE Connectivity's (TE) new ALCOSWITCH Anti-Vandal switch series is designed for security and reliability in a variety of panel mount industrial and building applications. The large pushbutton and available LED indicators illuminate the switch and allow for an easy user interface. The Anti-Vandal series is available in panel sizes of 16, 19, 22 and 25 mm, and with various pushbutton symbols including Spot, Ring, and Power Logo. Switches are sealed to IP67 and available in single and double pole configurations.



FEATURES

- Allow for an easy user interface with a large pushbutton and available LED indicators illuminate the switch
- Enable flexibility with various pushbutton symbols including Spot, Ring, and Power logo
- Achieve a vandal proof solution with a jam nut accessible for rear of the panel
- Ease of installation with available flying lead terminations.

APPLICATIONS

- Industrial equipment
- Elevators/Escalators
- Instrumentation
- Communication equipment
- Control equipment
- Medical equipment
- Parking Systems
- Emergency Communication

ELECTRICAL

- RoHS Directive 2002/95/E compliant
- REACH Compliant and Pb Free
- UL (E46765) for AV19, AV22 series

ALCOSWITCH ANTI-VANDAL SWITCH SERIES

TYPICAL PERFORMANCE CHARACTERISTICS

| | |
|------------------------------------|---|
| Number of poles: | 1 to 2 |
| Switch Functions: | OFF-ON, OFF-(ON) |
| Contact Rating: | 2A @ 36VDC (16mm) 3A @ 250VAC/28VDC (19, 22, 25mm) |
| Gold Contact: | 0.4 VA @ 20V max |
| Electrical life (pushbutton only): | 16mm: 200,000 cycles 19/22/25mm: 50,000 cycles |
| Contact resistance: | 50mOhms max. @ 1A, 12VDC (initial value) |
| Insulation resistance: | 1,000 MOhms min. @500VDC |
| Dielectric strength: | 2,000V for 1 minute |
| Actuator force: | 16mm: 4.5 +/- 1.5 N 19/22/25mm, Single Pole: 2.5 +/- 1.0 N 19/22/25mm, Double Pole: 3.5 +/- 1.0 N |
| Actuator travel: | 16mm: 2.0 mm 19/22/25mm: 3.2 mm |
| Life Expectancy: | Momentary: 1,000,000 actuations Push On/Off: 500,000 actuation |

MECHANICAL

| | |
|-----------------------|--------------|
| Operating temperature | -20 ~ +55° C |
|-----------------------|--------------|


MATERIALS

| | |
|----------------|------------------------------------|
| Contacts: | Copper with silver or gold plating |
| Actuator: | Stainless Steel |
| Terminals: | Copper, silver plated |
| Terminal seal: | Silicon |
| Case: | PBT |
| Bushing: | Stainless steel |




DIMENSIONS

Part Number 2316365-1



Part Number 2316366-1



ALCOSWITCH ANTI-VANDAL SWITCH SERIES

PRODUCT CODE STRUCTURE



PRODUCT SELECTION EXAMPLES

| Product key | Series | Body Style | LED color | LED voltage | Terminal Plating | Part number |
|-----------------|--------|-------------------------|--------------|-------------|------------------|-----------------------------|
| AV1610R112R04 | 16 mm | Single Pole - Momentary | White | 12 Volts | Gold | 2213774-1 |
| AV1910D512Q04 | 19 mm | Single Pole - Momentary | Yellow | 12 Volts | Silver | 2213765-9 |
| AV1910RAZ4Q04 | 19 mm | Single Pole - Momentary | Red / Green | 24 Volts | Silver | 2317404-2 |
| AV1910EG24T5Q04 | 19 mm | Single Pole - Momentary | Red / Yellow | 24 Volts | Silver | 3-2316531-5 |
| AV2210E324R04 | 22 mm | Single Pole - Momentary | Red | 24 Volts | Gold | 2213772-8 |
| AV2211EB12Q04 | 22 mm | Single Pole - Locking | Red / Blue | 12 Volts | Silver | 2317570-9 |
| AV2220EB12T5Q04 | 22 mm | Double Pole - Momentary | Red / Blue | 12 Volts | Silver | 4-2317570-4 |
| AV2510E312Q04 | 25 mm | Single Pole - Momentary | Red | 12 Volts | Silver | 2317656-3 |
| AV2521M124Q04 | 25 mm | Double Pole - Locking | White | 24 Volts | Silver | 2-2317658-6 |
| AV2511MB12T5Q04 | 25 mm | Single Pole - Locking | Red / Blue | 12 Volts | Silver | 2317659-7 |

te.com

©2023 TE Connectivity Ltd. Family of Companies. All Rights Reserved.

ALCOSWITCH, TE Connectivity, TE connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

USA: +1 (800) 522-6752

Canada: +1 (905) 475-6222

Mexico: +52 (0) 55-1106-0800

Latin/S. America: +54 (0) 11-4733-2200

Germany: +49 (0) 6251-133-1999

UK: +44 (0) 800-267666

France: +33 (0) 1-3420-8686

The Netherlands: +31 (0) 73-6246-999

China: +86 (0) 400-820-6015

04/23 ED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[AV2220E512R04](#)