



intercontec
products

Kontaktstift ø1 mm

Einsatzbereich: - 723 htec
- 740 htec

TE Teile Nr.: 61-0253-011-000
IC Ref. Nr.: 61.253.11
SEW-Nr.: 19053967

Elektrische Werte

Bemessungsstrom
Durchgangswiderstand

max. 7 A*
< 5 mOhm

Werkstoff

Kontakt

Messing, vergoldet

Anschluss

Anschlussart/ -bereich
max. Litzenaußendurchmesser
Abisolierlänge
Crimpeinstellungen

Crimp/ 0,14 - 1,0 mm²
ø2,1 mm
4 mm
sind individuell zu wählen

Mechanische Werte

Steckzyklen

500

Werkzeuge (nicht im Lieferumfang enthalten)

Digitale Crimpzange

TE Teile Nr.: C0-0324-000-000
IC Ref. Nr.: C0.324.00

Crimpen -kraftunterstützt

Crimpmaschine


TE Teile Nr.: WA-1672-000-000
IC Ref. Nr.: WA10672

digitaler Crimpeinsatz, klein

TE Teile Nr.: C0-0372-000-000
IC Ref. Nr.: C0.372.00

Locator für TE Teile Nr.: C0-0372-000-000
IC Ref. Nr.: C0.372.00

TE Teile Nr.: C0-0265-000-000
IC Ref. Nr.: C0.265.00



Hauptabmessungen
Kontaktstift

Y6-D783-000-00DE erstell: 02.10.2012/FS; geändert: 15.05.2020/VK

© 2020 TE Connectivity.

TE Connectivity, TE connectivity (logo), intercontec (logo) und speedtec sind Marken.

Auch wenn TE Connectivity (TE) bemüht ist, die Korrektheit der Informationen in diesem Beitrag sicherzustellen, übernimmt TE keinerlei Gewährleistung dafür, dass diese fehlerfrei, zutreffend, korrekt, verlässlich oder aktuell sind. TE behält sich das Recht vor, die in diesem Beitrag genannten Informationen jederzeit ohne Ankündigung zu ändern. TE weist ausdrücklich jegliche Gewährleistung hinsichtlich der in diesem Beitrag genannten Informationen zurück, einschließlich der implizierten Gewährleistung der Marktgängigkeit oder Eignung für bestimmte Zwecke. Die Maßangaben in diesem Beitrag dienen ausschließlich zu Referenzzwecken und Änderungen sind vorbehalten. Änderungen der Spezifikationen sind vorbehalten. Bitte fragen Sie TE nach den aktuellen Maßangaben und Designspezifikationen

TE Connectivity Industrial GmbH
Bernrieder Straße 15
94559 Niederwinkling, Germany
+49 9962 2002 - 0
intercontec@te.com
www.intercontec.biz



* Bei max. Anschlussquerschnitt



intercontec
products

Contact Pin $\varnothing 1$ mm

for: - 723 htec
- 740 htec

TE part number: 61-0253-011-000
IC reference number: 61.253.11
SEW code: 19053967

Electrical Data

rated current max. 7 A*
contact resistance < 5 mOhm

Material

contact brass, gold plated

Termination

cross-section crimp/ 0.14 - 1.0 mm²
max. outer wire diameter $\varnothing 2.1$ mm
stripping length 4 mm
crimp settings select individually

Mechanical Data

mating cycles 500

Tools (not part of product contents)


digital crimping tool TE part no.: C0-0324-000-000
IC ref. no.: C0.324.00

power crimping

crimping machine TE part no.: WA-1672-000-000
IC ref. no.: WA10672

digital crimp insert, small TE part no.: C0-0372-000-000
IC ref. no.: C0.372.00

locator for TE part no.: C0-0372-000-000 TE part no.: C0-0265-000-000
IC ref. no.: C0.372.00 IC ref. no.: C0.265.00



Main Dimensions
contact pin

Y6-D783-000-00EN issued: 02.10.2012/FS; modified: 15.05.2020/VK

© 2020 TE Connectivity

TE Connectivity, TE connectivity (logo), intercontec (logo) and speedtec are trademarks.

While TE Connectivity (TE) has made every reasonable effort to ensure the accuracy of the information in this presentation, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this article are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

TE Connectivity Industrial GmbH
Bernrieder Straße 15
94559 Niederwinkling, Germany
+49 9962 2002 - 0
intercontec@te.com
www.intercontec.biz



* for max. wire cross-section

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[61.253.11](#)