





Features

- 100 mm² PIN detector
- Low dark current
- High shunt resistance
- High sensitivity

Description

Low dark current PIN photodiode with 100 mm² square active area. Non-hermetic ceramic carrier package with glass window. Epoxy or silicone potting on special request.

Application

- Precision photometry
- Analytical instruments
- Medical equipment
- Fluorescence detector


RoHS

2011/65/EU


Absolute maximum ratings

Symbol	Parameter	Min	Max	Unit
T _{STG}	Storage temp	-40	125	°C
T _{OP}	Operating temp	-40	100	°C
V _{max}	Max reverse voltage		50	V
I _{PEAK}	Peak DC current		10	mA

Schematic




Spectral response (23 °C)




Electro-optical characteristics @ 23 °C

Symbol	Characteristic	Test Condition	Min	Typ	Max	Unit
	Active area		10000 x 10000			μm
	Active area		100			mm ²
I _D	Dark current	V _R = 10 V		1	10	nA
C	Capacitance	V _R = 0 V		900		pF
		V _R = 10 V		160		pF
	Responsivity	λ = 632 nm		0.4		A/W
		λ = 900 nm		0.64		A/W
t _R	Rise time	V _R = 0 V; λ = 850 nm; R _L = 50 Ω		2000		ns
		V _R = 10 V; λ = 850 nm; R _L = 50 Ω		40		ns
		V _R = 80 V; λ = 850 nm; R _L = 50 Ω		10		ns
	Shunt Resistance	V _R = 10 mV		150		MΩ
	N.E.P.	V _R = 10 V; λ = 900 nm		2.8 E-14		W/√Hz
V _{BR}	Breakdown voltage	I _R = 2 μA	50			V


Quantum efficiency (23 °C)




Capacitance as fct of reverse bias (23 °C)



Dark current as fct of bias (23 °C)



Dark current as fct of temperature (10 V)



Package dimension:

Small quantities: Foam pad, boxed (12 cm x 16.5 cm)

Handling:

Please refer to document "Instructions for handling and processing"

Disclaimer: Due to our strive for continuous improvement, specifications are subject to change within our PCN policy according to JESD46C.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[PS100-6B-CER-2 PIN](#) [PS100-6B-CERPING](#) [PS100-6-CER2PIN](#) [3001054](#)