



AMP

TE Internal #: 1583661-1

Hand Crimping Tools, Hydraulic (10,000 psi), Base Power Unit (No Crimp Tooling)

[View on TE.com >](#)

Application Tooling > Hand Crimping Tools



Power Technology Type: **Hydraulic (10,000 psi)**

Tooling Type: **Base Power Unit (No Crimp Tooling)**

Features

Other

Power Technology Type	Hydraulic (10,000 psi)
Tooling Type	Base Power Unit (No Crimp Tooling)

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides

on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 321259-1
TERM, SOLIS FLAG HR 4/0 1/2



TE Part # 324657
SPLICE BUTT M-M TERMINYL 8



TE Part # 2-329491-2
SPLICE,TERMI-FOIL 12 IN.



TE Part # 165429-1
SHUR PLUG REC.ASSY



TE Part # 2-329490-2
SPLICE,TERMI-FOIL 12 IN.



TE Part # 696434-1
TERM, RING, PLASTI-GRIP, 4, #10, 90 BEND



TE Part # 321866-1
STRATO-THERM, HR 1/0 1/4 NIPL BEND



TE Part # 1SET164006R0000
SPR025-N



TE Part # 2-329491-3
SPLICE,TERMI-FOIL 15 IN.

Customers Also Bought




TE Part #1616109-3
A700AP=RELAY



TE Part #525449-4
SLIP GAUGE, HANDTOOL



TE Part #525449-5
SLIP GAUGE, HANDTOOL




TE Part #1-532433-2
HDI PIN ASSY 3 ROW 225 POS



TE Part #2102573-1
ASSY 2/0 AL COPALUM LITE SINGLE
HOLE 3/8



TE Part #2-1618071-2
25-060-4X=WILMAR OVER/UNDERFRE



TE Part #293247-000
2522D0522-9



TE Part #290578-001
44A7422-0-1L



TE Part #766667-2
Wave Crimp, Flat to Round 8 AWG
Cbl Assy



TE Part #CTJ-3A-02-4032
RAIL ASSY

Documents

Datasheets & Catalog Pages

[AT-Hydraulic Crimp Tooling Solutions-1654519](#)

English

Bottoming Dies

English

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1583661-1](#)