



TE Internal #: 1601009-5
Magnet Wire Terminals, Solder Post, Mating Tab Width .04 in [1.02 mm], .16 – 1.02 mm Magnet Wire, 18 – 34 AWG Magnet Wire, SIAMEZE IDC
[View on TE.com >](#)

Terminals & Splices > Magnet Wire Terminals



Magnet Wire Terminal Type: **Solder Post**
Mating Tab Width: **1.02 mm [.04 in]**
Mating Tab Thickness: **.51 mm [.02 in]**
Magnet Wire Size: **.16 – 1.02 mm**

Features

Product Type Features

Compatible With Discrete Wire Type	Magnet Wire, Solid
------------------------------------	--------------------

Contact Features

Magnet Wire Terminal Type	Solder Post
Mating Tab Width	1.02 mm[.04 in]
Mating Tab Thickness	.51 mm[.02 in]
Terminal Plating Material	Unplated
Terminal Orientation	Straight

Termination Features

Termination Method to Wire & Cable	SIAMEZE IDC
------------------------------------	-------------

Mechanical Attachment

Mating Retention Type	Barbs
-----------------------	-------

Dimensions

Terminal Height	3.18 mm[.125 in]
Magnet Wire Size	.16 – 1.02 mm
Stock Thickness (Magnet Wire Side)	.51 mm[.02 in]



Product Length	8.76 mm[.345 in]
Usage Conditions	
Insulation Option	Uninsulated
Operating Temperature Range	-40 – 175 °C
Operation/Application	
Compatible With Wire Base Material	Copper
Packaging Features	
Packaging Quantity	30000
Packaging Method	Reel
Other	
Terminals & Splices Comment	Inserted height above the pocket is 3.18 mm [.125 in.], Magnet wire 30 AWG or smaller also requires a wrap post per P/N 1601447, Recommended Pocket Part Number 1601424

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2023 (233) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides



on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1601041-3 PC TAB STANDARD SIAMEZE	 TE Part # 4-1601009-4 PC TAB STANDARD SIAMEZE	 TE Part # 1601009-4 PC TAB STANDARD SIAMEZE	 TE Part # 1601120-4 TAB,PCB,FINE,SMZ
 TE Part # 1601009-1 131-020-000=TAB,PCB,STD,SMZ	 TE Part # 1601041-1 131-087-000=TAB,PCB,STD,SMZ	 TE Part # 1601120-1 150-011-000=TAB,PCB,FINE,SMZ	 TE Part # 2-1601120-1 150-012-000=TAB,PCB,FINE,SMZ

Customers Also Bought

 TE Part #2-1393243-4 RTE25524	 TE Part #964339-1 MAG MATE KONT. MKII	 TE Part #1-1546111-0 EUROSTYLE TB,HEADER,GREY,10POS	 TE Part #5822138-4 80 ME .050 L/P AU M/L PB-FREE
 TE Part #9-2176374-8 RQ 0805 1K1 0.1% 10PPM 1K RL	 TE Part #104344-3 05 MODII HDR SRST B/A W/HD		

Documents

Product Drawings
TAB,PCB,STD,SMZ
English



CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1601009-5_G.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1601009-5_G.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1601009-5_G.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1601009-5](#)