



Relays & Contactors > Relays > Relay Accessories, Sockets & Clips



Body Material: **Stainless Steel**
Relay Accessory Type: **Accessory, Metal Retaining Clip**

Features

Product Type Features

Relay Accessory Type	Accessory, Metal Retaining Clip
----------------------	---------------------------------

Body Features

Body Material	Stainless Steel
---------------	-----------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1393845-4 RP821012	 TE Part # 1393845-5 RP821024	 TE Part # 1415547-4 RP414012	 TE Part # 9-1415546-9 RP714012
 TE Part # 1860990-1 RT78601, RELAY SOCKET PCB 3.5MM	 TE Part # CAT-SCH691-SR1 Force Guided Relay with 2 contacts	 TE Part # 1-1415547-7 RP41N024	 TE Part # 1415547-1 RP714024
 TE Part # 1415547-2 RP714048	 TE Part # 1415547-3 RP734A12	 TE Part # 1415547-5 RP414024	 TE Part # 1415547-6 RP734012
 TE Part # 1415547-7 RP734020	 TE Part # 1415547-8 RP734024	 TE Part # 1415547-9 RP734036	 TE Part # 6-1415546-1 RP844024



TE Part # 6-1415546-2
RP424005



TE Part # 6-1415546-3
RP424006



TE Part # 6-1415546-4
RP424012



TE Part # 6-1415546-5
RP424024

Also in the Series | SCHRACK RY



Relay Accessories, Sockets & Clips(2)

Customers Also Bought



TE Part #1609112-8
10CS1 M0=F7803



TE Part #2176232-1
3522 130K 1% 3W



TE Part #1-2308272-6
CABLE CLAMP6 (CASE RAW)



TE Part #5227839-1
TNC PCB RT ANGLE JACK



TE Part #8-1393238-3
RTD34005




TE Part #1-829315-0
2X10P MOD2 STIFTLI



TE Part #2-2176330-9
CRGP 2010 2K2 1%



TE Part #1879355-4
RR03 5% 5K6 AMMO



TE Part #1860991-1
RT78602, RELAY SOCKET PCB 5MM



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1393161-9_A1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-1393161-9_A1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1393161-9_A1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

PCB Accessories Industrial Power Relays

English

Product Specifications

Definitions General Purpose Relays

English

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[RP28500](#)