




Connectors > Automotive Connectors > Automotive Connector Accessories > Automotive Connector Caps & Covers



Protection & Strain Relief Accessory Type: **Dust Cap**

Primary Product Color: **Natural - Translucent**

Primary Product Material: **PC/PET**

Number of Positions: **1**

Features

Product Type Features

Protection & Strain Relief Accessory Type	Dust Cap
---	----------

Configuration Features

Number of Positions	1
---------------------	---

Body Features

Primary Product Color	Natural - Translucent
Primary Product Material	PC/PET

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC






Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Not reviewed for solder process capability
---------------------------	--







Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.


Compatible Parts

 TE Part # 1-2394085-1 Pre-ASSY,Finger Access,Code K	 TE Part # 1-2394085-2 Pre-ASSY,Finger Access,Code L	 TE Part # 1-2394085-3 Pre-ASSY,Finger Access,Code M	 TE Part # 2-2394085-1 Pre-ASSY,Tool Access,Code A
 TE Part # 2-2394085-2 Pre-ASSY,Tool Access,Code B	 TE Part # 2-2394085-3 Pre-ASSY,Tool Access,Code C	 TE Part # 2-2394085-4 Pre-ASSY,Tool Access,Code D	 TE Part # 2-2394085-5 Pre-ASSY,Tool Access,Code E







 TE Part # 2-2394085-6 Pre-ASSY,Tool Access,Code F	 TE Part # 2-2394085-7 Pre-ASSY,Tool Access,Code G	 TE Part # 2-2394085-8 Pre-ASSY,Tool Access,Code H	 TE Part # 2-2394085-9 Pre-ASSY,Tool Access,Code J
 TE Part # 2394085-2 Pre-ASSY,Finger Access,Code B	 TE Part # 2394085-3 Pre-ASSY,Finger Access,Code C	 TE Part # 2394085-4 Pre-ASSY,Finger Access,Code D	 TE Part # 2394085-5 Pre-ASSY,Finger Access,Code E
 TE Part # 2394085-6 Pre-ASSY,Finger Access,Code F	 TE Part # 2394085-7 Pre-ASSY,Finger Access,Code G	 TE Part # 2394085-8 Pre-ASSY,Finger Access,Code H	 TE Part # 2394085-9 Pre-ASSY,Finger Access,Code J

Also in the Series | PowerTube HVP-HD 1000

 Automotive Connector Caps & Covers (5)	 Automotive Connector EMC Shielding (10)	 Automotive Housings(24)	 Automotive Terminals(6)
 Connector Seals & Cavity Plugs(5)	 Other Automotive Connector Accessories(6)	 PCB Headers & Receptacles(180)	

Customers Also Bought



 TE Part #WM-8S WEDGE LOCK, 8P, PLG, ORG, DTM	 TE Part #2355148-3 STEEL,SHIELD,IPT,CONN HSG	 TE Part #2-2399608-1 3POS,HVP1400,ASSY,180DEG,COD A /B/C	 TE Part #2355153-3 WIRE COVER,IPT HD
 TE Part #2383853-4 H&S 50mm, Shielt Sleeve	 TE Part #2394111-2 H&S 50mm, SWS	 TE Part #2394112-2 H&S 50mm, Cable clip	 TE Part #2394113-2 H&S 50mm, Cable cover
 TE Part #8-2399606-1 1POS,HVP1400,ASSY,180DEG,COD A	 TE Part #8-2399606-3 1POS,HVP1400,ASSY,180DEG,COD C		

Documents

Product Drawings

COVER,SHIPPING CAP FOR HD1000 PLUG

English

CAD Files

Customer View Model

ENG_CVM_CVM_2407805-1_B.3d_igs.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2407805-1_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2407805-1_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



HIVONEX CONNECTORS & CHARGING SOLUTIONS

English

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2407805-1](#)