




Connectors > Automotive Connectors > Data Connectivity Systems > Data Connectivity Headers



Connector System: **Wire-to-Board**

Sealable: **No**

Shielded: **Yes**

PCB Mount Orientation: **Vertical**

Number of Positions: **4**

Features

Product Type Features

Connector System	Wire-to-Board
Sealable	No

Configuration Features

PCB Mount Orientation	Vertical
Number of Positions	4

Body Features

Connector & Keying Code	A
-------------------------	---

Contact Features

Mating Tab Width	.5 mm[.02 in]
Mating Tab Thickness	.4 mm[.01 in]

Mechanical Attachment

Connector Mounting Type	Board Mount
-------------------------	-------------

Housing Features

Centerline (Pitch)	1.8 mm[.07 in]
--------------------	----------------



Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]

Operation/Application

Shielded	Yes
Circuit Application	Signal

Product Compliance


For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # 2304374-7
NANOMQS,SOLDER, PLATED

Customers Also Bought



TE Part #1-2308956-1
1-PORT MATENET HDR ASSY
180DEG, COD A



TE Part #2322791-3
40POS,TAB0.64X0.64,HDR ASSY,
90DEG



TE Part #2323854-2
TAB0.63X0.63,MS



TE Part #2137614-1
32P MQS header




TE Part #2323881-4
TAB1.5X0.6,MS



TE Part #1-2311788-2
12POS,HYBRID,HDR ASSY,90DEG,
SLDR



TE Part #2137614-2
32P MQS Header



TE Part #173860-1
070 MULTILOCK CAP ASSY 14P



TE Part #2322651-1
4POS,0.50 HSL,HDR ASSY,180DEG,
COD A



TE Part #2389935-1
4POS,TAB0.5X0.4,HDR ASSY,90DEG,
COD A

Documents

Product Drawings

2-PORT MATENET HDR ASSY 180DEG, COD A

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2415492-1_A1.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_2415492-1_A1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2415492-1_A1.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Product Specification](#)

English

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2415492-1](#)