




Connectors > Automotive Connectors > Data Connectivity Systems > Data Connectivity Housings



Cable Exit Angle: 180°

Number of Positions: 4

Shielded: No

Connector & Housing Type: Housing for Female Terminals

Mating Pin Diameter: .4 mm [.01 in]

Features

Product Type Features

Connector & Housing Type	Housing for Female Terminals
--------------------------	------------------------------

Configuration Features

Number of Positions	4
---------------------	---

Body Features

Cable Exit Angle	180°
------------------	------

Contact Features

Mating Pin Diameter	.4 mm[.01 in]
---------------------	---------------

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

Housing Features

Centerline (Pitch)	5 mm[.2 in]
--------------------	-------------



Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Cable Type	RG 174
Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]

Operation/Application

Shielded	No
Circuit Application	Signal

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts







TE Part # 2-2404815-9
1X4 COMBO,MATE-AX,HDR ASSY,
SEALED,COD Z




TE Part # 2306601-1
CVTY PLUG,MATE-AX,CVTY DIA,3.6,
BLK



TE Part # 2-2354440-9
4P,MATE-AX,PIN HSG ASSY,SLD,
180DEG,COD Z




TE Part # 2354440-9
4P,MATE-AX,PIN HSG ASSY,SLD,
180DEG,COD Z




TE Part # 2404815-9
1X4 COMBO,MATE-AX,HDR ASSY,
SEALED,COD Z


Customers Also Bought




TE Part #DT06-2S
PLG, 2P, GRY, N




TE Part #CAT-D48-ST273
DEUTSCH Solid Contacts




TE Part #DT04-2P
REC, 2P, GRY, N




TE Part #CAT-D487-W416
Wedgelocks: DEUTSCH DT



TE Part #CAT-AM71-CH8172
AMP SUPERSEAL 1.5MM,
CONNECTOR HOUSING



TE Part #281934-2
SINGLE WIRE SEAL



TE Part #114017-ZZ
SEALING PLUG, SIZE 12/16, WHT

Documents

- CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-2354439-9_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-2354439-9_A.3d_igs.zip

English



Customer View Model

[ENG_CVM_CVM_2-2354439-9_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-2354439-9](#)