



Terminals & Splices > Splices



Sealable: **Yes**
Number of Serrations: **0**
Product Length: **18.25 mm [.72 in]**
Government Qualified Splice: **No**
Packaging Method: **Bag/Box**

Features

Product Type Features

Sealable	Yes
Wire Insulation Support Retention Type	Non-Insulation Support

Configuration Features

Number of Serrations	0
Compatible With Wire & Cable Type	Discrete Wire

Dimensions

Product Length	18.25 mm[.72 in]
----------------	------------------

Usage Conditions

Insulation Option	Fully Insulated
Operating Temperature Range	-55 – 175 °C[-67 – 347 °F]

Industry Standards


Government Qualified Splice	No
-----------------------------	----

Packaging Features

Packaging Method	Bag/Box
------------------	---------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)






EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Customers Also Bought




TE Part #5053094268
RNF-100-1/4-BK-SP




TE Part #ZPF00000000011596
BJE 84




TE Part #751003-000
55PC0213-10-9CS2861




TE Part #808989-000
55PC0213-14-9CS2861




TE Part #496870-000
55PC1243-20-MST4-9CS2861




TE Part #970147-000
55PC1243-22-MST4-9CS2861



TE Part #873786-000
55PC4233-16-MST3-9CS2861



TE Part #A91340-000
55PC4233-22-MST3-9CS2861



Documents

Product Drawings

D-438-0103

English

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[D-438-0103](#)