



Wire Protection & Management > Interconnect Devices > SolderSleeve Shield Terminators



Operating Temperature (Max): 150 °C

Expanded Inside Diameter (Min): 5.08 mm [.2 in]

Recovered Inside Diameter (Max): 2.16 mm [.085 in]

Pre-Installed Lead: Yes

Resistance Properties: Splash Protection

Features

Product Type Features

Temperature Indicator	Yes
Temperature Indicator Type	Thermochromic

Configuration Features

Pre-Installed Lead Type	Braid Strap 654
Pre-Installed Lead	Yes

Dimensions

Shield Outside Diameter (Min)	2.15 mm[.085 in]
Compatible Jacket Diameter Range	5.08 mm[.2 in]
Product Length	16.5 mm[.65 in]
Expanded Inside Diameter (Min)	5.08 mm[.2 in]
Recovered Inside Diameter (Max)	2.16 mm[.085 in]

Usage Conditions

Operating Temperature (Max)	150 °C
Resistance Properties	Splash Protection
Wire Temperature (Max)	125 °C

Industry Standards

MIL/NAS Specification (MIL-S-83519, NAS-1747)	M83519/3-08
Government Qualified	No



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2024 (240) SVHC > Threshold: Pb (37% in Solder) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #CTJ620E06N-5145
PLUG ASSY



TE Part #53425-1
TERMINAL,PIDG PVF2 R 12-10 10



TE Part #YDTS26F25-35PAV001
PLUG ASSY



TE Part #866259-000
S02-08-R



TE Part #934769-000
55A1131-20-MST3-9CS2275



TE Part #CTJ116E02B-513
MODULE ASSY



TE Part #CTJ620E06N
PLUG ASSY



TE Part #YDIV40E17-26PNC009
RECP ASSY



TE Part #6-1617814-2
TD229-1002P=TD229-1002P

Documents

Product Drawings

S03-08-R

English

Product Specifications

Product Specification

English

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[S03-08-R](#)