



Wire Protection & Management > Interconnect Devices > SolderSleeve Shield Terminators



Operating Temperature (Max): 175 °C  
Expanded Inside Diameter (Min): 9.78 mm [.385 in]  
Recovered Inside Diameter (Max): 5.08 mm [.2 in]  
Pre-Installed Lead: No  
Wire Temperature (Max): 135 °C

Features

Configuration Features

Pre-Installed Lead	No
--------------------	----

Dimensions

Expanded Inside Diameter (Min)	9.78 mm[.385 in]
Recovered Inside Diameter (Max)	5.08 mm[.2 in]

Usage Conditions

Operating Temperature (Max)	175 °C
Wire Temperature (Max)	135 °C

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free




Solder Process Capability

Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Customers Also Bought




TE Part #864607-000  
202K142-25/225-0




TE Part #680105-000  
D-609-04




TE Part #680104-000  
D-609-03




TE Part #908877-000  
55PC6121-20-900




TE Part #CTJ-3D-09  
RAIL ASSY




TE Part #ZPF000000000121739  
182-0862-22




TE Part #CC1465-000  
D-500-0468-1-614-120



TE Part #YDTS20T13-35PCV001  
RECP ASSY



TE Part #146201-000  
SO63-1-9030CS2677



TE Part #605323-000  
SO63-2-9030CS2677

Documents

Product Drawings

D-108-0033

English



Product Specifications

Product Specification

English

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[D-108-0033](#)