



Wire Protection & Management > Heat Shrink Shapes > Heat Shrink Boots > Heat Shrink Boots: Non Lipped, Right Angle



Body Orientation: **Right Angle**

Molded Part Shape Code: **222**

Lipped: **No**

Material Code: **3**

Material Systems Code: **10**

[All Heat Shrink Boots: Non Lipped, Right Angle \(94\)](#)

## Features

### Configuration Features

Lipped	No
Adhesive Requirement	Adhesive Purchased Separately

### Body Features

Primary Product Material	Semi-Rigid Modified Polyolefin
Material Code	3
Material Systems Code	10

### Housing Features

Body Orientation	Right Angle
------------------	-------------

### Dimensions

Compatible Cable Diameter (Max)	5 mm, 6 mm, 7 mm, 8 mm [.196 in][.23 in][.27 in][.314 in]
Compatible Cable Diameter Range	3.8 – 9.9 mm [3.8 – 9.1 in]

### Usage Conditions

Operating Temperature Range	-55 – 135 °C [-67 – 275 °F]
Resistance Protection	Occasional Fluid Exposure

### Industry Standards

Compatible With Approved Standards Products	BS-G-198-5-DA, DEF Std 59-97 Issue 3
---	--------------------------------------



	Type DA, SAE AS I 81765/1, Type I, UL 224, File E85381
--	--

**Other**

Molded Part Shape Code	222
------------------------	-----

**Product Compliance**

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

**Product Compliance Disclaimer**

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

**Compatible Parts**




**Customers Also Bought**



TE Part #4-1625984-1  
HSA50 2K2 5%



TE Part #959025-000  
AD-1377-S-SPEC-CRIMP-TOOL



TE Part #811032-000  
382A012-12-0



TE Part #4-1879355-7  
RR03 5% 360K AMMO



TE Part #YDTS20W11-35SNV001  
RECP ASSY




TE Part #675714-000  
SO96-3-00



TE Part #620235-000  
D-108-0033



TE Part #RE11-442S  
PLUG ASSY



TE Part #237171-000  
MTC100-JH2-P32



TE Part #EK1531-000  
D-621-0008CS2866

## Documents

### Datasheets & Catalog Pages

[1654025\\_Sec4\\_-3](#)

English

### Raychem Molded Parts Visual Guide

English

### Product Specifications

[Product Specification](#)

English

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[222A111-3-0](#)