



Wire Protection & Management > Heat Shrink Shapes > Heat Shrink Caps



Wall Type: **Single Wall**
Material Code: **3**
Material Systems Code: **10**
Adhesive Requirement: **Adhesive Purchased Separately**
Operating Temperature Range: **-55 – 135 °C [-67 – 275 °F]**

Features

Product Type Features

Wall Type	Single Wall
-----------	-------------

Configuration Features

Adhesive Requirement	Adhesive Purchased Separately
----------------------	-------------------------------

Body Features

Sealant Type	None
Shrink Ratio	2:1
Primary Product Material	Crosslinked Polyolefin
Flexibility	Flexible
Primary Product Color	Black
Material Code	3
Material Systems Code	10

Dimensions

Recovered Wall Thickness (Nominal)	1.02 mm[.04 in]
Recovered Inside Diameter (Max)	2 mm[.08 in]
Expanded Inside Diameter (Min)	5.1 mm[.2 in]
Wall Thickness	Medium
Product Length	22 mm[.876 in]

Usage Conditions

--	--



Flammability Requirement	Flame-Retardant
Resistance Protection	Suitable for occasional exposure to fluids
Resistance Properties	Immersion Protection
Operating Temperature Range	-55 – 135 °C[-67 – 275 °F]

Other

Size Code	11
Molded Part Shape Code	101A

Product Compliance

For compliance documentation, visit the product page on TE.com>






EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



 TE Part # 890060-000 S1017-1.0X50	 TE Part # D856933001 100G1121-3.00-0/9-0	 TE Part # D292083001 100G0111-3.00-1	 TE Part # E267123001 100G0111-4.00-1
 TE Part # 1335613001 100G0111-4.00-2	 TE Part # 2630093001 100G0111-4.00-45	 TE Part # 2584333002 100G0111-4.00-6	 TE Part # E221163001 100G0111-4.00-8
 TE Part # CQ56513001 100G0121-3.00-0/9	 TE Part # CQ90593001 100G0121-4.00-0/9	 TE Part # CQ91273001 100G1121-3.00-6/9-0	 TE Part # CQ64993001 100G1121-4.00-6/9-0
 TE Part # CD68003001 100G1131-3.00-2/6/9-0	 TE Part # CQ23873001 100G0121-4.00-6/9	 TE Part # CT86473001 ZHPCG-15-1.0-2	 TE Part # CT89333001 ZHPCG-36-2.5-0
 TE Part # CD05863001 ZHPCG-15-6.0-0	 TE Part # 8089383001 ZHPCG-35-6.0-0	 TE Part # CQ48473001 ZHPCG-35-6.0-2	 TE Part # CQ47163001 100G0111-3.00-5


Customers Also Bought



TE Part #C71645-000
RMW-10/3-1200/ADH-0



TE Part #2428001-1
Std MIL-DTL-38999 Series III Conn Gasket



TE Part #966067-9
FER,WIRE,PL SLV,1.00/18,L8,RED,LP



TE Part #A39093-000
B-155-11



TE Part #9-1415036-1
PTMT00A0



TE Part #504777-000
55A4121-20-9/96-9CS2275



TE Part #TXM-433-LC
Module LC 433MHz AM OOK TX XMTR



TE Part #YDTS24T17-26PNV001
RECP ASSY



TE Part #YDTS24T17-35PDV001
RECP ASSY

Documents

Product Drawings

101A011-3-0

English

Datasheets & Catalog Pages

1654025_Sec4_-3

English

1654025_Sec4_101A011to094

English

Raychem Molded Parts Visual Guide

English

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[101A011-3-0](#)