



Relays & Contactors > Relays > Power Relays



Power Relay Type: **Industrial Panel Plug-In**

Coil Magnetic System: **Monostable, DC**

Coil Power Rating DC: **952 mW**

Coil Resistance: **64533 Ω**

Coil Special Features: **Electrical Indicator, LED, Protection Diode, UL Coil Insulation Class F**

Features

Product Type Features

Power Relay Type	Industrial Panel Plug-In
Relay Connection Type	Plug-In

Electrical Characteristics

Insulation Initial Dielectric Between Contacts & Coil	1200 Vrms
Insulation Initial Dielectric Between Open Contacts	1200 Vrms
Contact Limiting Making Current	12 A
Contact Limiting Short-Time Current	300 A
Insulation Creepage Class	3 – 5.5 mm
Coil Power Rating Class	800 – 1000 mW
Insulation Initial Dielectric Between Adjacent Contacts	2500 Vrms
Insulation Creepage Between Contact & Coil	4 mm[.157 in]
Contact Limiting Breaking Current	6 A
Coil Magnetic System	Monostable, DC
Coil Power Rating DC	952 mW
Coil Resistance	64533 Ω
Coil Special Features	Electrical Indicator, LED, Protection Diode, UL Coil Insulation Class F
Coil Voltage Rating	220 VDC



Contact Switching Load (Min)	10mA @ 12V
Contact Switching Voltage (Max)	240 VAC
Contact Voltage Rating	240 VAC

Body Features

Insulation Special Features	5000V Initial Surge Withstand Voltage between Contacts & Coil
Product Weight	30 g[1.058 oz]

Contact Features

Contact Arrangement	4 Form C (4 CO)
Contact Current Class	5 – 10 A
Contact Current Rating (Max)	6 A
Contact Material	AgNi90/10
Contact Number of Poles	4

Mechanical Attachment

Product Mount Type	Socket
--------------------	--------

Dimensions

Length Class (Mechanical)	25 – 30 mm
Insulation Clearance Class	2.5 – 4 mm
Height Class (Mechanical)	25 – 30 mm
Insulation Clearance Between Contact & Coil	3 mm
Width Class (Mechanical)	20 – 25 mm
Product Width	22.5 mm[.885 in]
Product Length	28 mm[1.1 in]
Product Height	29 mm[1.14 in]

Usage Conditions


Environmental Ambient Temperature (Max)	70 °C[158 °F]
Operating Temperature Range	-40 – 70 °C

Packaging Features

Packaging Method	Carton & Tube
------------------	---------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)





EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2017 (173) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts


 TE Part # 1-1415526-1 PT78742	 TE Part # 2-1415526-1 PT17021	 TE Part # 6-1415037-1 PT17040	 TE Part # 1860000-1 PT7874P
 TE Part # 1816124-1 PT17024	 TE Part # 4-1415033-1 PT78740	 TE Part # 5-1415037-1 PT17016	 TE Part # 5-1419111-9 PT28800



 TE Part # 3-1415043-1 PT78604	 TE Part # 1393162-1 PT28802	 TE Part # 4-1415043-1 PT78600	 TE Part # 5-1415034-1 PT78741
 TE Part # 1-1415539-4 PTML0220	 TE Part # 1-1415539-6 PTMG0220	 TE Part # 1415037-1 PTMT00L0	 TE Part # 9-1415036-1 PTMT00A0
 TE Part # 1860214-1 PT170P1 Jumper Link	 TE Part # 1860517-5 PT170R6 Jumper Bar	 TE Part # 6-1415043-1 PT78601	

Also in the Series

SCHRACK Miniature Relay PT



Power Relays(158)

Customers Also Bought

 TE Part #5749069-5 AMPLIMITE D-Sub Receptacle Assembly: Vertical, 1.27mm	 TE Part #1630019-4 HSC200 12R 5%	 TE Part #7-1415541-0 PT570LC4	 TE Part #2213189-1 Assembly, IPI Connector 22-18GA w/o cap
---	--	--	---



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_7-1415541-7_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_7-1415541-7_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_7-1415541-7_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Miniature Relay PT

English

Product Specifications

Definitions General Purpose Relays

English

Agency Approvals

VDE Certificate

English

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[7-1415541-7](#)