



Identification & Labeling > Labels > Standard Labels > CSL Self Laminating Polyester Labels



Label Type: **Blank Labels**

Label Style: **Die-Cut**

Label Adhesive Type: **Permanent**

Product Width: **12.7 mm [.5 in]**

Product Height: **19.1 mm [.75 in]**

[All CSL Self Laminating Polyester Labels \(20\)](#)

Features

Product Type Features

Label Type	Blank Labels
------------	--------------

Body Features

Primary Product Color	Clear
Primary Product Material	Clear Polyester

Dimensions

Product Width	12.7 mm[.5 in]
Product Height	19.1 mm[.75 in]

Usage Conditions

Operating Temperature Range	-40 – 120 °C[-40 – 248 °F]
-----------------------------	----------------------------

Printer/Label Features

Labels per Sheet	156
Printer Technology	Laser
Label Style	Die-Cut

Packaging Features

Packaging Quantity	4992
Packaging Method	Package

Other

--	--



Label Adhesive Type	Permanent
---------------------	-----------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-T3437-C8906
CSL Self Laminating Polyester Labels













TE Part # 187752-000
CR-107-LSR



TE Part # 394378-000
CR-110-LSR

Customers Also Bought



 <p>TE Part #794407-1 MINI UNML SCKT 20-16 AWG SN</p>	 <p>TE Part #1-1670916-1 2POS, MCON 1.2 LL REC SEALED</p>	 <p>TE Part #967067-1 MQS SGL WIRE SEAL</p>	 <p>TE Part #1456983-1 1X4 FEM UNSEALED LOW PROFILE, KEY A</p>
 <p>TE Part #173645-1 070 TAB CONT 16-20</p>	 <p>TE Part #1393366-1 V23540X7000Y 21=GET-FEM TERM S</p>	 <p>TE Part #7-1452668-3 MCON 1.2 LL REC SWS AG</p>	 <p>TE Part #183570-000 CR-106-LSR</p>
 <p>TE Part #C48138-000 MP-165102-10-8A</p>	 <p>TE Part #1601597-1 L061/076C16B=RTM 1100-3200</p>		

Documents

Product Drawings

CR-100-LSR

English

Datasheets & Catalog Pages

CSL and LSR - Self-Laminating Laser Printable Polyester Labels

English

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[CR-100-LSR](#)