



Relays & Contactors > Relays > Power Relays



Power Relay Type: **Industrial Panel Plug-In**

Coil Magnetic System: **Monostable, DC**

Coil Power Rating DC: **750 mW**

Coil Resistance: **64533 Ω**

Coil Special Features: **UL Coil Insulation Class F**

Features

Product Type Features

|                       |                          |
|-----------------------|--------------------------|
| Power Relay Type      | Industrial Panel Plug-In |
| Relay Connection Type | PCB Solder Pins          |

Electrical Characteristics

|   |                            |
|---|----------------------------|
| Insulation Initial Dielectric Between Contacts & Coil   | 1200 Vrms                  |
| Insulation Initial Dielectric Between Open Contacts     | 1200 Vrms                  |
| Contact Limiting Making Current                         | 12 A                       |
| Contact Limiting Short-Time Current                     | 300 A                      |
| Insulation Creepage Class                               | 3 – 5.5 mm                 |
| Coil Power Rating Class                                 | 600 – 800 mW               |
| Insulation Initial Dielectric Between Adjacent Contacts | 2500 Vrms                  |
| Insulation Creepage Between Contact & Coil              | 4 mm[.157 in]              |
| Contact Limiting Breaking Current                       | 6 A                        |
| Coil Magnetic System                                    | Monostable, DC             |
| Coil Power Rating DC                                    | 750 mW                     |
| Coil Resistance   | 64533 Ω                    |
| Coil Special Features                                   | UL Coil Insulation Class F |
| Coil Voltage Rating                                     | 220 VDC                    |
| Contact Switching Load (Min)                            | 1mA @ .02V                 |



|                                 |         |
|---------------------------------|---------|
| Contact Switching Voltage (Max) | 240 VAC |
| Contact Voltage Rating          | 240 VAC |

Body Features

|                             |   |
|-----------------------------|---|
| Insulation Special Features | 5000V Initial Surge Withstand Voltage between Contacts & Coil |
| Product Weight              | 30 g[1.058 oz]  |

Contact Features

|                              |                        |
|------------------------------|------------------------|
| Contact Arrangement          | 4 Form C (4 CO)        |
| Contact Current Class        | 5 – 10 A               |
| Contact Current Rating (Max) | 6 A                    |
| Contact Material             | AgNi90/10, Gold-Plated |
| Contact Number of Poles      | 4                      |

Mechanical Attachment

|                    |                       |
|--------------------|-----------------------|
| Product Mount Type | Printed Circuit Board |
|--------------------|-----------------------|

Dimensions

|   |                  |
|---|------------------|
| Length Class (Mechanical)                   | 25 – 30 mm       |
| Insulation Clearance Class                  | 2.5 – 4 mm       |
| Height Class (Mechanical)                   | 25 – 30 mm       |
| Insulation Clearance Between Contact & Coil | 3 mm             |
| Width Class (Mechanical)                    | 20 – 25 mm       |
| Product Width                               | 22.5 mm[.885 in] |
| Product Length                              | 28 mm[1.1 in]    |
| Product Height                              | 30 mm[1.18 in]   |

Usage Conditions

|   |               |
|---|---------------|
| Environmental Ambient Temperature (Max) | 70 °C[158 °F] |
| Operating Temperature Range             | -40 – 70 °C   |

Packaging Features

|                  |               |
|------------------|---------------|
| Packaging Method | Carton & Tube |
|------------------|---------------|

Other

|                |             |
|----------------|-------------|
| Solder Process | Wave Solder |
|----------------|-------------|

Product Compliance



For compliance documentation, visit the product page on [TE.com](#)>

|   |   |
|---|---|
| EU RoHS Directive 2011/65/EU                  | Compliant   |
| EU ELV Directive 2000/53/EC                   | Compliant   |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold   |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2024 (240)<br>Candidate List Declared Against: JAN 2024 (240)<br>Does not contain REACH SVHC |
| Halogen Content                               | Not Low Halogen - contains Br or Cl > 900 ppm.  |
| Solder Process Capability                     | Not applicable for solder process capability  |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




Also in the Series | [SCHRACK Miniature Relay PT](#)




Customers Also Bought




TE Part #DTT-20-03  
CRIMP TOOL




TE Part #HDP24-24-16SE-L015  
REC, 16P, BLK, E, THD, 12, S




TE Part #K1007153  
Toggle Switch 08-1-1-13




TE Part #DRC16-70SBE-P013UK  
PLG, 70P, BLK, E, SEAL BOND, B




TE Part #YHDP26-24-35PEL017  
PLG, 35P, BLK, E, RNG, 16/20, P




TE Part #2-2176245-2  
CRGS1206 5% 56R



TE Part #K1002956  
Toggle Switch 08-4-1-13



TE Part #K1008699  
Relay 26-60-05



TE Part #SRK-PC-080-25-601  
PIN, SOLID, SIZE M8, 25mm2, AG

Documents

- CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_9-1415542-8\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_9-1415542-8\_A.3d\_igs.zip



English

Customer View Model

ENG\_CVM\_CVM\_9-1415542-8\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Miniature Relay PT

English

Product Specifications

Definitions General Purpose Relays

English

Agency Approvals

VDE Certificate

English

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[9-1415542-8](#)