



LOC		DIST		REVISIONS						
GE	00	P	LTR	DESCRIPTION			DATE	DWN	APVD	
			E1	REVISED PER ECO-11-005030			26APR2011	RK	HMR	

1 MATERIAL: 0.30 THICK COPPER ALLOY, PREPLATED WITH 0.0008 MINIMUM THICK REFLOW TIN OR BRIGHT TIN (ELV COMPLIANT).

ALTERNATE MATERIAL: 0.30 THICK COPPER ALLOY, PREPLATED WITH 0.0008 MINIMUM THICK BRIGHT TIN (ELV COMPLIANT).




2



3

REVERSE REELING DIRECTION

4. QUALIFICATION OF THE CRIMP APPLICATION TOOLING SHALL BE CONTROLLED BY THE REQUIREMENTS ESTABLISHED UNDER USCAR 21.
5. LOOSE END SPLICING TO BE USED.



SECTION A-A

SECTION F-F

SECTION G-G

3	1326032-6 REELED FOR AMP APPLICATORS							12 AWG	I-1326032-2
	1326032-5 REELED FOR AMP APPLICATORS							14 AWG	I-1326032-1
	1326032-4 REELED FOR AMP APPLICATORS							16 AWG	I-1326032-
	1326032-3 REELED FOR AMP APPLICATORS							18 AWG	1326032-9
	1326032-2 REELED FOR AMP APPLICATORS							20 AWG	1326032-8
	1326032-1 REELED FOR AMP APPLICATORS							22 AWG	1326032-7
2	1.35	6.8	4.30	6.09	4.7	2.70	5.25	12 AWG	1326032-6
	1.35	6.5	4.30	5.62	3.9	1.70	3.88	14 AWG	1326032-5
	1.10	5.6	3.80	4.54	3.9	1.70	3.88	16 AWG	1326032-4
	1.10	5.6	3.80	4.54	3.3	1.30	2.76	18 AWG	1326032-3
	0.90	5.0	3.40	4.11	3.3	1.30	2.76	20 AWG	1326032-2
	0.90	5.0	3.40	4.11	2.5	0.90	2.11	22 AWG	1326032-1
REELING	N	L	ØK	J	H	ØF	E	WIRE SIZE	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN D. STRAUSSER 28APR99		TE Connectivity	
CHK D. BROWN 28APR99				APVD D. BROWN 28APR99		NAME	
DIMENSIONS: mm				PRODUCT SPEC		2.8mm RECEPTACLE, SEALED	
TOLERANCES UNLESS OTHERWISE SPECIFIED:				SAE/USCAR-2 8/97		SIZE CAGE CODE DRAWING NO	
9 PLC ±.3				APPLICATION SPEC		A1 00779 C=1326032	
1 PLC ±0.10				114-13013		RESTRICTED TO	
3 PLC ±				WEIGHT		SCALE 10:1	
5 PLC ±				CUSTOMER DRAWING		SHEET 1 OF 1	
4 PLC ±						REV E1	
ANGLES ±4°							
FINISH							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1326032-6](#)