



# STANDARD CIRCULAR CONNECTORS



✓ Active

## TE CONNECTIVITY (TE) JAM NUT RECEPTACLE

DEUTSCH | 38999 Series III

D38999/24MC04PN  
 TE Internal Number: YACT24MC04PNV00100  
 Mil-Spec: D38999/24MC04PN  
 Alias ID: ACT24MC04PNV001

Always EU RoHS/ELV Compliant

- Product Type **Connector**
- Mounting Style **Jam Nut**
- Shell Plating Material **Electroless Nickel**
- Shell Material **Composite**
- Polarization Code **N**

No documentation available.

Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features	Product Type	<b>Connector</b>
	Connector System	<b>Wire-to-Panel</b>
	Shell Size	<b>C (13)</b>
	Sealed	<b>Yes</b>
	Connector Style	<b>Receptacle</b>
	Shell Type	<b>Jam Nut Receptacle</b>
	Assembly Type	<b>Electrical Connector</b>

Configuration Features	Number of Power Positions	<b>4</b>
	Preloaded	<b>No</b>
	Number of Positions	<b>4</b>
	Factory Installed Backshell	<b>No</b>
	Positions Unloaded	<b>All</b>
	Keying	<b>Keyway Polarization N</b>
	Position Keyed	<b>N</b>

Electrical Characteristics	Operating Voltage	<b>600 VAC [ 850 VDC ]</b>
	Voltage (Vrms)	<b>1800</b>

Body Features	Shell Plating Material	<b>Electroless Nickel</b>
	Shell Material	<b>Composite</b>
	Insulation Material	<b>Hard Dielectric/Silicone</b>
	Hermetically Sealed	<b>No</b>
	Weight	<b>15.5 g [ .0342 lb ]</b>
	Fluid Type	<b>Coolanol 25, M2-V, MIL-DTL-5624 (JP-4, JP-5), MIL-DTL-83133 (JP-8), MIL-PRF-23699, MIL-PRF-5606, MIL-PRF-7808, SEA-AMS1424 Type I</b>
	Environmental Protection Type	<b>Elastomer Sealed</b>
	O-Ring Material	<b>Silicone</b>
	Environmental Protection	<b>Yes</b>
	Feedthrough Type	<b>No</b>
	Peripheral Seal Material	<b>Silicone</b>
Entry Style	<b>Rear Insertion</b>	
Contact Features	Contact Layout	<b>C04</b>
	Contact Type	<b>Pin</b>
	Contact Quantity (Size 16)	<b>4</b>
Mechanical Attachment	Mounting Style	<b>Jam Nut</b>
	Polarization Code	<b>N</b>
	Mating Alignment Type	<b>Keyed</b>
	Mating Retention	<b>With</b>
	Flange	<b>Jam Nut Flange</b>
	Mating Retention Type	<b>Triple Start Threaded</b>
	Panel Mount Retention	<b>With</b>
	Panel Mount Retention Type	<b>Jam Nut</b>
Housing Features	Alignment Keyed	<b>Clocking</b>
Dimensions	Panel Thickness	<b>1.58 – 3.2 mm [ .062 – .126 in ]</b>
	Accepts Wire Insulation Diameter Range	<b>1.65 – 2.77 mm [ .065 – .109 in ]</b>
	Assembly Length	<b>33 mm [ 1.3 in ]</b>
Usage Conditions	Operating Temperature Range	<b>-65 – 200 °C [ -85 – 392 °F ]</b>
	Fluid Resistance	<b>Yes</b>

---

Operation/Application

Durability Rating (Cycles)

**500**

---

Packaging Features

Packaging Quantity

**1**

---

Product Compliance

[Statement of Compliance](#)  
PDF

[VIEW ALL PRODUCT COMPLIANCE](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[D38999/24MC04PN](#)