

Film Capacitors

High Current, Wrap-and-Fill, Metallized Polypropylene



FEATURES

- Wire or lug terminals
- High stability
- High ripple to 30 amperes
- Low inductance
- Low ESR


PERFORMANCE CHARACTERISTICS

Operating Temperature: - 55 °C to + 105 °C
Capacitance Range: 1.0 μF to 30.0 μF
Capacitance Tolerance: ± 10 %, ± 5 %
DC Voltage Rating: 100 WVDC to 400 WVDC
Equivalent Series Resistance: 20 kHz to 100 kHz
Dissipation Factor: 0.1 % maximum
 Measured at 1000 Hz at + 25 °C
 $\Delta V/\Delta T$: 10 V/millisecond maximum
Voltage Test: 200 % of rated voltage for 2 minutes
Insulation Resistance: Measured at 100 WVDC after a 2 minute charge.
 At + 25 °C: 200 000 Megohm - Microfarads, or 400 000 Megohm minimum
Vibration Test (Condition B): No mechanical damage, short, open or intermittent circuits.

DC Life Test: 140 % of rated voltage for 1000 hours at + 105 °C. No visible damage. No open or short circuits.
 Maximum Δ CAP ± 1.0 %
 Minimum IR = 50 % of initial limit
 Maximum DF = 0.10 %
Humidity Test: 95 % relative humidity at + 40 °C for 250 hours. No visible damage.
 Maximum Δ CAP ± 1.0 %
 Minimum IR = 20 % of initial limit
 Maximum DF = 0.12 %

PHYSICAL CHARACTERISTICS

Pull Test:
Wire Leads: - 5 pounds (2.3 kilograms) for one minute. No physical damage.
Terminal Lugs: - 10 pounds (4.5 kilograms) for one minute. No physical damage.
Lead Bend: After three complete consecutive bends, no damage.
Marking: Sprague® trademark, type or part number, capacitance and voltage.



* Leads to be within ± 0.062" [1.57 mm] of center line at egress but not less than 0.031" [0.79 mm] from edge (Terminal Style L only).



Film Capacitors
High Current, Wrap-and-Fill,
Metallized Polypropylene

STANDARD RATINGS in inches [millimeters]											
CAPACITANCE (μ F)	PART NUMBER**	CASE SIZE		ESR LIMIT (Milliohm) 20 kHz - 100 kHz	MAXIMUM RIPPLE CURRENT (Amps rms) at 20 kHz - 100 kHz Case Temperature at						
		D	L		+25 °C	+35 °C	+45 °C	+55 °C	+65 °C	+75 °C	+85 °C
Terminal Style L - Units with Wire Leads											
100 WVDC											
1.0*	735P105X9100L	0.531 [13.49]	0.750 [19.05]	15.0	9.2	8.5	7.8	7.0	6.0	4.9	4.5
2.0	735P205X9100L	0.596 [15.14]	0.938 [23.81]	12.0	10.8	10.0	9.1	8.2	7.0	5.8	5.3
3.0	735P305X9100L	0.717 [18.21]	0.938 [23.81]	11.0	12.1	11.2	10.3	9.2	8.0	6.5	5.9
5.0	735P505X9100L	0.733 [18.62]	1.250 [31.75]	10.0	13.8	12.7	11.6	10.4	9.0	7.4	6.7
10.0*	735P106X9100L	0.898 [22.81]	1.500 [38.10]	9.0	15.0	15.0	14.2	12.7	11.0	9.0	8.2
20.0	735P206X9100L	1.000 [25.40]	2.250 [57.15]	8.0	15.0	15.0	15.0	15.0	13.6	11.1	10.0
30.0	735P306X9100L	1.200 [30.48]	2.250 [57.15]	6.0	15.0	15.0	15.0	15.0	15.0	12.4	11.4
200 WVDC											
1.0*	735P105X9200L	0.512 [13.01]	1.250 [31.75]	20.0	7.3	7.3	7.3	7.3	7.2	5.9	5.4
2.0*	735P205X9200L	0.698 [17.73]	1.250 [31.75]	15.0	12.0	12.0	11.3	10.1	8.7	7.1	6.5
3.0	735P305X9200L	0.747 [18.97]	1.500 [38.10]	13.0	15.0	13.8	12.6	11.3	9.8	8.0	7.3
5.0*	735P505X9200L	0.862 [21.89]	1.750 [44.45]	11.0	15.0	15.0	14.7	13.1	11.4	9.3	8.5
10.0*	735P106X9200L	1.030 [26.16]	2.250 [57.15]	9.0	15.0	15.0	15.0	15.0	13.8	11.3	10.3
20.0	735P206X9200L	1.440 [36.58]	2.250 [57.15]	6.0	15.0	15.0	15.0	15.0	15.0	14.1	12.8
400 WVDC											
1.0*	735P105X9400L	0.713 [18.11]	1.500 [38.10]	19.0	9.5	9.5	9.5	9.5	9.5	7.8	7.1
2.0*	735P205X9400L	0.895 [22.73]	1.750 [44.45]	15.0	15.0	15.0	15.0	13.4	11.6	9.5	8.7
3.0*	735P305X9400L	1.086 [27.58]	1.750 [44.45]	12.0	15.0	15.0	15.0	15.0	13.1	10.7	9.8
5.0*	735P505X9400L	1.192 [30.28]	2.250 [57.15]	10.0	15.0	15.0	15.0	15.0	15.0	12.5	11.4
10.0*	735P106X9400L	1.668 [42.37]	2.250 [57.15]	6.0	15.0	15.0	15.0	15.0	15.0	15.0	14.1
Terminal Style H - Units with Terminal Lugs											
100 WVDC											
1.0	735P105X9100H	0.531 [13.49]	0.875 [22.23]	15.0	10.3	9.5	8.7	7.8	6.7	5.5	5.0
2.0	735P205X9100H	0.596 [15.14]	1.062 [26.97]	12.0	12.0	11.0	10.0	8.9	7.8	6.3	5.8
3.0	735P305X9100H	0.717 [18.21]	1.062 [26.97]	11.0	13.3	12.3	11.2	10.0	8.7	7.1	6.5
5.0	735P505X9100H	0.733 [18.62]	1.375 [34.93]	10.0	14.8	13.7	12.5	11.2	9.7	7.9	7.2
10.0	735P106X9100H	0.898 [22.81]	1.625 [41.28]	9.0	17.8	16.5	15.0	13.5	11.7	9.5	8.7
20.0	735P206X9100H	1.000 [25.40]	2.375 [60.33]	8.0	21.6	20.0	18.3	16.4	14.2	11.6	10.6
30.0	735P306X9100H	1.200 [30.48]	2.375 [60.33]	6.0	24.3	22.5	20.5	18.4	15.9	13.0	11.9
200 WVDC											
1.0	735P105X9200H	0.512 [13.00]	1.375 [34.93]	20.0	7.3	7.3	7.3	7.3	7.3	6.4	5.8
2.0	735P205X9200H	0.698 [17.73]	1.375 [34.93]	15.0	14.3	13.3	12.1	10.8	9.4	7.7	7.0
3.0	735P305X9200H	0.747 [18.97]	1.625 [41.28]	13.0	15.9	14.7	13.5	12.0	10.4	8.5	7.8
5.0	735P505X9200H	0.862 [21.89]	1.875 [47.63]	11.0	18.3	17.0	15.5	13.9	12.0	9.8	8.9
10.0	735P106X9200H	1.030 [26.16]	2.375 [60.33]	9.0	22.4	20.7	18.9	16.9	14.6	12.0	10.9
20.0	735P206X9200H	1.440 [36.58]	2.375 [60.33]	6.0	27.4	25.4	23.2	20.7	17.9	14.7	13.4
400 WVDC											
1.0	735P105X9400H	0.713 [18.11]	1.625 [41.28]	19.0	9.5	9.5	9.5	9.5	9.5	8.3	7.5
2.0	735P205X9400H	0.895 [22.73]	1.875 [47.63]	15.0	15.0	15.0	15.0	14.2	12.3	10.0	9.1
3.0	735P305X9400H	1.086 [27.58]	1.875 [47.63]	12.0	21.1	19.5	17.8	15.9	13.8	11.3	10.3
5.0	735P505X9400H	1.192 [30.28]	2.375 [60.33]	10.0	24.4	22.6	20.6	18.5	16.0	13.1	11.9
10.0	735P106X9400H	1.668 [42.37]	2.375 [60.33]	6.0	30.0	27.8	25.4	22.7	19.7	16.1	14.7

* These ratings are stocked.

** Part Numbers listed are for a capacitance tolerance of $\pm 10\%$. To specify $\pm 5\%$ tolerance, change the "X9" in the Part Number to "X5".

ORDERING INFORMATION				
735P	105	X9	100	L
TYPE	CAPACITANCE	CAPACITANCE TOLERANCE	DC VOLTAGE RATING	TERMINAL STYLE
	This is expressed in picofarads. The first two digits are the significant figures. The third is the number of zeros to follow.	X9 = $\pm 10\%$ X5 = $\pm 5\%$	This is expressed in volts.	L = Wire Leads H = Lugs



Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay:](#)

[735P205X9100L](#) [735P206X9100L](#) [735P205X9400L](#) [735P106X9100L](#) [735P105X9100L](#) [735P305X9100L](#)
[735P305X9400L](#) [735P106X9400L](#) [735P105X9400L](#) [735P106X9400H](#) [735P505X9200L](#) [735P305X9200L](#)
[735P505X9400L](#) [735P106X9200L](#) [735P105X9200L](#) [735P505X9100L](#) [735P206X9200H](#) [735P205X9200L](#)
[735P206X9200L](#)