



Connectors > Connector Backshells & Adapters > Screened Backshells & Adapters

Cable Diameter Range: 4 – 64 mm [ 156 – 25 in ]

Adapter Entry Size: 05

Adapter Plating Material: Aluminum Alloys: Electroless Nickel per SAE AMS-C-26074, Class 3 or Class 4, Grade B, Steel & Other

Base Metals Heat Treatable to Improve Hardness: Electroless Nickel per SAE AMS-C-26074, Class 1, Grade B

Style: Shielded Boot

Termination Device Type: Magneform Ring

## Features

### Product Type Features

Style	Shielded Boot
Termination Device Type	Magneform Ring

### Body Features

Adapter Entry Size	05
Adapter Plating Material	Aluminum Alloys: Electroless Nickel per SAE AMS-C-26074, Class 3 or Class 4, Grade B, Steel & Other Base Metals Heat Treatable to Improve Hardness: Electroless Nickel per SAE AMS-C-26074, Class 1, Grade B

### Dimensions

Cable Diameter Range	4 – 64 mm[156 – 25 in]
----------------------	------------------------

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2019 (197) Candidate List Declared Against: JAN 2019 (197)
Halogen Content	Out of Scope - excluded from Halogen requirements
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Also in the Series | **Raychem Magnaform Backshells**




Screened Backshells & Adapters(291)




Unscreened Backshells & Adapters(1)

Customers Also Bought



TE Part #E53607-000  
208M816-19C12




TE Part #C02500-000  
208M910-19C06



TE Part #2164323001  
55A0113-16-9



TE Part #216432-000  
55A0113-16-9



TE Part #CZ3262-000  
55A3121-22-0/9



TE Part #5054104024  
RNF-100-3/16-BN-SP



TE Part #997861-000  
STXR40AB45-1210BI



TE Part #C13950-000  
STXR40AB90-1414BI



## Documents

### Product Drawings

[203M010-19C05](#)

English

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_807175-000\\_O.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_807175-000\\_O.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_807175-000\\_O.3d\\_stp.zip](#)

English

### Datasheets & Catalog Pages

[5-1654025-5\\_sec6\\_Adapters](#)

English

### Product Specifications

[General Information Package for Solid, Spin Coupling and Shielded Adapters](#)

English

[Product Specification](#)

English

### Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[203M010-19C05](#)