

Decade Divider, Single In-Line, Thin Film Divider, Through Hole Resistor Network



Precision resistor networks comprised of series-connected decade values are provided in single-in-line style with edgemounted leads on 100 mil centers. Integrated thin film construction, laser-trimmed to extremely tight tolerances, insures exceptionally close tracking over temperature and throughout operating life, in either voltage division or current monitoring mode. Voltage coefficient and noise are extremely low. Designers gain several advantages over the use of discrete resistor sets, including smaller size, better overall tracking, greater reliability, and lower cost.

FEATURES

- Tight ratio tolerance (0.01 %)
- 5 decade ratio divider
- High voltage capability (300 V)
- Compliant to RoHS Directive 2002/95/EC
- Halogen-free according to IEC 61249-2-21 definition



RoHS*
COMPLIANT
HALOGEN
FREE


Note

* Pb containing terminations are not RoHS compliant, exemptions may apply

TYPICAL PERFORMANCE

	ABSOLUTE	TRACKING
TCR	25	5
	ABSOLUTE	RATIO
TOL.	0.1	0.01

SCHEMATIC



STANDARD ELECTRICAL SPECIFICATIONS

TEST	SPECIFICATIONS	CONDITIONS
Material	Passivated nichrome	-
Pin/Lead Number	6	-
Resistance Range	100 Ω to 1 MΩ total	-
TCR: Absolute	± 25 ppm/°C	0 °C to + 70 °C
TCR: Tracking	± 5 ppm/°C	0 °C to + 70 °C
Tolerance: Absolute	± 0.1 %	+ 25 °C
Tolerance: Ratio	± 0.01 % to ± 0.1 %	+ 25 °C
Power Rating: Resistor	0.100 W	Maximum at + 70 °C
Power Rating: Package	0.500 W	Maximum at + 70 °C
Stability: Absolute	1000 ppm	2000 h at + 70 °C
Stability: Ratio	200 ppm	2000 h at + 70 °C
Voltage Coefficient	0.1 ppm/V	-
Working Voltage	300 V	-
Operating Temperature Range	0 °C to + 70 °C	-
Storage Temperature Range	- 55 °C to + 125 °C	-
Noise	- 20 dB	-
Thermal EMF	0.08 μV/°C	-
Shelf Life Stability: Absolute	ΔR ± 0.01 %	1 year at + 25 °C
Shelf Life Stability: Ratio	ΔR ± 0.002 %	1 year at + 25 °C

DIMENSIONS AND IMPRINTING in inches and millimeters			
	DIMENSION	INCHES	MILLIMETERS
	A	0.100 max.	2.54
	B	0.620 max.	15.78
	C	0.350 max.	8.89
	D	0.125 min.	0.25
	E	0.010 typ.	2.54
	F	0.020 typ.	0.51
	G	0.1 (5 x) typ.	2.54

PART NUMBER 100-	267-T	267-Q	267-A	267-B
Ratio Tolerance ⁽¹⁾	0.01 %	0.025 %	0.05 %	0.1 %
Voltage Rating	300 V			
Noise Index	< - 30 dB			


Note
⁽¹⁾ Excluding the 100 Ω

$$\frac{R1 + R2 + R3 + R4}{RT} = \frac{100 \text{ k}\Omega}{1 \text{ M}\Omega} = 0.1$$

$$\frac{R1 + R2 + R3}{RT} = \frac{10 \text{ k}\Omega}{1 \text{ M}\Omega} = 0.01$$

$$\frac{R1 + R2}{RT} = \frac{1 \text{ k}\Omega}{1 \text{ M}\Omega} = 0.001$$

$$R1 = 100 \Omega \pm 0.1 \%$$



MECHANICAL SPECIFICATIONS	
Resistive Element	Passivated nichrome
Substrate Material	Alumina
Body	Conformal coated
Terminals	Copper alloy
Marking Resistance to Solvents	Per MIL-PRF-83401
Tin/Lead Option	Sn60 - Sn63
Lead (Pb)-free Option	Sn96.5, Ag3.0, Cu0.5
Tin/Lead and Lead (Pb)-free Finish	Hot solder dip

GLOBAL PART NUMBER INFORMATION																													
New Global Part Numbering: VTF100-267TUF																													
<table border="1"> <tr> <td>V</td><td>T</td><td>F</td><td>1</td><td>0</td><td>0</td><td>-</td><td>2</td><td>6</td><td>7</td><td>T</td><td>B</td><td>X</td> </tr> <tr> <td>V</td><td>T</td><td>F</td><td>1</td><td>0</td><td>0</td><td>S</td><td>-</td><td>2</td><td>6</td><td>7</td><td>T</td><td>B</td><td>X</td> </tr> </table>	V	T	F	1	0	0	-	2	6	7	T	B	X	V	T	F	1	0	0	S	-	2	6	7	T	B	X		
V	T	F	1	0	0	-	2	6	7	T	B	X																	
V	T	F	1	0	0	S	-	2	6	7	T	B	X																
<table border="1"> <tr> <td>SERIES MODEL (10 or 11 digits)</td> </tr> <tr> <td>VTF100-267 (Tin lead)</td> </tr> <tr> <td>VTF100S-267 (Lead (Pb)-free) (e1)</td> </tr> </table>	SERIES MODEL (10 or 11 digits)	VTF100-267 (Tin lead)	VTF100S-267 (Lead (Pb)-free) (e1)	<table border="1"> <tr> <td>TOLERANCE (1 digit)</td> </tr> <tr> <td>T = 0.01 % ratio</td> </tr> <tr> <td>Q = 0.025 % ratio</td> </tr> <tr> <td>A = 0.05 % ratio</td> </tr> <tr> <td>B = 0.1 % ratio</td> </tr> </table>	TOLERANCE (1 digit)	T = 0.01 % ratio	Q = 0.025 % ratio	A = 0.05 % ratio	B = 0.1 % ratio	<table border="1"> <tr> <td>PACKAGING (2 digits)</td> </tr> <tr> <td>BX = Boxed</td> </tr> </table>	PACKAGING (2 digits)	BX = Boxed																	
SERIES MODEL (10 or 11 digits)																													
VTF100-267 (Tin lead)																													
VTF100S-267 (Lead (Pb)-free) (e1)																													
TOLERANCE (1 digit)																													
T = 0.01 % ratio																													
Q = 0.025 % ratio																													
A = 0.05 % ratio																													
B = 0.1 % ratio																													
PACKAGING (2 digits)																													
BX = Boxed																													
Historical Part Number example: 100-267Q (for reference purposes only)																													
<table border="1"> <tr> <td>100</td> </tr> <tr> <td>SERIES</td> </tr> </table>	100	SERIES	<table border="1"> <tr> <td>267</td> </tr> <tr> <td>MODEL</td> </tr> </table>	267	MODEL	<table border="1"> <tr> <td>Q</td> </tr> <tr> <td>TOLERANCE</td> </tr> </table>	Q	TOLERANCE																					
100																													
SERIES																													
267																													
MODEL																													
Q																													
TOLERANCE																													



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay:](#)

[VTF100-267QUF](#) [VTF100-267AUF](#)