


Super Fast Soft Recovery Avalanche Sinterglass Diode

Features

- Miniature axial leaded
- Glass passivated
- Hermetically sealed glass envelope
- Low reverse current
- High reverse voltage
- Lead (Pb)-free component
- Component in accordance to RoHS 2002/95/EC and WEEE 2002/96/EC



95 10526

Applications

TV and monitor
SMPS
Electronic ballast

Parts Table

Part	Type differentiation	Package
BYT43A	$V_R = 50 \text{ V} @ I_{FAV} = 1 \text{ A}$	DOT-30B
BYT43B	$V_R = 100 \text{ V} @ I_{FAV} = 1 \text{ A}$	DOT-30B
BYT43D	$V_R = 200 \text{ V} @ I_{FAV} = 1 \text{ A}$	DOT-30B
BYT43G	$V_R = 400 \text{ V} @ I_{FAV} = 1 \text{ A}$	DOT-30B
BYT43J	$V_R = 600 \text{ V} @ I_{FAV} = 1 \text{ A}$	DOT-30B
BYT43K	$V_R = 800 \text{ V} @ I_{FAV} = 1 \text{ A}$	DOT-30B
BYT43M	$V_R = 1000 \text{ V} @ I_{FAV} = 1 \text{ A}$	DOT-30B

Absolute Maximum Ratings

$T_{amb} = 25 \text{ }^\circ\text{C}$, unless otherwise specified

Parameter	Test condition	Part	Symbol	Value	Unit
Reverse voltage = Repetitive peak reverse voltage		BYT43A	$V_R = V_{RRM}$	50	V
		BYT43B	$V_R = V_{RRM}$	100	V
		BYT43D	$V_R = V_{RRM}$	200	V
		BYT43G	$V_R = V_{RRM}$	400	V
		BYT43J	$V_R = V_{RRM}$	600	V
		BYT43K	$V_R = V_{RRM}$	800	V
		BYT43M	$V_R = V_{RRM}$	1000	V
Peak forward surge current	$t_p = 8.3 \text{ ms}$, half sinewave		I_{FSM}	30	A

Parameter	Test condition	Part	Symbol	Value	Unit
Average forward current	Lead length $l = 10$ mm, $T_L = 25$ °C		I_{FAV}	1	A
Junction and storage temperature range			$T_j = T_{stg}$	- 55 to + 175	°C
Non repetitive reverse avalanche energy	$I_{(BR)R} = 0.4$ A		E_R	10	mJ

Maximum Thermal Resistance

$T_{amb} = 25$ °C, unless otherwise specified

Parameter	Test condition	Part	Symbol	Value	Unit
Junction ambient	Lead length $l = 10$ mm, $T_L =$ constant		R_{thJA}	60	K/W
	on PC board with spacing 25 mm		R_{thJA}	110	K/W

Electrical Characteristics

$T_{amb} = 25$ °C, unless otherwise specified

Parameter	Test condition	Part	Symbol	Min	Typ.	Max	Unit
Forward voltage	$I_F = 1$ A	BYT43A- BYT43J	V_F			1.6	V
		BYT43K- BYT43M	V_F			2	V
Reverse current	$V_R = V_{RRM}$		I_R			5	μA
	$V_R = V_{RRM}$, $T_j = 150$ °C		I_R			150	μA
Reverse breakdown voltage	$I_R = 100$ μA	BYT43A	$V_{(BR)R}$	50			V
		BYT43B	$V_{(BR)R}$	100			V
		BYT43D	$V_{(BR)R}$	200			V
		BYT43G	$V_{(BR)R}$	400			V
		BYT43J	$V_{(BR)R}$	600			V
		BYT43K	$V_{(BR)R}$	800			V
		BYT43M	$V_{(BR)R}$	1000			V
Reverse recovery time	$I_F = 0.5$ A, $I_R = 1$ A, $i_R = 0.25$ A	BYT43A- BYT43J	t_{rr}			50	ns
		BYT43K- BYT43M	t_{rr}			75	ns

Typical Characteristics ($T_{amb} = 25\text{ }^{\circ}\text{C}$ unless otherwise specified)




Figure 1. Max. Thermal Resistance vs. Lead Length




Figure 4.




Figure 2. Max. Reverse Current vs. Junction Temperature




Figure 5. Max. Average Forward Current vs. Ambient Temperature




Figure 3. Forward Current vs. Forward Voltage




Figure 6. Reverse Current vs. Junction Temperature




Figure 7. Max. Reverse Power Dissipation vs. Junction Temperature




Figure 8. Max. Reverse Power Dissipation vs. Junction Temperature





Figure 9. Diode Capacitance vs. Reverse Voltage

Package Dimensions in mm

Standard Glass Case
DOT 30 B
Weight max. 0.5g



Ozone Depleting Substances Policy Statement

It is the policy of Vishay Semiconductor GmbH to

1. Meet all present and future national and international statutory requirements.
2. Regularly and continuously improve the performance of our products, processes, distribution and operating systems with respect to their impact on the health and safety of our employees and the public, as well as their impact on the environment.

It is particular concern to control or eliminate releases of those substances into the atmosphere which are known as ozone depleting substances (ODSs).

The Montreal Protocol (1987) and its London Amendments (1990) intend to severely restrict the use of ODSs and forbid their use within the next ten years. Various national and international initiatives are pressing for an earlier ban on these substances.

Vishay Semiconductor GmbH has been able to use its policy of continuous improvements to eliminate the use of ODSs listed in the following documents.

1. Annex A, B and list of transitional substances of the Montreal Protocol and the London Amendments respectively
2. Class I and II ozone depleting substances in the Clean Air Act Amendments of 1990 by the Environmental Protection Agency (EPA) in the USA
3. Council Decision 88/540/EEC and 91/690/EEC Annex A, B and C (transitional substances) respectively.

Vishay Semiconductor GmbH can certify that our semiconductors are not manufactured with ozone depleting substances and do not contain such substances.

We reserve the right to make changes to improve technical design and may do so without further notice.

Parameters can vary in different applications. All operating parameters must be validated for each customer application by the customer. Should the buyer use Vishay Semiconductors products for any unintended or unauthorized application, the buyer shall indemnify Vishay Semiconductors against all claims, costs, damages, and expenses, arising out of, directly or indirectly, any claim of personal damage, injury or death associated with such unintended or unauthorized use.

Vishay Semiconductor GmbH, P.O.B. 3535, D-74025 Heilbronn, Germany



Notice

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay:](#)

[BYT43K-TR](#)