

# HSL-TB32-MD

## 32-CH Separate I/O Terminal Base



### Specifications

|                     |                                                            |
|---------------------|------------------------------------------------------------|
| General Description | Separate I/O wiring connection for HSL I/O modules         |
|                     | Every I/O points uses 3-pin connector                      |
|                     | Pin definition is signal/ground/power (from left to right) |
|                     | Separate fuse protection for each I/O points               |
|                     | (jumper selection)                                         |
|                     | Supports common/separate DC power supply                   |
|                     | (jumper selection)                                         |
|                     | Terminator resistor on board (jumper selection)            |
|                     | Interlocking design for rugged installation                |
|                     | Power LED indicator                                        |
| I/O Wire Gauge      | 20 AWG. (max.); 28 AWG. (min.)                             |
|                     | 22 V to 26 V <sub>DC</sub>                                 |
|                     | 129 x 107 x 47.5 mm (W x L x H)                            |


|                |                                 |
|----------------|---------------------------------|
| I/O Wire Gauge | 20 AWG. (max.); 28 AWG. (min.)  |
| Power Supply   | 22 V to 26 V <sub>DC</sub>      |
| Dimensions     | 129 x 107 x 47.5 mm (W x L x H) |

### Support Modules

- HSL-DI16DO16-M-NN
- HSL-DI32-M-N
- HSL-DO32-M-N

# HSL-TB32-M-DIN

## 32-CH I/O Terminal Base



### Specifications

|                     |                                                   |
|---------------------|---------------------------------------------------|
| General Description | Field I/O wiring connection for HSL I/O modules   |
|                     | Spring terminal for easy field wiring             |
|                     | Power and ground included for each signal channel |
|                     | Interlocking design for rugged installation       |
|                     | Power LED indicator                               |
|                     | DIN rail mounting                                 |
|                     | Terminator resistor on board                      |
|                     | 20 AWG. (max.); 28 AWG. (min.)                    |
|                     | 22 V to 26 V <sub>DC</sub>                        |
|                     | 128.5 x 85.5 x 108 mm (W x L x H)                 |


|                |                                   |
|----------------|-----------------------------------|
| I/O Wire Gauge | 20 AWG. (max.); 28 AWG. (min.)    |
| Power supply   | 22 V to 26 V <sub>DC</sub>        |
| Dimensions     | 128.5 x 85.5 x 108 mm (W x L x H) |

### Support Modules

- HSL-DI16DO16-M-NN
- HSL-DI32-M-N
- HSL-DO32-M-N
- HSL-R8DI16-M-N
- HSL-AI16AO2-M-VV-AV

# HSL-TB32-U-DIN

## 32 Points Universal Terminal Base



### Specifications

|                     |                                                   |
|---------------------|---------------------------------------------------|
| General Description | Field I/O wiring connection for HSL I/O modules   |
|                     | Spring terminal for easy field wiring             |
|                     | Power and ground included for each signal channel |
|                     | Interlocking design for rugged installation       |
|                     | Power LED indicator                               |
|                     | DIN rail mounting                                 |
|                     | Terminator resistor on board                      |
|                     | 20 AWG. (max.); 28 AWG. (min.)                    |
|                     | 22 V to 26 V <sub>DC</sub>                        |
|                     | 126 x 120.1 x 107.3 mm (W x L x H)                |

|                |                                    |
|----------------|------------------------------------|
| I/O Wire Gauge | 20 AWG. (max.); 28 AWG. (min.)     |
| Power Supply   | 22 V to 26 V <sub>DC</sub>         |
| Dimensions     | 126 x 120.1 x 107.3 mm (W x L x H) |

### Support Modules

- HSL-DI16DO16-DB-NN
- HSL-DI32-DB-N
- HSL-DO32-DB-N

# HSL-TB64

## 64 Points High Density Terminal Base



### Specifications

|                     |                                                   |
|---------------------|---------------------------------------------------|
| General Description | Field I/O wiring connection for HSL I/O modules   |
|                     | Spring terminal for easy field wiring             |
|                     | Power and ground included for each signal channel |
|                     | Interlocking design for rugged installation       |
|                     | Power LED indicator                               |
|                     | DIN rail mounting                                 |
|                     | Terminator resistor on board                      |
|                     | 20 AWG. (max.); 28 AWG. (min.)                    |
|                     | 22 V to 26 V <sub>DC</sub>                        |
|                     | 168.7 x 120.1 x 107.1 mm (W x L x H)              |

|                |                                      |
|----------------|--------------------------------------|
| I/O Wire Gauge | 20 AWG. (max.); 28 AWG. (min.)       |
| Power Supply   | 22 V to 26 V <sub>DC</sub>           |
| Dimensions     | 168.7 x 120.1 x 107.1 mm (W x L x H) |

### Support Modules

- HSL-DI16DO16-DB-NN
- HSL-DI32-DB-N
- HSL-DO32-DB-N

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ADLINK Technology:](#)

[HSL-TB64-DIN](#)