



Product: [2424](#)

CAT6+ Horizontal, 4pr, UTP, LSZH Jkt

Product Description

CAT6+ (350MHz), 4-Pair, U/UTP-unshielded, Zero Halogen, Premise Horizontal cable, 23 AWG solid bare copper conductors, polyolefin insulation, patented tape separator, ripcord, LSZH jacket.

Technical Specifications

Product Overview

Suitable Applications:	Premise Horizontal Cable, POE, POE+, Gigabit Ethernet, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM, NTSC/PAL Component or Composite Video, AES/EBU, Digital Video, RS-422
------------------------	---

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
23	Solid	BC - Bare Copper	4

Conductor Count:	8
Total Number of Pairs:	4

Insulation

Material	
PO - Polyolefin	
Bonded-Pair:	N/A

Color Chart

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

Outer Jacket Material

Material	Material Trade Name	Nominal Diameter	Ripcord	Separator Material
LSZH - Low Smoke Zero Halogen (Flame Retardant)	Haloarrest®	0.221 in	Yes	Dielectric Tape (Patented)

Electrical Characteristics

Conductor DCR

Max. Conductor DCR	Max. DCR Unbalance
78 Ohm/km	3 %

Capacitance

Max. Capacitance Unbalance	Nom. Mutual Capacitance
330 pF/100m	17 pF/ft

Delay

Frequency [MHz]	Max. Delay	Max. Delay Skew
100 MHz	537.6 ns/100m	35 ns/100m

High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted)	Max./Min. Fitted Impedance
1 MHz	2.0 dB/100m	79.3 dB	77.3 dB	77.3 dB	75.3 dB	70.8 dB	67.8 dB	20.0 dB	100 ± 15	102 ± 15
4 MHz	3.7 dB/100m	70.3 dB	68.3 dB	66.5 dB	64.5 dB	58.8 dB	55.8 dB	23.6 dB	100 ± 15	100 ± 15
8 MHz	5.3 dB/100m	65.8 dB	63.8 dB	60.5 dB	58.5 dB	52.7 dB	49.7 dB	25.3 dB	100 ± 15	100 ± 15
10 MHz	5.9 dB/100m	64.3 dB	62.3 dB	58.4 dB	56.4 dB	50.8 dB	47.8 dB	26.0 dB	100 ± 15	100 ± 15
16 MHz	7.4 dB/100m	61.2 dB	59.2 dB	53.8 dB	51.8 dB	46.7 dB	43.7 dB	26.0 dB	100 ± 15	100 ± 15
20 MHz	8.3 dB/100m	59.8 dB	57.8 dB	51.4 dB	49.4 dB	44.8 dB	41.8 dB	26.0 dB	100 ± 15	100 ± 15
25 MHz	9.4 dB/100m	58.3 dB	56.3 dB	49.0 dB	47.0 dB	42.8 dB	39.8 dB	25.5 dB	100 ± 15	100 ± 15
31.25 MHz	10.5 dB/100m	56.9 dB	54.9 dB	46.4 dB	44.4 dB	40.9 dB	37.9 dB	25.0 dB	100 ± 15	100 ± 15
62.5 MHz	15.1 dB/100m	52.4 dB	50.4 dB	37.3 dB	35.3 dB	34.9 dB	31.9 dB	23.5 dB	100 ± 15	100 ± 15
100 MHz	19.3 dB/100m	49.3 dB	47.3 dB	30.0 dB	28.0 dB	30.8 dB	27.8 dB	22.5 dB	100 ± 15	100 ± 15
155 MHz	24.5 dB/100m	46.4 dB	44.4 dB	21.9 dB	19.9 dB	27.0 dB	24.0 dB	21.6 dB	100 ± 22	100 ± 15
200 MHz	28.2 dB/100m	44.8 dB	42.8 dB	16.6 dB	14.6 dB	24.8 dB	21.8 dB	21.0 dB	100 ± 22	100 ± 15
250 MHz	31.8 dB/100m	43.3 dB	41.3 dB	11.5 dB	9.5 dB	22.8 dB	19.8 dB	20.5 dB	100 ± 32	100 ± 15
300 MHz	35.2 dB/100m	42.1 dB	40.1 dB	6.9 dB	4.9 dB	21.3 dB	18.3 dB	20.1 dB	100 ± 32	100 ± 15
350 MHz	38.4 dB/100m	41.1 dB	39.1 dB	2.7 dB	0.7 dB	19.9 dB	16.9 dB	19.8 dB	100 ± 32	100 ± 15
400 MHz	41.5 dB/100m	40.3 dB	38.3 dB			18.8 dB	15.8 dB	19.5 dB	100 ± 32	100 ± 15
450 MHz	44.3 dB/100m	39.5 dB	37.5 dB			17.7 dB	14.7 dB	19.2 dB	100 ± 32	100 ± 15
500 MHz	47.1 dB/100m	38.8 dB	36.8 dB			16.8 dB	13.8 dB	19.0 dB	100 ± 32	100 ± 15
550 MHz	49.7 dB/100m	38.2 dB	36.2 dB			16.0 dB	13.0 dB	18.8 dB	100 ± 32	100 ± 15

Segregation class according EN50174-2:

a

Voltage

UL Voltage Rating

300 V RMS

Temperature Range

Installation Temp Range:	+5°C To +50°C
Non-UL Temp Rating:	+75°C
Storage Temp Range:	-20°C To +75°C
Operating Temp Range:	-20°C To +75°C

Mechanical Characteristics

Bulk Cable Weight:	23 lbs/1000ft
Max. Pull Tension:	25 lbs
Min Bend Radius During Installation:	2.25 in
Min Bend Radius/Minor Axis:	1.0 in

Standards

NEC/(UL) Compliance:	N/A
IEC Compliance:	11801 ed 2.2 (2011) Class E
CPR Euroclass:	Eca
Data Category:	Category 6
ANSI Compliance:	S-116-732-2013 Category 6, ANSI/NEMA WC-66 Category 6
TIA/EIA Compliance:	ANSI/TIA-568-C.2 Category 6
IEEE Compliance:	IEEE 802.3bt Type 1, Type 2, Type 3, Type 4
Third Party Performance Verification:	Category 6

Applicable Environmental and Other Programs

Environmental Space:	LSZH
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes

EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	Yes
EU CE Mark:	No
EU REACH SVHC Compliance (yyyy-mm-dd):	2017-07-10
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Aerial:	No
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Non-Halogenated:	Yes
Suitability - Oil Resistance:	No
Suitability - Outdoor:	No
Suitability - Sunlight Resistance:	No

Flammability, LSOH, Toxicity Testing

IEC Flammability:	IEC 60332-1-2
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	2413

Part Number

Variants

Item #	Color	Putup Type	Length	UPC/EAN
2424.06305	Blue	Reel	305 m	8719605005038
2424 0061000	Blue	Reel	1,000 ft	612825061557
2424.08305	Gray	Reel	305 m	8719605005069
2424.07305	Purple	Reel	305 m	8719605005052
2424 0071000	Purple	Reel	1,000 ft	612825061540
2424.071000	Purple	Reel	1,000 m	8719605005045
2424.02500	Red	Reel	500 m	8719605005021
2424 0091000	White	Reel	1,000 ft	612825061564

Product Notes

Notes:	Electrical values are expected performance based on cable testing and representative performance within a typical Belden system. Values above 350 MHz are for Engineering Information Only. Print Includes Descending Footage/Meter Markings from Max. Put-Up Length to 0.
--------	--

History

Update and Revision:	Revision Number: 0.354 Revision Date: 09-25-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[2424 0061000](#) [2424 0071000](#) [2424 0091000](#)