



**Product:** [9222](#)

50Ω Triax RG-58A/U Type, #20, PO, TC Braids, PVC Jkt

### Product Description

50 Ohm Triax RG-58A/U Type, 20 AWG stranded (7x28) .037" tinned copper conductor, polyethylene insulation, double tinned copper braid shields (95% coverage), PVC jacket.

### Technical Specifications

#### Physical Characteristics (Overall)

##### Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
20	7x28	TC - Tinned Copper	0.038 in	1

Conductor Count:	1
------------------	---

##### Insulation

Material	Nominal Diameter
PE - Polyethylene	0.12 in

##### Inner Shield Material

Type	Layer	Material	Coverage [%]
Braid	1	Tinned Copper (TC)	95%

##### Inner Jacket Material

Material	Nominal Diameter
PE - Polyethylene	0.177 in

##### Outer Shield Material

Type	Layer	Material	Coverage [%]
Braid	1	Tinned Copper (TC)	95%

##### Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.241 in	0.021 in
	0.216 in	

#### Electrical Characteristics

##### Conductor DCR

Nominal Conductor DCR	Nominal Inner Shield DCR	Nominal Outer Shield DCR
9.5 Ohm/1000ft	4.7 Ohm/1000ft	4.3 Ohm/1000ft

##### Capacitance

Nom. Capacitance Conductor to Shield
30.8 pF/ft

##### Inductance

Nominal Inductance
0.077 μH/ft

## Impedance

### Nominal Characteristic Impedance

50 Ohm

## High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
1 MHz	0.5 dB/100ft
10 MHz	1.5 dB/100ft
50 MHz	3.3 dB/100ft
100 MHz	4.9 dB/100ft
200 MHz	7.2 dB/100ft
400 MHz	12 dB/100ft
500 MHz	14 dB/100ft
700 MHz	18 dB/100ft
900 MHz	22 dB/100ft
1000 MHz	24 dB/100ft

## Delay

### Max. Delay Skew

66 ns/100m

## Voltage

### Non-UL Voltage Rating

1400 V RMS

## Temperature Range

Non-UL Temp Rating:	75°C
Operating Temp Range:	-40°C To +75°C

## Mechanical Characteristics

Bulk Cable Weight:	39 lbs/1000ft
Max. Pull Tension:	83 lbs
Min Bend Radius/Minor Axis:	2.5 in

## Standards

CPR Euroclass:	Fca
RG Type:	58A/U Type

## Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
MII Order #39 (China RoHS):	Yes

## Suitability

Suitability - Indoor:	Yes
-----------------------	-----

## Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

## Part Number

## Variants

Item #	Color	Putup Type	Length	UPC
9222 004100	Yellow	Reel	100 ft	612825225430
9222 004500	Yellow	Reel	500 ft	612825225447

9222 004U500	Yellow	UnReel	500 ft	612825225423
--------------	--------	--------	--------	--------------

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

## History

Update and Revision:	Revision Number: 0.267 Revision Date: 08-25-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[9222 004100](#) [9222 004500](#) [9222 004U500](#)