



**Product:** [1049A](#)

Inst, 4 Pr #18 Str BC, PVC-NYL Ins E1, IS/OS, Blk PVC Jkt, 600V TC-ER  
150V NPLF 90C Dry/Wet

[Request Sample](#)

### Product Description

UL Instrumentation, 4 Pair 18AWG (7x26) Bare Copper, PVC-NYL Insulation E1 Color Code, Individual & Overall Beldfoil® Shield, Black PVC Outer Jacket, 600V TC-ER 150V NPLF 90C Dry/Wet SUN RES DIR BUR

### Technical Specifications

#### Product Overview

Suitable Applications:	Industrial Control, Raceways Cable trays and ducts, Digital Control, Instruments (4-20ma, 0-10v, ...), low voltage digital control (24v, ...), encoders, control circuits, distributed control system (DCS), programmable logic controller (PLC), Solenoids, Valves, Actuators, Positioners
------------------------	---

#### Construction Details

##### Conductor

Element	No. of Elements	Size	Stranding	Material
Pair(s)	4	18 AWG	7x26	BC - Bare Copper

##### Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	PVC/Nylon - Polyvinyl Chloride + Nylon	0.022 in (0.56 mm)	0.088 in (2.2 mm)	ICEA Chart E1

##### Inner Shield

Element	Shield Type	Material	Coverage	Drainwire Type	Notes
Pair(s)	Tape	Bi-Laminate (Alum+Poly)	100%	20 AWG (7x28) TC	each pair, extra polyester tape for isolation

##### Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	18 AWG (7x26) TC

##### Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.047 in (1.2 mm)	0.493 in (12.5 mm)	Yes

Overall Cable Diameter (Nominal):	0.493 in (12.5 mm)
-----------------------------------	--------------------

#### Electrical Characteristics

##### Electricals

Element	Nom. Conductor DCR	Nom. Inner Shield DCR	Max. Current
Pair(s)	6.66 Ohm/1000ft	8.48 Ohm/1000ft (27.8 Ohm/km)	10 Amps per conductor @ 30°C

##### Voltage

<b>UL Voltage Rating</b>
600 V (TC-ER), 150 V (NPLF)

#### Mechanical Characteristics

##### Temperature

<b>UL Temperature</b>	<b>Operating</b>
-----------------------	------------------

90°C Dry, 90°C Wet -30°C to 90°C Dry/Wet

#### Bend Radius

Stationary Min.	Installation Min.
5.9 in (150 mm)	5.9 in (150 mm)

Max. Pull Tension:	214 lbs (97.1 kg)
Bulk Cable Weight:	122 lbs/1000ft

#### Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Indoor, Outdoor, Sunlight Resistance, Burial
Flammability / Reaction to Fire:	UL 1685 FT4 Loading, FT4, IEEE 1202 FT4
NEC / UL Compliance:	Article 336, Article 760, NPLF, TC-ER
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

#### History

Update and Revision:	Revision Number: 0.622 Revision Date: 01-04-2024
----------------------	--

#### Part Numbers

##### Variants

Item #	Color	Putup Type	Length	UPC	Footnote
1049A 0107500	Black	Reel	7,500 ft	612825105374	C Z

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[1049A 0107500](#)