


## 49725A Molded Cable Assemblies - D-Subminiature Assembly



For more Information  
please call

1-800-Belden1



### General Description:

15 position shielded D-Sub, for any 15-pin application exposed to high-noise environment, S-R PVC insulation, foil shield (general purpose), PVC jacket.

### Physical Characteristics (Overall)

#### Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material	Dia. (in.)
15	24	7x32	TC - Tinned Copper	.024

Total Number of Conductors: 15

Number of Pins: 15

#### Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)
S-R PVC - Semi-Rigid Polyvinyl Chloride	0.01

#### Connector Characteristics

Connector Characteristics - First End # of Connector Contacts/positions: 15

Connector Characteristics - First End Connector Gender: Male

Connector Characteristics - First End Connector Shielding Type: Metal Backshell

Connector Characteristics - First End Connector Type: D-Sub

Connector Characteristics - First End Overmold Color: Chrome

Connector Characteristics - First End Overmold Compound Material: PVC

Connector Characteristics - First End Overmold Type: 15 Position D-Sub

Connector Characteristics - First End Retention Hardware: Thumbscrew

Connector Characteristics - Second End # of Connector Contacts/positions: 15

Connector Characteristics - Second End Connector Gender: Female

Connector Characteristics - Second End Connector Shielding Type: Metal Backshell

Connector Characteristics - Second End Connector Type: D-Sub

Connector Characteristics - Second End Overmold Color: Chrome

Connector Characteristics - Second End Overmold Compound Material: PVC

Connector Characteristics - Second End Overmold Type: 15 Position D-Sub

Connector Characteristics - Second End Retention Hardware: Thumbscrew

#### Outer Shield

Outer Shield Material:

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
24	7x32	TC - Tinned Copper

#### Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	0.032

## 49725A Molded Cable Assemblies - D-Subminiature Assembly

### Overall Cable

Overall Nominal Diameter: 0.284 in.

### Assembly Dimensional

Assembly Dimensional Length: 5

### Wiring

Wiring: Point to Point. Pin #1 on end 1 to Pin #1 on end 2, Pin #2 to Pin #2, etc. Cable shield connected to connector shell.

### Mechanical Characteristics (Overall)

UL Temperature Rating: 80°C (UL AWM Style 2464)

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CM (cable only)
AWM Specification:	UL Style 2464 (300 V 80°C) (cable only)
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

#### Plenum/Non-Plenum

Plenum (Y/N): No

### Electrical Characteristics (Overall)

#### Max. Operating Voltage - UL:

##### Voltage

300 V RMS (UL AWM Style 2464)

### Notes (Overall)

**Notes:** Molded handles are 100% shielded to assist in FCC compliance and guard against EMI/RFI. All connectors tin-plated and male connectors have detents for positive ground connection. Wiring is point-to-point with the shield to connector shell.

**Notes (Cont'd.):** Jack screw retention on both connectors.

### Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
49725A 060S2	1 EA	0.500 LB	CHROME		15 POS SHD D-SUB 9541

Revision Number: 1 Revision Date: 09-19-2008

© 2017 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[49725A 060S2](#)