






REV.	DESCRIPTION	DATE	APPROVED
A	Engineering Release	05/12/17	J. C.

*Length "X.X"	Tolerance
2.0" ~ 16.0"	±0.05"
16.1" ~ 40.0"	±0.15"
40.1" ~ 80.0"	±0.30"
80.1" ~ 500.0"	±0.5%



Part Number Configuration
OR2-6.5-UR-F6PX67PR

Lens Options:
Z – Clear Fresnel
D – Diffused
LED Color, See Page 2
Length in 0.1" Increments Only



NOTES:

1. SEALED TO IP67 RATING
2. ROHS COMPLIANT
3. MOUNTING HARDWARE AND ADAPTER SHIPPED NON-ASSEMBLED
4. MINIMUM BEND RADIUS OF FLEXIBLE LIGHT PIPE: 0.87" [22mm]

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED)		BIVAR®	
DECIMALS	ANGULAR	4 THOMAS, IRVINE, CA. 92618	
.X ± .1	X° ± 1°	TEL.: (949) 951-8808 FAX: (949) 951-3974	
.XX ± .02		TITLE: IP67 RATED PANEL MOUNT	
.XXX ± .010		FLP INDICATOR, ORCA	
DESIGNED: TD. Nguyen	DATE: 04/30/17	PART NO: OR2-X.X-XXX-F6PX67PR	REVISION: A
CHECKED: K. Baron	DATE: 04/30/17	CAGE CODE : 32559	SHEET # 1 OF 2
CAD GENERATED DOCUMENT. DO NOT MEASURE DRAWING.			

REV.	DESCRIPTION	DATE	APPROVED
	SEE SHEET #1		

Assy P/N	Emitted Color	Dominant Wavelength λd (nm) / CCT (K)	Absolute Max. Ratings			LED Electro-Optical Data					LED P/N	Polarity Diagram
			Pd (mW)	If (mA)	Peak If (mA)	Vf (V)			LED Iv (mcd)			
		MIN				TYP	MAX	MIN	TYP			
SINGLE COLOR LED ASSEMBLIES (20mA)												
OR2-X.X-BLU-F6PX67PR	BLUE	465 - 475	220	50	100	2.7	3.2	3.6	5000	8000	R20BLU-4-0045	FIG. A
OR2-X.X-GRN-F6PX67PR	GREEN	517 - 527	220	50	100	2.7	3.2	3.6	15000	25000	R20GRN-4-0045	FIG. A
OR2-X.X-WHT-F6PX67PR	WHITE	6000K	220	50	100	2.7	3.2	3.6	10000	16000	R20WHT-4-0045	FIG. A
SINGLE COLOR LED ASSEMBLIES (50mA)												
OR2-X.X-RED-F6PX67PR	RED	620 - 635	140	80	160	1.8	2.4	2.6	12000	18000	R50RED-4-0045	FIG. A
OR2-X.X-YLW-F6PX67PR	YELLOW	588 - 596	140	80	160	1.8	2.4	2.6	12000	18000	R50YLW-4-0045	FIG. A
BI-COLOR & TRI-COLOR LED ASSEMBLIES (50mA)												
OR2-X.X-RG-F6PX67PR	RED	617 - 630	150	80	160	1.8	2.4	2.6	3000	4000	R50RG2-4-0045	FIG. B
	GREEN	515 - 525	220	80	150	3.0	3.4	3.8	6000	10000		
OR2-X.X-RB-F6PX67PR	RED	617 - 630	150	80	160	1.8	2.4	2.6	3000	4000	R50RB2-4-0045	FIG. C
	BLUE	460 - 470	220	80	150	3.0	3.4	3.8	1000	3000		
OR2-X.X-BG-F6PX67PR	BLUE	460 - 470	220	80	150	3.0	3.4	3.8	1000	3000	R50BG2-4-0045	FIG. D
	GREEN	515 - 525	220	80	150	3.0	3.4	3.8	6000	10000		
OR2-X.X-RGB-F6PX67PR	RED	617 - 630	150	80	160	1.8	2.4	2.6	3000	4000	R50RGB-4-0045	FIG. E
	GREEN	515 - 525	220	80	150	3.0	3.4	3.8	6000	10000		
	BLUE	460 - 470	220	80	150	3.0	3.4	3.8	1000	3000		




FIG. A




FIG. B




FIG. C




FIG. D




FIG. E

ABSOLUTE MAXIMUM RATINGS (Ta=25°C)

REVERSE VOLTAGE	5V
REVERSE CURRENT	10μA
OPERATING TEMPERATURE RANGE	-25°C ~ +80°C
STORAGE TEMPERATURE	-30°C ~ +80°C
LEAD SOLDERING TEMPERATURE(1/16" FROM BODY)	260°C FOR 5 SECONDS

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED) <u>DECIMALS</u> <u>ANGULAR</u>		 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974	
		TITLE: IP67 RATED PANEL MOUNT FLP INDICATOR, ORCA	
DESIGNED: TD. Nguyen	DATE: 04/30/17	PART NO: OR2-X.X-XXX-F6PX67PR	REVISION: A
CHECKED: K. Baron	DATE: 04/30/17	CAGE CODE : 32559	SHEET # 2 OF 2
CAD GENERATED DOCUMENT. DO NOT MEASURE DRAWING			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

BIVAR:

[OR2-6.0-RGB-F6PZ67PR-9](#) [OR2-6.0-RG-F6PD67PR-2](#) [OR2-6.0-RG-F6PD67PR-6](#) [OR2-6.0-RG-F6PD67PR-9](#) [OR2-6.0-RG-F6PZ67PR-2](#) [OR2-6.0-RG-F6PZ67PR-4](#) [OR2-6.0-RG-F6PZ67PR-5](#) [OR2-6.0-RG-F6PZ67PR-6](#) [OR2-6.0-RG-F6PZ67PR-9](#) [OR2-6.0-WHT-F6PD67PR-2](#) [OR2-6.0-WHT-F6PD67PR-4](#) [OR2-6.0-WHT-F6PD67PR-5](#) [OR2-6.0-WHT-F6PD67PR-6](#) [OR2-6.0-WHT-F6PD67PR-9](#) [OR2-6.0-WHT-F6PZ67PR-2](#) [OR2-6.0-WHT-F6PZ67PR-4](#) [OR2-6.0-WHT-F6PZ67PR-5](#) [OR2-6.0-WHT-F6PZ67PR-6](#) [OR2-6.0-WHT-F6PZ67PR-9](#) [OR2-6.0-YLW-F6PD67PR-2](#) [OR2-6.0-YLW-F6PD67PR-4](#) [OR2-6.0-YLW-F6PD67PR-5](#) [OR2-6.0-YLW-F6PD67PR-6](#) [OR2-6.0-YLW-F6PD67PR-9](#) [OR2-6.0-YLW-F6PZ67PR-2](#) [OR2-6.0-YLW-F6PZ67PR-4](#) [OR2-6.0-YLW-F6PZ67PR-5](#) [OR2-6.0-YLW-F6PZ67PR-6](#) [OR2-6.0-YLW-F6PZ67PR-9](#) [OR2-6.0-BG-F6PD67PR-2](#) [OR2-6.0-BG-F6PD67PR-4](#) [OR2-6.0-BG-F6PD67PR-5](#) [OR2-6.0-BG-F6PD67PR-6](#) [OR2-6.0-BG-F6PD67PR-9](#) [OR2-6.0-BG-F6PZ67PR-2](#) [OR2-6.0-BG-F6PZ67PR-4](#) [OR2-6.0-BG-F6PZ67PR-5](#) [OR2-6.0-BG-F6PZ67PR-6](#) [OR2-6.0-BG-F6PZ67PR-9](#) [OR2-6.0-BLU-F6PD67PR-2](#) [OR2-6.0-BLU-F6PD67PR-4](#) [OR2-6.0-BLU-F6PD67PR-5](#) [OR2-6.0-BLU-F6PD67PR-6](#) [OR2-6.0-BLU-F6PD67PR-9](#) [OR2-6.0-BLU-F6PZ67PR-2](#) [OR2-6.0-BLU-F6PZ67PR-4](#) [OR2-6.0-BLU-F6PZ67PR-5](#) [OR2-6.0-BLU-F6PZ67PR-6](#) [OR2-6.0-BLU-F6PZ67PR-9](#) [OR2-6.0-GRN-F6PD67PR-2](#) [OR2-6.0-GRN-F6PD67PR-4](#) [OR2-6.0-GRN-F6PD67PR-5](#) [OR2-6.0-GRN-F6PD67PR-6](#) [OR2-6.0-GRN-F6PD67PR-9](#) [OR2-6.0-GRN-F6PZ67PR-2](#) [OR2-6.0-GRN-F6PZ67PR-4](#) [OR2-6.0-GRN-F6PZ67PR-5](#) [OR2-6.0-GRN-F6PZ67PR-6](#) [OR2-6.0-GRN-F6PZ67PR-9](#) [OR2-6.0-RB-F6PD67PR-2](#) [OR2-6.0-RB-F6PD67PR-4](#) [OR2-6.0-RB-F6PD67PR-5](#) [OR2-6.0-RB-F6PD67PR-6](#) [OR2-6.0-RB-F6PD67PR-9](#) [OR2-6.0-RB-F6PZ67PR-2](#) [OR2-6.0-RB-F6PZ67PR-4](#) [OR2-6.0-RB-F6PZ67PR-5](#) [OR2-6.0-RB-F6PZ67PR-6](#) [OR2-6.0-RB-F6PZ67PR-9](#) [OR2-6.0-RED-F6PD67PR-2](#) [OR2-6.0-RED-F6PD67PR-4](#) [OR2-6.0-RED-F6PD67PR-5](#) [OR2-6.0-RED-F6PD67PR-6](#) [OR2-6.0-RED-F6PD67PR-9](#) [OR2-6.0-RED-F6PZ67PR-2](#) [OR2-6.0-RED-F6PZ67PR-4](#) [OR2-6.0-RED-F6PZ67PR-5](#) [OR2-6.0-RED-F6PZ67PR-6](#) [OR2-6.0-RED-F6PZ67PR-9](#) [OR2-6.0-RGB-F6PD67PR-2](#) [OR2-6.0-RGB-F6PD67PR-4](#) [OR2-6.0-RGB-F6PD67PR-5](#) [OR2-6.0-RGB-F6PD67PR-6](#) [OR2-6.0-RGB-F6PD67PR-9](#) [OR2-6.0-RGB-F6PZ67PR-2](#) [OR2-6.0-RGB-F6PZ67PR-4](#) [OR2-6.0-RGB-F6PZ67PR-5](#) [OR2-6.0-RGB-F6PZ67PR-6](#) [OR2-6.0-RG-F6PD67PR-4](#) [OR2-6.0-RG-F6PD67PR-5](#)