


REV.	DESCRIPTION	DATE	APPROVED
A	Engineering Update w/o Changes	02/24/04	M. C.
B	Typo Correction	10/28/08	T. Y.



SERIES	SCREW SIZE	I.D.	O.D.	- XXX	H
9913	#2	.091(2.3mm)	.187(4.7mm)	-062	1/16 (1.6mm)
				-125	1/8 (3.2mm)
9910	#2	.091(2.3mm)	.250(6.4mm)	-187	3/16 (4.8mm)
				-250	1/4 (6.4mm)
9908	#4	.125(3.2mm)	.187(4.7mm)	-312	5/16 (7.9mm)
				-375	3/8 (9.5mm)
				-437	7/16 (11.1mm)
9911	#4	.125(3.2mm)	.250(6.4mm)	-500	1/2 (12.7mm)
				-562	9/16 (14.3mm)
9905	#6	.147(3.7mm)	.250(6.4mm)	-625	5/8 (15.9mm)
				-750	3/4 (19.1mm)
				-812	13/16 (20.6mm)
9912	#8	.171(4.3mm)	.250(6.4mm)	-875	7/8 (22.2mm)
				-937	15/16 (23.8mm)
				-1000	1.0 (25.4mm)

3. TOLERANCE "H" DIMENSION:

$H \leq 0.500$ (12.7mm) ± 0.005 (0.1mm)

$H > 0.500$ (12.7mm) ± 0.010 (0.3mm)

2. MATERIAL: NYLON 6, ULTRAMID 8270 HS, NATURAL. BIVAR MATERIAL CODE 01-NL-WE.

ALLIED CHEMICAL POLYAMID NYLON 6 WITH CLARIANT CNY02655 WHITE NYLON CONCENTRATE..

1. GENERAL SPECIFICATIONS: BIVAR EXTRUDED PRODUCT SPECIFICATION BV00-E103.

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED)		 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974	
DECIMALS	ANGULAR		
.X $\pm .1$	X° $\pm 1^\circ$		
.XX $\pm .01$			
.XXX $\pm .005$			
DESIGNED: Ty Yin	DATE: 02/24/04	TITLE: NYLON TUBE SPACERS	
CHECKED: D. Green	DATE: 02/24/04	PART NO: 99XX-XXX	REVISION: B
		CAGE CODE : 32559	SHEET # 1 OF 1
CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING.			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

BIVAR:

[9910-500](#) [9910-312](#) [9910-062](#) [9910-1.000](#) [9910-10MM](#) [9910-11MM](#) [9910-125](#) [9910-12MM](#) [9910-13MM](#) [9910-14MM](#) [9910-15MM](#) [9910-16MM](#) [9910-17MM](#) [9910-187](#) [9910-18MM](#) [9910-19MM](#) [9910-1MM](#) [9910-20MM](#) [9910-250](#) [9910-2MM](#) [9910-375](#) [9910-3MM](#) [9910-437](#) [9910-4MM](#) [9910-562](#) [9910-5MM](#) [9910-625](#) [9910-687](#) [9910-6MM](#) [9910-750](#) [9910-7MM](#) [9910-812](#) [9910-875](#) [9910-8MM](#) [9910-937](#) [9910-9MM](#)