



**Product:** [FS3C004N0](#) 

Outdoor Central Loose Tube OM3 4 Fibers

### Product Description

FX Outdoor Central Loose Tube OM3 4 Fibers OSP Non-Unitized Black

### Technical Specifications

|                    |                    |
|--------------------|--------------------|
| Part Number:       | FS3C004N0          |
| Construction Type: | Central Loose Tube |

### Product Overview

|                        |         |
|------------------------|---------|
| Environmental Space:   | Outdoor |
| Suitable Applications: | Outdoor |

### Construction

#### Fiber Cable Construction

| Fiber Type | Fiber Count |
|------------|-------------|
| OM3        | 4           |

|                     |                            |
|---------------------|----------------------------|
| Fiber Color Coding: | Blue, Orange, Green, Brown |
|---------------------|----------------------------|

#### Buffer Specification

| Buffer Diameter |
|-----------------|
| 0.150           |

|                            |            |
|----------------------------|------------|
| Cable Core Water Blocking: | Gel-Filled |
|----------------------------|------------|

### SubUnit Specifications

|                            |                   |
|----------------------------|-------------------|
| Number of Active Subunits: | Non-Unitized      |
| SubUnit Diameter:          | 0.150 in (3.8 mm) |

### Physical Specifications

|                            |            |
|----------------------------|------------|
| Buffer Tube Waterblocking: | Gel Filled |
|----------------------------|------------|

### Jacket Specifications

|                    |               |
|--------------------|---------------|
| Number of Jackets: | Single Jacket |
|--------------------|---------------|

#### Outer Jacket Material

| Material          | Nominal Diameter  |
|-------------------|-------------------|
| PE - Polyethylene | 0.315 in (8.0 mm) |

|                                  |       |
|----------------------------------|-------|
| Outer Jacket Color:              | Black |
| Number of Outer Jacket Ripcords: | 1     |

### Optical Characteristics

|                                  |                          |
|----------------------------------|--------------------------|
| Effective Modal Bandwidth (EMB): | 2000 MHz-km / 500 MHz-km |
| Fiber Core Diameter:             | 50/125µm                 |
| Max Attenuation at 1300 nm:      | 1.0 dB/km                |
| Max Attenuation at 850 nm:       | 3.0 dB/km                |
| Wavelength:                      | 850 nm / 1300 nm         |

|  |                          |
|--|--------------------------|
| 10 Gigabit Ethernet Performance:       | 300 m / 300 m            |
| 1 Gigabit Ethernet Performance:        | - / 550 m                |
| Min Overfilled Launch (OFL) Bandwidth: | 1500 MHz-km / 500 MHz-km |

## Mechanical Characteristics

### Mechanical Tests

| Description   | Requirement/Value |
|---|-------------------|
| Cable Min. Bend Radius Installation (Short Term)      | 20x Cable OD      |
| Cable Min. Bend Radius Operation (Long Term)          | 10x Cable OD      |
| Cable Max. Tensile Strength Installation (Short Term) | 135 N (600 lbf)   |
| Cable Max. Tensile Strength Operation (Long Term)     | 45 N (200 lbf)    |

### Temperature Range

|                          |              |
|--------------------------|--------------|
| Operating Temp Range:    | -40C to +70C |
| Installation Temp Range: | -20C to +70C |
| Storage Temp Range:      | -40C to +70C |

### Standards

|                               |                    |
|-------------------------------|--------------------|
| UL Rating/Flame Test:         | OSP                |
| NEC/(UL) Specification:       | N/A                |
| Telecommunications Standards: | ANSI/ICEA S-87-640 |
| RoHS:                         | Yes                |
| UV/ Sunlight Protection:      | Yes                |

### History

#### Variants

| Item #    | Color | UPC          |
|-----------|-------|--------------|
| FS3C004N0 | Black | 612825371212 |

|                      |  |
|----------------------|--|
| Update and Revision: | Revision Number: 0.116 Revision Date: 08-22-2019 |
|----------------------|--|

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[FS3C004N0](#)