




## PROFESSIONAL THERMAL MONOCULAR

# FLIR SCION® PTM



Built to equip law enforcement professionals with superior thermal surveillance, the FLIR Scion® PTM packs high-performance thermal imaging into a rugged, IP67-rated handheld monocular. Capable of geotagged video recording and live video transmission, the Scion PTM can instantly stream encrypted thermal footage of any pursuit, evidence recovery, or search and rescue effort to the command center via wireless network. A smooth 60 Hz refresh rate and picture-in-picture zoom capture minute details from a distance and maintain peripheral awareness for constant thermal supervision of suspects, team members, and standbys.

[www.flir.com](http://www.flir.com)



### LIVE ENCRYPTED VIDEO STREAMING

Securely stream real-time thermal video to the command center via networked devices

Link powerful Scion PTM thermal imaging to integrated devices via Wi-Fi and network with other deployed smart sensors on the scene for enhanced, real-time situational awareness and centralized public safety information.



### VERSATILE LENS OPTIONS

Available long-range lenses for the Scion family of thermal monoculars offers a new level of clarity and reach.

High-performance thermal lenses ranging from 14-36 mm offer a choice between quick, close-proximity detection and fine-tuned, long-range surveillance. When the mission demands reliable vision from a distance, premium Scion lenses can detect targets up to 1420 m away. 25 mm and 36 mm Scion optics leverage a manual focus ring to achieve a new level of clarity among FLIR thermal monoculars.



### SUPERIOR THERMAL DETECTION


Sharp, 60 Hz thermal imaging powered by the breakthrough FLIR Boson™ thermal core

FLIR outfits law enforcement professionals with tools to counter unseen threats. Able to perform at any time of day, thermal imaging pierces complete darkness, glaring light, and lingering haze to provide superior awareness in difficult conditions. The advanced image processing of FLIR's Boson thermal core paired with a 60 Hz image refresh rate provide smooth, unwavering vision in challenging environments.

## SPECIFICATIONS

General	Scion PTM166	Scion PTM336	Scion PTM366	Scion PTM466
Core Technology	BOSON 12 $\mu$ m VOx Microbolometer			
Detector Resolution	640 $\times$ 512	320 $\times$ 256	640 $\times$ 512	640 $\times$ 512
Lens System	14 mm	25 mm		36 mm
Field of View (H $\times$ W)	31° $\times$ 24°	9° $\times$ 6.5°	18° $\times$ 13°	12° $\times$ 9°
Optical Magnification	.7x	2.6x	1.3x	2.0x
Digital Zoom	1X   2X   4X   8X	1X   2X   4X	1X   2X   4X   8X	
Refresh Rate	60 Hz			
Video Recording	Yes			
Focus	$\infty$	Manual		
Eye Relief	16 mm			
Display	Quad-VGA (1280x960) High definition display			
Display Focus	Manual			
Features				
Color palettes	White Hot; Black Hot; Iron Bow; Rainbow; Graded Fire; Lava			
Viewing Modes	Scouting, Picture-in-Picture, Lock Span mode			
Picture While Recording (PWR)	Yes			
Media capturing	2 GB Internal storage / Optional micro SD™ card (up to 128 GB)			
GPS	Yes			
Real Time Clock (RTC)	Yes			
Date/Time Stamp	Yes			
Auto Power OFF	Yes			
Magnetic Compass	Yes			
Accelerometer	Yes			
Interfacing				
USB Type	USB-C; Power In; Video Out; Video and Image File Transfer			
Power				
Battery Type / Life	6x CR123A 3V Lithium Battery / Up to 4.5 Hours at 20°C or Rechargeable battery pack / Up to 10 Hours at 20°C			

## DETECTION RANGE PERFORMANCE




Ranges calculated using Johnson criteria (1.8 m man)


Specifications are subject to change without notice. For the most up-to-date specs, go to [www.flir.com](http://www.flir.com)

Scion PTM166		Scion PTM336	Scion PTM366	Scion PTM466
Communications				
Bluetooth™	BLE 4.1+			
Wi-Fi	Video Streaming			
NFC	Yes			
Physical				
Weight	Unit only : 452g With Batteries (6): 565g	Unit only: 567g With Batteries (6): 680g	Unit only: 680g With Batteries (6): 793g	
Size	227 × 76.8 × 60.5 mm (9 × 3 × 2.4 in)	239 × 76.8 × 60.5 mm (9.4 × 3 × 2.4 in)	278 x 77 x 73mm (10.9 x 3.03 x 2.87)	
Environmental rating	IP67 waterproof / 2m drop			
Operating Temperature	-20°C to 50°C			
Storage Temp.	-40°C to 70°C			
Color (Housing)	Black			
Mounting	¼-20 Tripod Mount			
Country of Origin	USA			
Included in Box	SCION, Battery tray, 6xCR123, USB-C cable, Black MOLLE pouch, Quick Start Guide			


100 & 200 series units



300 series units



400 series units



### FLIR SYTEMS, INC.

9 Townsend West,  
Nashua, NH 03063  
Phone: 1-888-959-2259  
or (603) 321-7600  
Fax: 1-888-959-2260

### FLIR PRODUCT REPAIR CENTER

Support: <https://flir.custhelp.com/>  
Register on: [customer.flir.com](http://customer.flir.com)

### ORDER PLACEMENT, RETURN TO STOCK AND INQUIRIES

Email: [Orders@flir.com](mailto:Orders@flir.com)

### PRODUCT REGISTRATION

[flir.com/support](http://flir.com/support)

### TECHNICAL SUPPORT

<http://customer.flir.com>

[www.flir.com](http://www.flir.com)  
NASDAQ: FLIR

Equipment described herein is subject to US export regulations and may require a license prior to export. Diversion contrary to US law is prohibited. Imagery for illustration purposes only. Specifications are subject to change without notice. ©2020 FLIR Systems, Inc. All rights reserved. Updated 09/08/2020

20-0691-PVS - SCION 60HZ PTM



The World's Sixth Sense®

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

FLIR:

[SCION PTM166](#) [SCION PTM336](#) [SCION PTM366](#) [SCION PTM466](#)