

4112-9212 This information is given as an indication. In the continual goal to improve our products, we reserve the right to make any modifications judged necessary



26.5 GHz

SMA

FAILSAFE

TRANSFER

SWITCH

Page
1 / 2

OPTIONS:

R F CHARACTERISTICS

FREQUENCY RANGE

: 0 - 26.5 GHz

IMPEDANCE

: 50 Ohms

FREQUENCY (GHz)	0 - 3	3 - 8	8 -12.4	12.4- 18	18 -26.5
V.S.W.R	<= 1.20	1.30	1.40	1.50	1.70
INSERT. LOSS	<= 0.20 dB	0.30 dB	0.40 dB	0.50 dB	0.70 dB
ISOLATION	>= 80 dB	70 dB	65 dB	60 dB	50 dB
AVER. POWER (*)	240 W	150 W	120 W	100 W	40 W

ELECTRICAL CHARACTERISTICS

ACTUATOR

: FAILSAFE

NOMINAL CURRENT AT 25° C (*10%)

: 140 mA

ACTUATOR VOLTAGE (Vcc)

: 28V (24 to 30V)

TERMINALS

: solder pins (250 Deg.C max./30 sec)

MECHANICAL CHARACTERISTICS

CONNECTORS

: SMA female per MIL C 39012

LIFE

: 2.500.000 cycles

SWITCHING TIME (nominal voltage;25° C)

: < 15 ms

CONSTRUCTION

: splashproof

WEIGHT

: < 85 g

ENVIRONMENTAL CHARACTERISTICS



OPERATING TEMPERATURE RANGE

(°C) : -25 , +70

STORAGE TEMPERATURE RANGE


(°C) : -40 , +85

(* : average power at 25° C)



General tolerance: $\pm 0,5$ mm

Voltage	RF continuity
energized	1↔3 2↔4
De-energized	1↔2 3↔4



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Radial:

R577F13002