



NON-CONTACT VOLTAGE DETECTOR + FLASHLIGHT

FLIR VP40™



The FLIR VP40 is a high-quality non-contact AC voltage detector (NCV) and flashlight that offers high-end features, making it the best value product in its category. The reliable, durable detector includes a bright flashlight, a vibration feedback alarm, and a CAT IV safety rating. Use it to identify live and neutral wires in sockets and junction boxes, and to trace live and neutral wires without contact. The VP40 is the right choice for field-troubleshooting and verification of electrical installations within residential, commercial, and industrial buildings.

www.flir.com/VP40



RUGGED AND RELIABLE

Features a high-quality, durable design for safety and long-term, trouble-free operation

- Detect voltage in the latest safety outlets
- Detect voltage in electrical systems in large industrial facilities and residential low-voltage installations
- Never miss voltage presence with the tactile vibration and LED alarms – even in dark or noisy areas
- Durable to withstand a 3 m drop



EASY TO USE

Offers an ergonomic design that's easy to grip and operate

- Avoid touching live wires with NCV technology
- Reduce risk of dropping the VP40 with double molded slip-resistant grip and an anti-roll case
- Place the sensor closer to electrical sources with the low-profile probe tip



TROUBLESHOOT QUICKLY

Provides features that can improve work efficiency

- Execute tasks efficiently with the bright flashlight and tip light to see target area
- Eliminate interruption from a dead battery with the low-battery indication feature
- Maximize battery life with the 'auto power off' feature

SPECIFICATIONS

Measurement

AC Voltage Range (default, solid green light)	90 to 1000 V AC
AC Excitation Voltage / Distance	90 V AC minimum / 1 cm (0.4 in)
Frequency Range	45 to 65 Hz
High-Sensitivity Mode (solid amber light)	24 to 1000 V AC

Meter Data

Flashlight	Yes
Tip Light	Yes
Category Rating	CAT IV-1000 V
Warranty	Limited 3-year

General Information

Certifications	UL, cUL, RCM
----------------	--------------

Power System

Power Requirements	2 × AAA alkaline batteries
Battery Life	~7 hours continuous (flashlight off)
Low Battery Voltage	Status LED flashes amber color
Auto Power Off	After 3 minutes of inactivity

Environmental Data

Drop Test	3 m (9.8 ft)
Operating Ambient Temperatures	0 to 60°C (-32 to 140°F)
Storage Temperature	-40 to 90°C (-40 to 194°F)

Physical Data

Weight	0.20 kg (0.44 lb), including batteries
Dimensions (H × W × L)	29 × 26 × 156 mm (1.1 × 1.0 × 6.1 in)

Specifications are subject to change without notice. For the most up-to-date specs, go to www.flir.com

CORPORATE HEADQUARTERS

FLIR Systems, Inc.
27700 SW Parkway Ave.
Wilsonville, OR 97070
PH: +1 877.773.3547

LATIN AMERICA

FLIR Systems Brasil
Av. Antonio Bardella, 320
Sorocaba, SP 18085-852
Brasil
PH: +55 15 3238 7080

NASHUA

FLIR Systems, Inc.
9 Townsend West
Nashua, NH 03063
USA
PH: +1 866.477.3687

CANADA

FLIR Systems, Ltd.
920 Sheldon Court
Burlington, ON L7L 5K6
Canada
PH: +1 800.613.0507

www.flir.com
NASDAQ: FLIR

Equipment described herein is subject to US export regulations and may require a license prior to export. Diversion contrary to US law is prohibited. Imagery for illustration purposes only. Specifications are subject to change without notice. ©2018 FLIR Systems, Inc. All rights reserved. 09/18

18-1797-INS



The World's Sixth Sense®

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Extech:](#)

[VP40](#)