



NOTES:



1. ALLOWABLE FLEXIBLE LIGHT PIPE CUT LENGTH AVAILABLE IN INCREMENTS OF 0.05".
2. MINIMUM BEND RADIUS OF FLEXIBLE LIGHT PIPE: 1.22" [31mm].
3. COMPONENTS SHIPPED NON-ASSEMBLED.
4. SEE SHEET 2 FOR DETAILED ASSEMBLY INSTRUCTIONS TO ACHIEVE OPTIMUM FUNCTION OF SEALING GASKET.




PART NUMBER CONFIGURATOR

SEE SHEET 2 FOR ORDERING INFORMATION

SF4-X.XX-F5PX-X							
LENGTH (L) (SEE TABLE 1)	CABLE COLOR (SEE TABLE 3)						
LENS COLOR (SEE TABLE 2)	IP RATING						
	<table><tr><th>IP OPTION</th><th>CODE</th></tr><tr><td>NONE</td><td>(BLANK)</td></tr><tr><td>IP54</td><td>54</td></tr></table>	IP OPTION	CODE	NONE	(BLANK)	IP54	54
IP OPTION	CODE						
NONE	(BLANK)						
IP54	54						



CUSTOMER USE DRAWING



STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED)		BIVAR [®] 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974	
DECIMALS	ANGULAR	TITLE: FLP ASSEMBLY WITH SMFLP ADAPTER, LC2	
.X ± .1	X° ± 1°	DESIGNED: K. BARON	DATE: 8/26/2019
.XX ± .02		REVISION: B	
.XXX ± .010		DRAWING NO: SF4-X.XX-F5PX-X	
		REVISION: B	
		SHEET SIZE: A	CAGE CODE: 32559
		CHECKED: A. VALDEZ	DATE: 4/9/2024
		SCALE: 2:1	SHEET # 1 OF 2
CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING			

TABLE 1 - LENGTH	
LENGTH (L)*	TOLERANCE
1.00" - 16.00"	±0.05"
16.05" - 40.00"	±0.15"
40.05" - 80.00"	±0.30"
80.05" - 3,940.00"	±0.5%

*AVAILABLE IN 0.05" INCREMENTS

TABLE 2 - LENS	
ORDER CODE	LENS APPEARANCE
(BLANK)	CLEAR
D	DIFFUSED
S	SMOKED
BE	TINTED BLUE
GN	TINTED GREEN
RD	TINTED RED
YW	TINTED YELLOW

TABLE 3 - CABLE	
ORDER CODE	CABLE COLOR
(BLANK)	BLACK
2	RED
4	YELLOW
5	GREEN
6	BLUE
9	WHITE

SAMPLE PART NUMBER:

SF4-11.20-F5PD54-5

11.20" LENGTH

DIFFUSED LENS

GREEN CABLE

IP54 RATED SEALING GASKET INCLUDED

ASSEMBLY INSTRUCTIONS TO ACHIEVE OPTIMUM FUNCTION OF SEALING GASKET:

- CLEAN PANEL SURFACE AROUND MOUNTING HOLE WITH ALCOHOL
- PEEL LINER OFF TOP OF THE SEALING GASKET WHILE KEEPING SEALING GASKET ON PLASTIC ROLL
- APPLY SEALING GASKET TO PANEL HOLE AS CENTERED AS POSSIBLE AND PEEL PLASTIC LINER SLOWLY AWAY
- INSERT LIGHT PIPE INTO PANEL UNTIL SEALING GASKET MATERIAL IS COMPRESSED BETWEEN LENS AND PANEL
- HOLD FOR A FEW SECONDS TO ENSURE ENTIRE SEALING GASKET ADHERES TO PANEL AND LENS FLANGE SURFACE

CUSTOMER USE DRAWING

		BIVAR[®]	
CAGE CODE:	32559	DRAWING NO: SF4-X.XX-F5PX-X	REVISION: B
SHEET SIZE:	A	SCALE: 2:1	SHEET # 2 OF 2
CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[BIVAR:](#)

[SF4-1.5-F5P](#) [SF4-1.5-F5P54](#) [SF4-1.5-F5P54-2](#) [SF4-1.5-F5P54-4](#) [SF4-1.5-F5P54-5](#) [SF4-1.5-F5P54-6](#) [SF4-1.5-F5P54-9](#) [SF4-10.0-F5P](#) [SF4-10.0-F5P54](#) [SF4-10.0-F5P54-2](#) [SF4-10.0-F5P54-4](#) [SF4-10.0-F5P54-5](#) [SF4-10.0-F5P54-6](#) [SF4-10.0-F5P54-9](#) [SF4-144.0-F5P](#) [SF4-144.0-F5P54](#) [SF4-144.0-F5P54-2](#) [SF4-144.0-F5P54-4](#) [SF4-144.0-F5P54-5](#) [SF4-144.0-F5P54-6](#) [SF4-144.0-F5P54-9](#) [SF4-18.0-F5P](#) [SF4-18.0-F5P54](#) [SF4-18.0-F5P54-2](#) [SF4-18.0-F5P54-4](#) [SF4-18.0-F5P54-5](#) [SF4-18.0-F5P54-6](#) [SF4-18.0-F5P54-9](#) [SF4-2.0-F5P](#) [SF4-2.0-F5P54](#) [SF4-2.0-F5P54-2](#) [SF4-2.0-F5P54-4](#) [SF4-2.0-F5P54-5](#) [SF4-2.0-F5P54-6](#) [SF4-2.0-F5P54-9](#) [SF4-2.5-F5P](#) [SF4-2.5-F5P54](#) [SF4-2.5-F5P54-2](#) [SF4-2.5-F5P54-4](#) [SF4-2.5-F5P54-5](#) [SF4-2.5-F5P54-6](#) [SF4-2.5-F5P54-9](#)