


DO NOT
SCALE FROM
THIS PRINTDESIGNED AND DIMENSIONED IN MILLIMETERS[INCHES]
ALL DIMENSIONS REFERENCE EXCEPT AS SHOWN

HTEC8-1XXX-XX-X-DV-XX-X-XX

No OF POSITIONS (PER ROW)

-10, -20, -30 (SEE FIG 1)
-09, -13, -25, -37, -40, -49,
-50, -60, -70, -80, -90, -100
(SEE FIG 2, SHT 2)

CARD THICKNESS

(SEE TABLE 5, SHT 2)

-01: 1.57 mm CARD

***-03: 2.36 mm CARD

PLATING SPECIFICATION

-L: 10 μ m LIGHT SELECTIVE GOLD IN
CONTACT AREA, MATTE TIN ON TAIL
-S: 30 μ m SELECTIVE GOLD IN CONTACT
AREA, MATTE TIN ON TAIL

ROW SPECIFICATION

-DV: DOUBLE VERTICAL

(***= NOT RELEASED)

PACKAGING

BLANK: TRAY (SEE NOTES 2 & 7)
-TR: TAPE & REEL (SEE NOTES 7 & 9)
(-09 THRU -70 POS ONLY)
-FR: FULL REEL QTY TAPE & REEL
(SEE NOTES 7 & 9)
(-09 THRU -70 POS ONLY)

PICK & PLACE OPTION

-K: POLYAMIDE FILM
(SEE FIG 3, SHT 2)

OPTIONS

BLANK: NO ALIGNMENT PIN
(USE HTEC8-XXX-01-DV, ONLY
AVAILABLE FOR -01 CARD THICKNESS)

-A: ALIGNMENT PIN

(USE HTEC8-XXX-XX-DV-A)

-WT: WELD TAB (SEE FIG 4, SHT 3)

(-A OPTION ONLY)

-BL: BOARD LOCK (SEE FIG 5, SHT 4)

(MUST SELECT BOTH -A AND -WT OPTIONS)




TABLE 1

No OF POS	COPLANARITY
-09 THRU -60	0.102 [.004]
-70 THRU -100	0.127 [.005]

TABLE 2

No OF POSITIONS	"A"	"B"	"C"	"D"	"E"
-10	12.60 [.496]	9.40 [.370]	7.20 [.283]	10.20 [.402]	7.20 [.283]
-20	20.60 [.811]	17.40 [.685]	15.20 [.598]	18.20 [.717]	15.20 [.598]
-30	28.60 [1.126]	25.400 [1.000]	23.200 [.913]	26.20 [1.031]	23.20 [.913]

NOTES:

1. MINIMUM PUSHOUT FORCE FOR SIGNALS AND SHIELD: 2.22N [.5 LB].
2. TRAYS ARE STANDARD PACKAGING.
3. NOTE DELETED.
4. K-DOT PROVIDED AS STANDARD.
5. MATING EDGE CARD THICKNESS TOLERANCE TO BE ± 0.157 [.0062] (PAD TO PAD) OF NOMINAL.
6. MATING CARD MUST HAVE LEAD-IN. SEE SAMTEC FOOTPRINT FOR SPECIFICATIONS.
7. ORDERS WILL BE PACKAGED ACCORDING TO THE SAMTEC PACKAGING EFFICIENCY STANDARDS (SPES) FOUND ON WWW.SAMTEC.COM.
8. NOTE DELETED.
9. ATTACH LABEL -4X2 TO EACH REEL.

* PROPRIETARY NOTE *

THIS DOCUMENT CONTAINS CONFIDENTIAL AND
PROPRIETARY INFORMATION AND ALL DESIGN,
MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS
AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC,
INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE
OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR
REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY
OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS
WRITTEN CONSENT OF SAMTEC, INC.

MATERIAL:

INSULATOR: LCP
COLOR: -01 CARD THICKNESS BLACK,
-03 CARD THICKNESS NATURAL
CONTACT: COPPER ALLOY

DO NOT SCALE DRAWING
SHEET SCALE: 2.5:1

DESCRIPTION:

0.8mm HIGH SPEED EDGE CARD ASSEMBLY
DWG. NO.

HTEC8-1XXX-XX-X-DV-XX-X-XX

BY: JERRY SU

08/11/2018

SHEET 1 OF 4





FIG 2
FOR POSITIONS -09, -13, -25, -37,
-40, -49, -50, -60, -70, -80, -90, -100
HTEC8-160-01-X-DV-A SHOWN
(DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1)
(SOME FEATURES NOT SHOWN FOR CLARITY)

TABLE 3

No OF POSITIONS	"F"	"G"	"H"	"J"	"K"	"L"	"M"	"N"
-09	15.00 [.591]	11.800 [.4646]	4.500 [.1772]	2.400 [.094]	5.30 [.209]	9.60 [.378]	12.60 [.496]	9.60 [.378]
-13	18.20 [.717]	15.000 [.5906]	6.100 [.2402]	4.000 [.157]	6.90 [.272]	12.80 [.504]	15.80 [.622]	12.80 [.504]
-25	27.80 [1.094]	24.600 [.9685]	6.100 [.2402]	4.000 [.157]	16.50 [.650]	22.40 [.882]	25.40 [1.000]	22.40 [.882]
-37	37.40 [1.472]	34.200 [1.3465]	18.100 [.7126]	16.000 [.630]	14.10 [.555]	32.00 [1.260]	35.00 [1.378]	32.00 [1.260]
-40	39.80 [1.567]	36.600 [1.4409]	18.900 [.7441]	16.800 [.661]	15.70 [.618]	34.40 [1.354]	37.40 [1.472]	34.40 [1.354]
-49	47.00 [1.850]	43.800 [1.7244]	22.900 [.9016]	20.800 [.819]	18.90 [.744]	41.60 [1.638]	44.60 [1.756]	41.60 [1.638]
-50	47.80 [1.882]	44.600 [1.7559]	22.900 [.9016]	20.800 [.819]	19.70 [.776]	42.40 [1.669]	45.40 [1.787]	42.40 [1.669]
-60	55.80 [2.197]	52.600 [2.0709]	26.900 [1.0591]	24.800 [.976]	23.70 [.933]	50.40 [1.984]	53.40 [2.102]	50.40 [1.984]
-70	63.80 [2.512]	60.600 [2.3858]	26.900 [1.0591]	24.800 [.976]	31.70 [1.248]	58.40 [2.299]	61.40 [2.417]	58.40 [2.299]
-80	71.80 [2.827]	68.600 [2.7008]	26.900 [1.0591]	24.800 [.976]	39.70 [1.563]	66.40 [2.614]	69.40 [2.732]	66.40 [2.614]
-90	79.80 [3.142]	76.600 [3.0157]	26.900 [1.0591]	24.800 [.976]	47.70 [1.878]	74.40 [2.929]	77.40 [3.047]	74.40 [2.929]
-100	87.80 [3.457]	84.600 [3.3307]	26.900 [1.0591]	24.800 [.976]	55.70 [2.193]	82.40 [3.244]	85.40 [3.362]	82.40 [3.244]

c:\enterprise\dwg\misc\mktg\HTEC8-1XXX-XX-X-DV-XX-X-XX-MKT.SLDDRW




FIG 3
-K OPTION
(SOME FEATURES NOT SHOWN FOR CLARITY)

TABLE 4

OPTION 2	No OF POS	"P"
NONE	-10 THRU -30	((("A" - 7.01 [.276]) / 2)
	-09, -13, -25, -37, -40 THRU -100	((("F" - 7.01 [.276]) / 2)
-WT	-10 THRU -30	((("S" - 7.01 [.276]) / 2)
	-09, -13, -25, -37, -40 THRU -100	
-BL	-10 THRU -30	((("U" - 7.01 [.276]) / 2)
	-09, -13, -25, -37, -40 THRU -100	

TABLE 5

CARD THICKNESS	"Q"	"X"	"Y"	"Z"	"AA"	"AB"
-01	0.71 [.028]	1.75 [.069]	5.60 [.220]	7.00 [.276]	1.04 [.041]	4.32 [.170]
-03	0.31 [.012]	2.54 [.100]	6.39 [.252]	7.79 [.307]	1.83 [.072]	5.11 [.201]

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 2.5:1

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code 55322

DESCRIPTION:

0.8mm HIGH SPEED EDGE CARD ASSEMBLY
DWG. NO.

HTEC8-1XXX-XX-X-DV-XX-X-XX

BY: JERRY SU 08/11/2018 SHEET 2 OF 4






FIG 4
-WT: WELD TAB OPTION
HTEC8-160-01-X-DV-A-WT SHOWN
AVAILABLE IN ALL POSITIONS
(-A OPTION REQUIRED)
(DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 2)
(SOME FEATURES NOT SHOWN FOR CLARITY)

TABLE 6		
No OF POS	"S"	"T"
-09	19.60 [.772]	17.30 [.681]
-10	17.20 [.677]	14.90 [.587]
-13	22.80 [.898]	20.50 [.807]
-20	25.20 [.992]	22.90 [.902]
-25	32.40 [1.276]	30.10 [1.185]
-30	33.20 [1.307]	30.90 [1.217]
-37	42.00 [1.654]	39.70 [1.563]
-40	44.40 [1.748]	42.10 [1.657]
-49	51.60 [2.031]	49.30 [1.941]
-50	52.40 [2.063]	50.10 [1.972]
-60	60.40 [2.378]	58.10 [2.287]
-70	68.40 [2.693]	66.10 [2.602]
-80	76.40 [3.008]	74.10 [2.917]
-90	84.40 [3.323]	82.10 [3.232]
-100	92.40 [3.638]	90.10 [3.547]



• PROPRIETARY NOTE • THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.	 520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail: info@SAMTEC.com code 55322
	DESCRIPTION: 0.8mm HIGH SPEED EDGE CARD ASSEMBLY
	DWG. NO. HTEC8-1XXX-XX-X-DV-XX-X-XX
	BY: JERRY SU 08/11/2018






FIG 5
-BL: BOARD LOCK OPTION
HTEC8-160-01-X-DV-A-BL-WT SHOWN
(FOR -09, -13, -25, -37, -40, -49, -50, -60, -70, -80, -90 & -100 POSITIONS
DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 2)
(FOR -10, -20 & -30 POSITIONS DIFFERENT AS SHOWN,
OTHERWISE SAME AS FIG 1)
(SOME FEATURES NOT SHOWN FOR CLARITY)
(AVAILABLE IN ALL POSITIONS)

TABLE 7		
No OF POS	"U"	
-09	26.25	[1.033]
-10	23.85	[.939]
-13	29.45	[1.159]
-20	31.85	[1.254]
-25	39.05	[1.537]
-30	39.85	[1.569]
-37	48.65	[1.915]
-40	51.05	[2.010]
-49	58.25	[2.293]
-50	59.05	[2.325]
-60	67.05	[2.640]
-70	75.05	[2.955]
-80	83.05	[3.270]
-90	91.05	[3.585]
-100	99.05	[3.900]





FIG 6
HTEC8-130-01-X-DV SHOWN
(DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1)
(SOME FEATURES NOT SHOWN FOR CLARITY)

• PROPRIETARY NOTE •
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

samtec
520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code 55322

DO NOT SCALE DRAWING
SHEET SCALE: 2.5:1

DESCRIPTION:
0.8mm HIGH SPEED EDGE CARD ASSEMBLY
DWG. NO.
HTEC8-1XXX-XX-X-DV-XX-X-XX
BY: JERRY SU 08/11/2018 SHEET 4 OF 4

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[HTEC8-120-01-S-DV-A-TR](#) [HTEC8-1100-01-L-DV-A-BL-K](#) [HTEC8-120-01-S-DV-TR](#) [HTEC8-113-01-L-DV-A-BL-TR](#)
[HTEC8-170-01-L-DV-A-K-FR](#) [HTEC8-125-01-S-DV-A-K-FR](#) [HTEC8-130-01-L-DV-A-WT-K](#) [HTEC8-110-01-L-DV-A-BL-](#)
[K-TR](#) [HTEC8-149-01-L-DV-A-BL-K-TR](#) [HTEC8-110-01-L-DV-A-BL-K-FR](#) [HTEC8-160-01-L-DV-A-BL](#) [HTEC8-125-01-](#)
[S-DV-A-K-TR](#) [HTEC8-150-01-S-DV-A-WT-K-TR](#) [HTEC8-190-01-L-DV-A-BL](#) [HTEC8-150-01-L-DV-A-FR](#) [HTEC8-125-](#)
[01-S-DV-K-TR](#) [HTEC8-110-01-S-DV](#) [HTEC8-150-01-S-DV-A-WT-K-FR](#) [HTEC8-125-01-L-DV-A-K-FR](#) [HTEC8-140-01-](#)
[L-DV-A-WT-TR](#) [HTEC8-170-01-L-DV-A-K-TR](#) [HTEC8-130-01-L-DV-K-TR](#) [HTEC8-109-01-L-DV-A-BL-K-TR](#) [HTEC8-](#)
[113-01-L-DV-A-BL-FR](#) [HTEC8-120-01-S-DV-A-WT-TR](#) [HTEC8-140-01-L-DV-A-WT-FR](#) [HTEC8-150-01-L-DV-A-K](#)
[HTEC8-125-01-L-DV-A-K-TR](#) [HTEC8-130-01-S-DV-A-WT-K](#) [HTEC8-190-01-L-DV-A-BL-K](#) [HTEC8-140-01-L-DV-A-TR](#)
[HTEC8-130-01-L-DV-A-TR](#) [HTEC8-130-01-L-DV-A-BL-K-TR](#) [HTEC8-130-01-L-DV-A-FR](#) [HTEC8-140-01-S-DV-A-K](#)
[HTEC8-130-01-S-DV-A-K](#) [HTEC8-113-01-L-DV-A-K-TR](#) [HTEC8-130-01-S-DV](#) [HTEC8-160-01-L-DV-A-WT-K-FR](#)
[HTEC8-160-01-S-DV-A-WT-K-TR](#) [HTEC8-120-01-L-DV-A-K](#) [HTEC8-140-01-L-DV-A-FR](#)