


(2.54 mm) .100" PITCH • DISCRETE WIRE TERMINAL

IPL1	1	PINS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION	TAIL OPTION	K	OPTION
		02, 03, 04, 05, 06, 08, 10, 12, 15, 16, 20, 25 (Standard sizes)	-01 = Through-hole -02 = Surface Mount	-L = 10 μm (0.25 μm) Gold on contact, Matte Tin on tail	-S = Single Row -SH = Single Row Horizontal (-02 lead style only) -D = Double Row	-RA = Right-angle (-01 lead style only) -RE1 = Right-angle Elevated (-01 lead style only) (-K is a required callout)	-K = Keyed Polarization	-TR = Tape & Reel (-02 lead style only) Comes with Polyimide Pick & Place Pad -FR = Full Reel Tape & Reel (must order max. quantity per reel; contact Samtec for quantity breaks) (-02 lead style only) Comes with Polyimide Pick & Place Pad

IPL1

Cable Mates:
MMSD, MMSS,
MMSDT, MMSST



MMSD/IPL1	
WIRE GAUGE	CURRENT RATING (PER PIN)
20	4.8 A
22	4.3 A
24	3.9 A
26	3.5 A
28	2.6 A
30	2.1 A

2 PINS POWERED

SPECIFICATIONS

Insulator Material:

Natural LCP

Terminal Material:

Phosphor Bronze

Plating:

Sn or Au over
50 μm (1.27 μm) Ni

Operating Temp Range:

-55 °C to +125 °C

Voltage Rating:

675 VAC/954 VDC

PROCESSING

Lead-Free Solderable:

Yes

-S & -D (-02 Lead Style)


SMT Lead Coplanarity:

(0.10 mm) .004" max (02-05)
(0.13 mm) .005" max (06-10)*
(0.15 mm) .006" max (11-25)*

*(.004" stencil solution may be available; contact IPG@samtec.com)

-SH SMT Lead Coplanarity:

(0.15 mm) .006" max (02-25)*
(.004" stencil solution may be available; contact IPG@samtec.com)



ALSO AVAILABLE

MOQ Required

Other sizes

With or without plug polarization

Guide post holes

Other platings

Weld tab

Note:

Some lengths, styles and options are non-standard, non-returnable.

View complete specifications at: samtec.com?IPL1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[IPL1-106-02-H-S-K](#)