


SPECIFICATION CONTROL DRAWING



1. MATING INTERFACE DIMENSIONS PER MIL-STD-348A, FIG. 326-5

2. ELECTRICAL

FREQUENCY RANGE GHz	DC TO 26.5 GHz
VSWR (MAX.) *	1.05 + .010 x FGHz.
INSERTION LOSS (dB MAX.) *	.04 dB x $\sqrt{\text{FGHz}}$.
NOMINAL IMPEDANCE (OHMS)	50
VOLTAGE RATING (MAX. VRMS)	125
RF LEAKAGE (MIN. dB DOWN)	-85 dB - FGHz
TEMPERATURE RATING (DEGREES CENTIGRADE)	-65° c TO +150° c
DIELECTRIC WITHSTANDING VOLTAGE (MAX. VRMS)	375
INSULATION RESISTANCE (MIN. MEGOHMS)	5,000
CONTACT RESISTANCE	
• CENTER CONTACT (MAX. MILLIOHMS)	3.0
• OUTER CONTACT (MAX. MILLIOHMS)	2.0

* TERMINATED IN A 50 OHM LOAD

RoHS
COMPLIANT

This Document contains proprietary and confidential information.

REV.	DCN NO.	DATE	APP.	DIMENSIONS ARE IN INCHES TOLERANCES				dynawave INCORPORATED HAVERHILL MA. 01835		
				DECIMALS	FRACTIONAL	ANGULAR				
AA	06-1927	8/1/06	DC	X ± .030	± 1/64	X° ± 1° 0'				
AB	07-1525	5/16/07	DC	.XX ± .010		X° X' ± 15'				
AC	17-1175	2/3/17	DC	.XXX ± .005						
AD	18-2229	11/5/18	DC	SURFACE ROUGHNESS 63 ✓ MIL-STD 10.				TITLE SMP MALE (SBCM) BULKHEAD MOUNT DIRECT SOLDER TO Ø.047 S/R CABLE		
				DRAWN	DC	DATE	8/1/06			
				APPROVED	TS	DATE	8/1/06			
				CODE IDENT.	SHEET 1 OF 2		DWG. NO. 2119-4721-6205			
				2J899						

SPECIFICATION CONTROL DRAWING

3. MECHANICAL

CAPTIVATION-CENTER CONTACT

- MIN. AXIAL FORCE _____ 4.5 LBS.
- MIN. RADIAL TORQUE _____ N/A

CONNECTOR ENGAGEMENT FORCES

- INSERTION (MAX. OUNCES) _____ N/A
- WITHDRAWAL (MIN. OUNCES) _____ N/A

CONNECTOR DURABILITY (MIN. MATING) _____ 1000

- ASSEMBLY TORQUE OF BODIES _____ 6.0 TO 8.0 IN./LBS.

CONNECTOR INSTALLATION / REMOVAL FORCE.

- INSERTION (MAX. LBS) _____ 2.0
- WITHDRAWAL (MIN. LBS) _____ 0.5

RECOMMENDED MATING TORQUE _____ 6.0 TO 8.0 IN./LBS.

RECOMMENDED TORQUE TOOL _____ 9-20231-09

4. ENVIRONMENTAL

TEMPERATURE CYCLING _____ MIL-STD-202, METHOD 102, COND. C (-65 ° c TO + 165 ° c)

SHOCK _____ MIL-STD-202, METHOD 213, COND. I (100 G's)

VIBRATION _____ MIL-STD-202, METHOD 204, COND. D (20 G's)

MOISTURE RESISTANCE _____ MIL-STD-202, METHOD 106, LESS STEP 7b

CORROSION _____ MIL-STD-202, METHOD 101, COND. B (48 HOURS)

BAROMETRIC PRESSURE (ALTITUDE) _____ MIL-STD-202, METHOD 105, COND. C (70,000 FT.) (94 VRMS)

5. MATERIAL

BODY (FULL DETENT) AND SHROUD _____ STAINLESS STEEL PER ASTM A 582, TYPE 303, COND A.

CONTACT _____ BERYLLIUM COPPER PER ASTM-B196/B 196M-03 COPPER ALLOY NO. UNS-C17300.

INSULATOR _____ TEFLON PER ASTM-D-1710, TYPE 1, GRADE 1, CLASS B.

REAR INSULATOR _____ TORLON 4023

6. FINISH

SHROUD _____ PASSIVATED PER AMS-2700, TYPE 2, CLASS 4.

BODY AND CONTACT _____ GOLD PER ASTM-B-488, TYPE II, CODE, CLASS 1.27
(.000050 MIN.) OVER NICKEL PER QQ-N-290, CLASS 1
(.000050 MIN.) OVER COPPER PER AMS-2418 (.000010 MIN.)

INSULATORS _____ N/A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Winchester Interconnect:](#)

[2119-4721-6205](#)