

# 1250 Rocker Switches 10A 250Vac



10(6)A 250Vac T100  
6A 400Vac T100  
1A 30Vdc



UL CSA 10A 250Vac  
UL CSA 16A 250Vac Resistive  
UL CSA 125Vac 1/2hp  
UL CSA 1A 30Vdc  
UL 100°C, file E45221, CSA file LR10990

In house test

Inrush 75A to EN61058-1 & 10A 28Vdc



RoHS compliant

3mm contact gap  
Technical data on pages 4 & 5

- Standard rocker switch
- Double pole in single pole body
- Snap in or sub panel mount
- Integral terminal barrier
- Push on or PCB terminals
- High inrush tolerance
- Bezel size:  
29.5 x 15mm (snap in)  
23.5 x 13mm (sub panel mount)



C1250AP



C1250AN

**C 1250 A P B B 085W**

**B** BLACK  
**W** WHITE

**B** BLACK  
**W** WHITE  
**G** GREY


TERMINAL CODE    FUNCTION CODE    ROCKER CODE    BODY CODE    BODY COLOR    ROCKER COLOR    LEGEND & OPTIONS

## ORDER FORMAT


| TERMINAL                                           | FUNCTION                                                                                                                          | ROCKER                                                                                  | BODY                                                                                                                                                                                                          | OPTIONS                                                                                                                                                                                                                                        |
|----------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <p><b>C</b></p> <p>6.3 x 0.8</p>                   | <p>On when pressed over terminal 1</p> <p><b>1250</b></p> <p>ON - OFF<br/>Double pole</p> <p>Poles are 9.0mm between centres.</p> | <p><b>A</b> Curved</p> <p>Shown in N body</p>                                           | <p><b>N</b></p> <p>Panel cut-out      Bezel</p> <p>Sub-panel      Facia</p> <p>Panel thickness      Dim X</p> <p>0.75-1.24      26.1/26.2</p> <p>1.25-1.99      26.3/26.4</p> <p>2.00-3.00      26.7/26.8</p> | <p><b>Finish</b><br/>Matt finish only</p> <p><b>Color</b><br/>Call factory for custom colors.<br/>A full range is available for large orders</p> <p><b>Legend printing</b><br/>Select from the examples or call factory for custom legends</p> |
| <p><b>X</b></p> <p>PCB 0.8sq<br/>(N body only)</p> | <p>On when pressed over terminal 1</p> <p><b>1250SP</b></p> <p>ON - OFF<br/>Single pole</p>                                       | <p><b>P</b></p> <p>Panel cut-out      Bezel</p> <p>Panel thickness</p> <p>0.75-3.00</p> | <p>Cut-outs must be punched in the direction of insertion</p>                                                                                                                                                 |                                                                                                                                                                                                                                                |

### Dimensions (mm)


1250AN (C terminals shown)



1250AN (X terminals shown)



1250AP (C terminals shown)



### Examples of our range of legend printing

( ) is legend color    B-Black, W-White, R-Red



085(B)



086(B)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Bulgin:](#)

[X1250ANBB](#)