

## Detailed Specifications

<b>Frame Width:</b>	30[mm]
<b>Frame Height:</b>	30[mm]
<b>Frame Depth:</b>	10[mm]
<b>Max. Air Flow:</b>	3.5[CFM]
<b>Max. Air Flow:</b>	0.1[m <sup>3</sup> per min]
<b>Max. Static Pressure:</b>	0.15[In H <sub>2</sub> O]
<b>Max. Static Pressure:</b>	38[Pa]
<b>Fan Speed:</b>	8500[RPM]
<b>Noise:</b>	26[dB]
<b>Life Expectancy:</b>	40 degree C 30,000 Hours[L10]
<b>Bearing Type:</b>	Sleeve Bearing
<b>Nominal Voltage:</b>	12[V]
<b>Operating Voltage - Lower:</b>	7[V]
<b>Operating Voltage - Upper:</b>	13.2[V]
<b>Current:</b>	0.06[A]
<b>Input Power:</b>	0.7[W]
<b>Mass:</b>	8.5[g]
<b>Tach / Locked Rotor Output:</b>	Locked Rotor
<b>Status:</b>	Active

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[03010SS-12L-AL-00](#)