

Detailed Specifications

Frame Width:	80[mm]
Frame Height:	80[mm]
Frame Depth:	15[mm]
Max. Air Flow:	33.9[CFM]
Max. Air Flow:	0.96[m ³ per min]
Max. Static Pressure:	0.14[In H ₂ O]
Max. Static Pressure:	34.2[Pa]
Fan Speed:	3100[RPM]
Noise:	34[dB]
Life Expectancy:	40 degree C 40,000 Hours[L10]
Bearing Type:	Sleeve Bearing
Nominal Voltage:	24[V]
Operating Voltage - Lower:	12[V]
Operating Voltage - Upper:	26.4[V]
Current:	0.12[A]
Input Power:	2.9[W]
Mass:	55[g]
Tach / Locked Rotor Output:	Locked Rotor
Status:	Active

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[08015SS-24N-AL-00](#)