

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO J.S.T. AND SHALL NOT BE USED OR SHOWN WITHOUT WRITTEN PERMISSION.

1	2	3	4
Item No.	Part No.	Description	
1	SSHL-002T-P0.2	GH Connector Contact	
2	UL1571, 28 AWG	Black	


Electrical Specifications

Current: 1.0AAC/DC

Voltage: 50V AC/DC

APPLICABLE HOUSINGS

NO. OF CIRCUITS	HOUSING PART NO.
2	GHR-02V-S
3	GHR-03V-S
4	GHR-04V-S
5	GHR-05V-S
6	GHR-06V-S
7	GHR-07V-S
8	GHR-08V-S
9	GHR-09V-S
10	GHR-10V-S
11	GHR-11V-S
12	GHR-12V-S
13	GHR-13V-S
14	GHR-14V-S
15	GHR-15V-S



JST

ZONE	REV	DESCRIPTION	DATE	APPROVED
	1	Add Electrical Specifications	6/29/2018	LM

All dimensions are in millimeters with a default tolerance of +/- 5.0 unless otherwise specified.

Drawn By:
Larissa Mosley
Checked By:
Steven Pilkington

CUSTOMER NAME

DESCRIPTION

1.25mm Pitch GH Series Standard Leads - 4" Inside Length
DOUBLE END LEADS

SIZE	CUSTOMER PART NO.	PART NO.	REV
		AGHGH28K102	
SCALE	1:1	DRAWING NO. GAM-322	DATE 4/24/2018

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JST:](#)

[AGHDGHD26K254](#)