


**HS 6.4-19.1/50 MM Y****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

**General ordering data**

|                    |                                                                                  |
|--------------------|----------------------------------------------------------------------------------|
| Version            | Conductor and cable markers, 6.4 - 19.1 mm, 50.8 x 30.9 mm, yellow               |
| Order No.          | <a href="#">2437780000</a>                                                       |
| Type               | HS 6.4-19.1/50 MM Y                                                              |
| GTIN (EAN)         | 4050118458039                                                                    |
| Qty.               | 400 pc(s).                                                                       |
| compatible printer | <a href="#">2599430000</a> <a href="#">2599440000</a> <a href="#">1140490000</a> |

Creation date September 17, 2022 10:13:14 PM CEST

Catalogue status 09.09.2022 / We reserve the right to make technical changes.

## HS 6.4-19.1/50 MM Y

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 0.77 mm | Depth (inches)  | 0.03 inch  |
| Height     | 50.8 mm | Height (inches) | 2 inch     |
| Width      | 30.9 mm | Width (inches)  | 1.217 inch |
| Net weight | 1.6 g   |                 |            |

### Temperatures

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -55...135 °C |
|-----------------------------|--------------|

### General data

|                                   |              |                                   |                                                           |
|-----------------------------------|--------------|-----------------------------------|-----------------------------------------------------------|
| Colour                            | yellow       | Halogen                           | Yes                                                       |
| Material                          | Polyolefine  | Number per roll                   | 400                                                       |
| Operating temperature range       | -55...135 °C | Operating temperature range, max. | 135 °C                                                    |
| Operating temperature range, min. | -55 °C       | Recommended industries            | Plant manufacture, Energy, Device manufacturer, Machinery |
| Width                             | 30.9 mm      |                                   |                                                           |

### Conductor and cable markers

|                                   |                    |                                  |                         |
|-----------------------------------|--------------------|----------------------------------|-------------------------|
| Conductor O.D.                    | 6.4 - 19.1 mm      | Conductor O.D., max.             | 19.1 mm                 |
| Conductor O.D., min.              | 6.4 mm             | Conductor cross-section, max.    | 70 mm <sup>2</sup>      |
| Conductor cross-section, min.     | 16 mm <sup>2</sup> | Cross-section for connected wire | 16 - 70 mm <sup>2</sup> |
| Halogen                           | Yes                | Rate of shrinkage                | 3:1                     |
| Recommended shrinking temperature | 90 °C              |                                  |                         |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001530    | ETIM 7.0    | EC001530    |
| ETIM 8.0    | EC001530    | ECLASS 9.0  | 27-40-04-01 |
| ECLASS 9.1  | 27-40-04-01 | ECLASS 10.0 | 27-40-04-01 |
| ECLASS 11.0 | 27-28-11-02 | ECLASS 12.0 | 27-28-11-02 |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|                  |                                          |
|------------------|------------------------------------------|
| Engineering Data | <a href="#">EPLAN</a>                    |
| Catalogues       | <a href="#">Catalogues in PDF-format</a> |

### HS 6.4-19.1/50 MM Y

**Weidmüller Interface GmbH & Co. KG**


Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[2437780000](#)