

IE-SR-4GT-LTE/4G-USEMEA**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Weidmüller Industrial Security Routers**

- Secure networks
 - Stateful packet inspection Firewall
 - IP/Port- forwarding
 - Network segmentation
- Easy integration of machine networks into manufacturing networks through 1: 1 NAT
- Secure and easy remote maintenance with Weidmüller u-link remote access service
- Enable modular and future proof network architectures with static and dynamic routing
- Secure communication over the Internet by using IPsec and OpenVPN
- Reliable internet connection, even without on-site internet access, thanks to integrated 4G/LTE cellular modem
- Full flexibility thanks to Fast Ethernet and Gigabit Ethernet interfaces ranging from 2 up to 4 ports.

General ordering data

Version	Security/NAT/VPN/U-link Router, with integrated multi-band modem (4G/3G), US/EMEA-model, Gigabit Ethernet, 4x RJ45 10/100/1000BaseT(X), IP20, -25 °C...70 °C
Order No.	2873930000
Type	IE-SR-4GT-LTE/4G-USEMEA
GTIN (EAN)	4064675647690
Qty.	1 pc(s).

IE-SR-4GT-LTE/4G-USEMEA

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	115 mm	Depth (inches)	4.528 inch
Height	150 mm	Height (inches)	5.905 inch
Width	35 mm	Width (inches)	1.378 inch
Net weight	632 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-25 °C...70 °C
Humidity	5 - 90 %, no condensation		

Mobile radio interface

Frequency band	EMEA / Americas, LTE: B1 (2100), B2 (1900), B3 (1800), B4 (AWS), B5 (850), B7 (2600), B12 (700ac), B13 (700c), B20 (800DD), B25 (1900), B26 (US 850 Ext), B29 (US 700de Lower), B30 (2300 WCS), B41 (TDD 2500), UMTS: B1 (2100), B2 (1900), B3 (1800), B4 (AWS), B5 (850), B8 (900)		
Mode of operation	Permanent connection, Manual connection control via web interface, Manual connection control via API or SMS, Fallback		
Transmission rate mobile radio	LTE category	CAT 6	
	Download rate, max.	300 Mbit/s	
	Upload rate, max.	50 Mbit/s	
Wireless module	multi-band modem (4G/3G)		

VPN

IPsec	Configurable as IPsec server or client	OpenVPN	Configurable as OpenVPN server or client (Layer 2 and Layer 3)
u-link	OpenVPN-based remote access service via the Weidmüller u-link cloud		

Modes of operation

Extended IP router	Each interface (LAN, WAN, optional 4G/LTE) can be configured as separate IP network	IP router	IP routing (IPv4, Layer-3) with SPI firewall (Stateful Packet Inspection), Static or dynamic routing, Supports RIPv2 / OSPF
Transparent bridge	4-port switch with additional Layer-2 filter		

EMC conformity and approvals

EMC standards	EN 61000-6-4, EN 61000-6-2	Safety standard	EN 62368-1, EN 62311, UL 61010-1, UL 61010-2-201
Shock	according to IEC 60068-2-27	Vibration	according to IEC 60068-2-6

Environmental conditions

Humidity	5 - 90 %, no condensation		
Operating altitude	Altitude, max.	2,000 m	
	Note	in acc. with UL	
Operating temperature, max.	70 °C		
Operating temperature, min.	-25 °C		

Creation date July 23, 2024 5:11:44 PM CEST

IE-SR-4GT-LTE/4G-USEMEA

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Storage temperature, max.	85 °C
Storage temperature, min.	-40 °C

Guarantee

Time interval	3 years
---------------	---------

Interfaces

Connector for external antennas		Digital inputs	2x, galvanically isolated, VPN-initiate: establishes a pre-configured VPN connection (24 V in), Cut: physically disconnects (Link Down) the WAN port (24 V in), Trigger pre-configured packet filter rules (24 V in)
Digital outputs	2x SMA female Alarm: indicates a configurable network state or fault (24 V out), VPN-active: indicates an active VPN connection (24 V out), 1x	Function reset button	Restoration of factory settings
LED indicator	Power: indicates power supply status, boot-up process, firmware update process, Status: indicates system status, VPN: indicates VPN tunnel status, LTE/4G: indicates mobile radio connection status, Port LED: Link/ACT, Speed (RJ45 port)	Number of SCM-Card slots	1
Number of SIM-Card slots	1	Number of ports	4x RJ45 10/100/1000BaseT(X)
RJ45 ports	10/100BaseT(X), auto negotiation, Full-/half-duplex mode, Auto MDI/MDI-X port, 10/100/1000BaseT(X)	SCM-Card slot type	Smart Card (ID-000 format), Save and restore the configuration using smart card (memory chip)
SIM-Card slot type	Mini-SIM (ID-000 format)	Serial port	1x RS-485, 2-wire, galvanically isolated, 1 removable 3-pole terminal block
USB port	USB 2.0 interface for firmware update or restoration of the device configuration via USB flash drive		

Management features

Device configuration	Webbrowser (HTTP/HTTPS), SNMP v1/v2c/v3, Windows tool	Monitoring function	SNMP v1/v2c/v3, Syslog
IP-address management	Static, DHCP-Client, DHCP-Server (pool-based)	Security functions	IPv4 Stateful Packet Inspection Firewall (incoming/outgoing), NAT masquerading, 1:1 NAT, IP forwarding, Port forwarding
Time synchronization management	NTP server, NTP client		

Power supply

Connection type	1 removable 4-pin terminal block
-----------------	----------------------------------

Creation date July 23, 2024 5:11:44 PM CEST

IE-SR-4GT-LTE/4G-USEMEA

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Current consumption	Voltage	24 V
	Current	1.5 A
Reverse polarity protection	Yes	
Voltage supply	24 V DC, 1 single input	
Voltage supply range	Voltage type	DC
	Voltage, min.	19.2 V
	Voltage, max.	28.8 V

Technical data

Housing main material	Aluminium	Protection degree	IP20
Speed	Gigabit Ethernet	Type of mounting	DIN rail

Technology

Standard	IEEE 802.3 for 10BASE-T, IEEE 802.3u for 100BASE-TX, IEEE 802.3ab for 1000BASE-T
----------	--

Classifications

ETIM 6.0	EC001478	ETIM 7.0	EC001478
ETIM 8.0	EC001478	ETIM 9.0	EC001478
ECLASS 9.0	19-17-01-03	ECLASS 9.1	19-17-01-03
ECLASS 10.0	19-17-04-05	ECLASS 11.0	19-17-04-05
ECLASS 12.0	19-17-04-05	ECLASS 13.0	19-17-04-05

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	1bb4009c-24f3-4115-ab13-f6bde3580fe2
RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c, 7a, 7cl, 7cII

Important note

Product information	For the SCM card usage please check the compatibility list for suitable router models and hardware revisions found at the SCM card IE-EBR-SMARTCARD-SR 2909820000.
---------------------	--

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E141197

IE-SR-4GT-LTE/4G-USEMEA**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Downloads**

Approval/Certificate/Document of Conformity	UK Declaration of Conformity EU Declaration of Conformity
Engineering Data	CAD data – STEP
Product Change Notification	Firmware Release Notes Product Change Notification (Mobile radio modem)
Software	Software – u-link VPN-Client Current Firmware
User Documentation	u-link EULA V3 EN (28.5.2018) Hardware Installation Guide Manual u-link EULA V4 EN (20.9.2023) Mandatory connection parameters for u-link VPN clients
Catalogues	Catalogues in PDF-format

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[2873930000](#)