

IE-C5DD4UG0010MCSMCS-E**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Assembled IE cables, PROFINET, Cat. 5, PUR, green, drag-chain compatible, M12

General ordering data

Version	Dragline cable, PROFINET, M12 D-code – IP 67 straight pin, M12 D-code – IP 67 straight pin, Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B), PUR, 1 m
Order No.	1025950010
Type	IE-C5DD4UG0010MCSMCS-E
GTIN (EAN)	4032248830855
Qty.	1 pc(s).

Creation date January 18, 2022 10:19:56 PM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

IE-C5DD4UG0010MCSMCS-E**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Length	1 m	Length (inches)	39.37 inch
Net weight	90 g		

Temperatures

Storage temperature	-50 °C...70 °C	Operating temperature	-40 °C...70 °C
Installation temperature	-20 °C...60 °C		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Cable specific standards

Standard, insulating material	DIN EN 50290-2-23 (VDE 0819) Table 2/A (HD 624.3)	Standard, shielding material	DIN EN 13602 Cu-ETP-A..B
Standard, wire material	DIN EN 13602 Cu-ETP-A		

General standards

Certificate no. (cULus)	E316369	Connector standard	IEC 61076-2-101
-------------------------	---------	--------------------	-----------------

Standards

Connector standard	IEC 61076-2-101	Standard, insulating material	DIN EN 50290-2-23 (VDE 0819) Table 2/A (HD 624.3)
Standard, shielding material	DIN EN 13602 Cu-ETP-A..B	Standard, wire material	DIN EN 13602 Cu-ETP-A

Cable structure

Arrangement of wire cores	Star-quad	Colour sequence or wires - wire pairs	white, yellow, blue, orange
Complete shielding	Aluminium foil, Shielding braid made from copper wiring	Cross-section	4*AWG 22/7 - 0.36 mm ²
Diameter of inner sheathing	3.9 mm	Filler	As central element
Insulation	PE	Insulation cross-section	1.5 mm
Material sheath	PUR	Number of wires	4
Overlap of shielding braid	85 %	Sheath diameter, max.	6.7 mm
Sheath diameter, min.	6.3 mm	Sheathing colour	green (RAL 6018)
Sheathing material thickness	0.9 mm	Shielding	SF/UTP
Shielding braid thickness	0.13 mm	Standard designations	2YH(ST)C11Y 2x2x0,75/1,5-100 LI VZN GN FRNC
Strands	7	Wire core insulation thickness	0.38 mm
Wire material	Stranded tin-plated copper wire		

Electrical properties of cable

Capacity at 1 kHz	52 nF/km
Category	Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B)
Characteristic impedance	100 ± 15 Ω at 1–100 MHz
Deviation	40 ns/100m

Creation date January 18, 2022 10:19:56 PM CET

IE-C5DD4UG0010MCSMCS-E**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Loop resistance	120 Ω/km
Operating voltage (UL rating)	Operating voltage 600 V
Operating voltage (UL rating)	600 V undefined
Operating voltage, UL	600 V
Resistance differential	3 %
Signal propagation time	5.3 ns/m
Speed	180 m/min
Test voltage: wire-wire-shield	2000 V _{eff} , 50 Hz, 1 min
Transfer impedance	20 mΩ/m at 10 MHz

Mechanical and material properties of cable

Abrasion resistance	very good	Acceleration	4 m/s ²
Bending cycles	3 Mio	Fire propagation	No
Halogen	halogen-free, according to IEC 60754-2	Min. bending radius, once only	5 x cable diameter
Min. bending radius, repetitive	7.5 x cable diameter	Pulling force	≤ 150 N
Resistance to oils	in accordance with IEC 60811-2-1	Resistance to spread of flame	in accordance with IEC 60332-1
Silicone-free	Yes	Speed	180 m/min
UV-resistant	Yes		

Plug, left

Connector left	M12 D-code – IP 67 straight pin
----------------	------------------------------------

Plug, right

Connector right	M12 D-code – IP 67 straight pin
-----------------	------------------------------------

plug

Connector left	M12 D-code – IP 67 straight pin	Connector right	M12 D-code – IP 67 straight pin
----------------	------------------------------------	-----------------	------------------------------------

Classifications

ETIM 6.0	EC002599	ETIM 7.0	EC002599
ETIM 8.0	EC002599	ECLASS 9.0	27-06-03-08
ECLASS 9.1	27-06-03-08	ECLASS 10.0	27-06-03-08
ECLASS 11.0	27-06-03-08		

Approvals

Approvals



ROHS	Conform
UL File Number Search	E316369

IE-C5DD4UG0010MCSMCS-E**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Downloads**

Approval/Certificate/Document of Conformity	DUXR.E316369 PROFINET Manufacturer's Declaration
Engineering Data	CAD data – STEP
Engineering Data	WSCAD
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN PI PROFINET CABLING EN

Data sheet**IE-C5DD4UG0010MCSMCS-E****Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germanywww.weidmueller.com**Drawings****Wiring**

M12		M12
1	yellow	1
2	white	2
3	orange	3
4	blue	4

IE-C5DD4UG0010MCSMCS-E

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Blank



TM-I is an acknowledged and accredited marker type for traffic engineering applications. There are various different tag lengths available for individual labelling with long character strings. Easy handling of separation and installation thanks to the project marker field. Pre-attachment of sleeves and retrofitting of tags offer excellent versatility

The special contour of TM-I allows easy assembly and secures firm positioning. They are compatible with a number of commercially available sleeves. Thanks to the MultiCard format, the tags can be printed quickly and conveniently with the PrintJet CONNECT, plotter or the STI pen.

- Easy handling of separation and installation thanks to the project marker field.
- Acknowledged and accredited marker for traffic engineering applications
- Pre-attachment of sleeves and retrofitting of tags offer excellent versatility
- Not suited for labelling with P-Ink or STI pen in connection with CLI T sleeves

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	TM-I 12 MC NE GE	Version
Order No.	1718411687	TM-I, Insert markers, 12 x 4 mm, yellow
GTIN (EAN)	4008190348984	
Qty.	320 pc(s).	

IE-C5DD4UG0010MCSMCS-E

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Blank



TM-I is an acknowledged and accredited marker type for traffic engineering applications. There are various different tag lengths available for individual labelling with long character strings. Easy handling of separation and installation thanks to the project marker field. Pre-attachment of sleeves and retrofitting of tags offer excellent versatility

The special contour of TM-I allows easy assembly and secures firm positioning. They are compatible with a number of commercially available sleeves. Thanks to the MultiCard format, the tags can be printed quickly and conveniently with the PrintJet CONNECT, plotter or the STI pen.

- Easy handling of separation and installation thanks to the project marker field.
- Acknowledged and accredited marker for traffic engineering applications
- Pre-attachment of sleeves and retrofitting of tags offer excellent versatility
- Not suited for labelling with P-Ink or STI pen in connection with CLI T sleeves

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	TM-I 18 MC NE GE	Version
Order No.	1718431687	TM-I, Insert markers, 18 x 4 mm, yellow
GTIN (EAN)	4008190349028	
Qty.	320 pc(s).	

IE-C5DD4UG0010MCSMCS-E

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Screwty® cable gland tool



The ideal tool for any application

Screwty® is the ideal, all-purpose tool for tightening all common sensor and actuator cables. Even difficult-to-reach round plugs are accessible using the Screwty®. A simple turning movement tightens and loosens the connectors without the need for excessive force. The Screwty® is a unique and global solution since it fits with most cables and plugs from other vendors (over 90 %). The Screwty® consists of a handle with a conventional 1/4" adapter. Thus it can be used for all sizes: for M12 and M8 round plug-in connectors, and for M12F and M8F customisable plugs and sockets, as well as for all M23 plugs and sockets.

General ordering data

Type	SCREWTY- M12	Version
Order No.	1900000000	Cable gland tool for moulded M12 lines
GTIN (EAN)	4032248375868	
Qty.	1 pc(s).	

Type	SCREWTY SET	Version
Order No.	1910000000	Bolting tool
GTIN (EAN)	4032248436842	
Qty.	1 pc(s).	

Screwty® cable gland tool with torque function



The ideal tool for any application

Screwty® is the ideal, all-purpose tool for tightening all common sensor and actuator cables. Even difficult-to-reach round plugs are accessible using the Screwty®. A simple turning movement tightens and loosens the connectors without the need for excessive force. The Screwty® is a unique and global solution since it fits with most cables and plugs from other vendors (over 90 %). The Screwty® consists of a handle with a conventional 1/4" adapter. Thus it can be used for all sizes: for M12 and M8 round plug-in connectors, and for M12F and M8F customisable plugs and sockets, as well as for all M23 plugs and sockets.

General ordering data

Type	SCREWTY SET -DM	Version
Order No.	1920000000	Bolting tool
GTIN (EAN)	4032248436859	
Qty.	1 pc(s).	

Type	SCREWTY-M12-DM	Version
Order No.	1900001000	Cable gland tool for moulded M12 lines
GTIN (EAN)	4032248436408	
Qty.	1 pc(s).	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1025950010](#)