

## SVF 7.62HP/03/180G SN BK BX

**Weidmüller Interface GmbH & Co. KG**


Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

### Product image



Similar to illustration

180° inverted pin header with PUSH IN connection technology for field wiring in 6mm<sup>2</sup> in a 7.62 pitch, as a “three-flange variant” for enclosure feed-through. Suitable for enclosures with a max. wall thickness of 2mm. Also perfect as a touch-safe solution for reverse voltages. Meets the requirements of UL1059 600 V Class C and IEC 61800-5-1.

### General ordering data

|              |  |
|--------------|--|
| Version      | PCB plug-in connector, male plug, 7.62 mm, Number of poles: 3, 180°, PUSH IN without actuator, Tension-clamp connection, Clamping range, max. : 10 mm <sup>2</sup> , Box |
| Order No.    | <a href="#">1060840000</a>   |
| Type         | SVF 7.62HP/03/180G SN BK BX  |
| GTIN (EAN)   | 4032248810864  |
| Qty.         | 65 pc(s).  |
| Product data | IEC: 1000 V / 57 A / 0.5 - 10 mm <sup>2</sup><br>UL: 600 V / 39 A / AWG 24 - AWG 10  |
| Packaging    | Box  |

Creation date January 20, 2022 12:47:23 AM CET

## SVF 7.62HP/03/180G SN BK BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |          |
|------------|----------|
| Net weight | 15.369 g |
|------------|----------|

## System Parameters

| Product family                                  |   | Type of connection                            |                   |
|---|---|---|-------------------|
|   | OMNIMATE Power - series<br>BV/SV 7.62HP               |   | Field connection  |
| Wire connection method                          |   | Pitch in mm (P)                               |                   |
|   | PUSH IN without actuator,<br>Tension-clamp connection |   | 7.62 mm           |
| Pitch in inches (P)                             |   | Conductor outlet direction                    |                   |
|   | 0.3 inch  |   | 180°              |
| Number of poles                                 |   | L1 in mm                                      |                   |
|   | 3   |   | 15.24 mm          |
| L1 in inches                                    |   | Number of rows                                |                   |
|   | 0.6 inch  |   | 1                 |
| Pin series quantity                             |   | Rated cross-section                           |                   |
|   | 1   |   | 6 mm <sup>2</sup> |
| Touch-safe protection acc. to DIN VDE<br>57 106 |   | Touch-safe protection acc. to DIN VDE<br>0470 |                   |
|   | Safe from finger touch                                |   | IP20 plugged      |
| Volume resistance                               |   | Can be coded                                  |                   |
|   | 4.50 mΩ   |   | Yes               |
| Stripping length                                |   | Tightening torque for screw flange, min.      |                   |
|   | 12 mm   |   | 0.2 Nm            |
| Tightening torque for screw flange, max.        |   | Screwdriver blade                             |                   |
|   | 0.3 Nm  |   | 0.6 x 3.5         |
| Plugging cycles                                 |   |   |                   |
|   | 25  |   |                   |

## Material data

| Insulating material                   |                    | Colour                                |        |
|---------------------------------------|--------------------|---------------------------------------|--------|
|                                       | PA GF              |                                       | black  |
| Colour chart (similar)                |                    | Insulating material group             |        |
|                                       | RAL 9011           |                                       | II     |
| Comparative Tracking Index (CTI)      |                    | UL 94 flammability rating             |        |
|                                       | ≥ 500              |                                       | V-0    |
| Contact material                      |                    | Contact surface                       |        |
|                                       | Copper alloy       |                                       | tinned |
| Layer structure of plug contact       |                    | Storage temperature, min.             |        |
|                                       | 4...6 μm Sn glossy |                                       | -40 °C |
| Storage temperature, max.             |                    | Operating temperature, min.           |        |
|                                       | 70 °C              |                                       | -50 °C |
| Operating temperature, max.           |                    | Temperature range, installation, min. |        |
|                                       | 125 °C             |                                       | -25 °C |
| Temperature range, installation, max. |                    |                                       |        |
|                                       | 125 °C             |                                       |        |

## Conductors suitable for connection

|   |                     |
|---|---------------------|
| Clamping range, min.                            | 0.5 mm <sup>2</sup> |
| Clamping range, max.                            | 10 mm <sup>2</sup>  |
| Solid, min. H05(07) V-U                         | 0.5 mm <sup>2</sup> |
| Solid, max. H05(07) V-U                         | 6 mm <sup>2</sup>   |
| Stranded, max. H07V-R                           | 10 mm <sup>2</sup>  |
| Flexible, min. H05(07) V-K                      | 0.5 mm <sup>2</sup> |
| Flexible, max. H05(07) V-K                      | 10 mm <sup>2</sup>  |
| w. plastic collar ferrule, DIN 46228 pt 4, min. | 1.5 mm <sup>2</sup> |
| w. plastic collar ferrule, DIN 46228 pt 4, max. | 6 mm <sup>2</sup>   |
| w. wire end ferrule, DIN 46228 pt 1, min.       | 1.5 mm <sup>2</sup> |
| w. wire end ferrule, DIN 46228 pt 1, max.       | 6 mm <sup>2</sup>   |

**SVF 7.62HP/03/180G SN BK BX**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

|  |  |                              |                             |       |
|--|--|------------------------------|-----------------------------|-------|
| Clampable conductor                    | Cross-section for conductor connection | Type                         | fine-wired                  |       |
|  |  | nominal                      | 2.5 mm <sup>2</sup>         |       |
|  | wire end ferrule                       | Stripping length             | nominal                     | 12 mm |
|  |  | Recommended wire-end ferrule | <a href="#">H2.5/12</a>     |       |
|  |  | Stripping length             | nominal                     | 14 mm |
|  |  | Recommended wire-end ferrule | <a href="#">H2.5/19D BL</a> |       |
|  | Cross-section for conductor connection | Type                         | fine-wired                  |       |
|  |  | nominal                      | 4 mm <sup>2</sup>           |       |
|  | wire end ferrule                       | Stripping length             | nominal                     | 12 mm |
|  |  | Recommended wire-end ferrule | <a href="#">H4.0/12</a>     |       |
|  |  | Stripping length             | nominal                     | 14 mm |
|  |  | Recommended wire-end ferrule | <a href="#">H4.0/20D GR</a> |       |
|  | Cross-section for conductor connection | Type                         | fine-wired                  |       |
|  |  | nominal                      | 6 mm <sup>2</sup>           |       |
|  | wire end ferrule                       | Stripping length             | nominal                     | 12 mm |
|  |  | Recommended wire-end ferrule | <a href="#">H6.0/12</a>     |       |
| Stripping length                       |  | nominal                      | 14 mm                       |       |
| Recommended wire-end ferrule           |  | <a href="#">H6.0/20 SW</a>   |                             |       |
| Cross-section for conductor connection | Type                                   | fine-wired                   |                             |       |
|  | nominal                                | 1.5 mm <sup>2</sup>          |                             |       |
| wire end ferrule                       | Stripping length                       | nominal                      | 15 mm                       |       |
|  | Recommended wire-end ferrule           | <a href="#">H1.5/18D SW</a>  |                             |       |
|  | Stripping length                       | nominal                      | 12 mm                       |       |
|  | Recommended wire-end ferrule           | <a href="#">H1.5/12</a>      |                             |       |

Reference text The outside diameter of the plastic collar should not be larger than the pitch (P). Length of ferrules is to be chosen depending on the product and the rated voltage.

**Rated data acc. to IEC**

|   |                        |   |                   |
|---|------------------------|---|-------------------|
| tested acc. to standard   | IEC 60664-1, IEC 61984 | Rated current, min. number of poles (Tu=20°C)                         | 57 A              |
| Rated current, max. number of poles (Tu=20°C)                             | 50 A                   | Rated current, min. number of poles (Tu=40°C)                         | 57 A              |
| Rated current, max. number of poles (Tu=40°C)                             | 45 A                   | Rated voltage for surge voltage class / pollution degree II/2         | 1,000 V           |
| Rated voltage for surge voltage class / pollution degree III/2            | 800 V                  | Rated voltage for surge voltage class / pollution degree III/3        | 800 V             |
| Rated impulse voltage for surge voltage class/ pollution degree II/2      | 6 kV                   | Rated impulse voltage for surge voltage class/ pollution degree III/2 | 8 kV              |
| Rated impulse voltage for surge voltage class/ contamination degree III/3 | 8 kV                   | Short-time withstand current resistance                               | 3 x 1s with 420 A |
| Clearance, min.   | 12.7 mm                | Creepage distance, min.   | 12.7 mm           |


## SVF 7.62HP/03/180G SN BK BX

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany


www.weidmueller.com

## Technical data

### Rated data acc. to CSA

|                                   |  |   |        |                       |  |
|-----------------------------------|--|---|--------|-----------------------|--|
| Institute (CSA)                   |  |  |        | Certificate No. (CSA) |  |
|                                   |  |   |        | 200039-1121690        |  |
| Rated voltage (Use group B / CSA) | 600 V  | Rated voltage (Use group C / CSA)   | 600 V  |                       |  |
| Rated voltage (Use group D / CSA) | 600 V  | Rated current (Use group B / CSA)   | 36 A   |                       |  |
| Rated current (Use group C / CSA) | 36 A   | Rated current (Use group D / CSA)   | 5 A    |                       |  |
| Wire cross-section, AWG, min.     | AWG 24   | Wire cross-section, AWG, max.   | AWG 10 |                       |  |
| Reference to approval values      | Specifications are maximum values, details - see approval certificate. |   |        |                       |  |

### Rated data acc. to UL 1059

|                                       |  |   |        |                         |  |
|---------------------------------------|--|---|--------|-------------------------|--|
| Institute (cURus)                     |  |  |        | Certificate No. (cURus) |  |
|                                       |  |   |        | E60693                  |  |
| Rated voltage (Use group B / UL 1059) | 600 V  | Rated voltage (Use group C / UL 1059)   | 600 V  |                         |  |
| Rated voltage (Use group D / UL 1059) | 600 V  | Rated current (Use group B / UL 1059)   | 39 A   |                         |  |
| Rated current (Use group C / UL 1059) | 39 A   | Rated current (Use group D / UL 1059)   | 5 A    |                         |  |
| Wire cross-section, AWG, min.         | AWG 24   | Wire cross-section, AWG, max.   | AWG 10 |                         |  |
| Reference to approval values          | Specifications are maximum values, details - see approval certificate. |   |        |                         |  |

### Packing

|           |        |            |        |
|-----------|--------|------------|--------|
| Packaging | Box    | VPE length | 338 mm |
| VPE width | 130 mm | VPE height | 54 mm  |

### Type tests

|  |            |  |
|--|------------|--|
| Test: Durability of markings                 | Standard   | DIN EN 61984 section 7.3.2 / 09.02 taking pattern from DIN EN 60068-2-70 / 07.96 |
|  | Test       | mark of origin, type identification, pitch                                       |
|  | Evaluation | available  |
|  | Test       | durability   |
| Test: Misengagement (Non-interchangeability) | Evaluation | passed   |
|  | Standard   | DIN EN 61984 section 6.3 and 6.9.1 / 09.02, DIN EN 60512-13-5 / 11.08            |
|  | Test       | 180° turned with coding elements   |
|  | Evaluation | passed   |
| Test: Misengagement (Non-interchangeability) | Test       | 180° turned without coding elements  |
|  | Evaluation | passed   |

**SVF 7.62HP/03/180G SN BK BX**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

|   |                |  |                              |
|---|----------------|--|------------------------------|
| Test: Clampable cross section                             | Standard       | DIN EN 60999-1 section 7 and 9.1 / 12.00, DIN EN 60947-1 section 8.2.4.5.1 / 04.08 |                              |
|   | Conductor type | Type of conductor and conductor cross-section                                      | solid 0.5 mm <sup>2</sup>    |
|   |                | Type of conductor and conductor cross-section                                      | stranded 0.5 mm <sup>2</sup> |
|   |                | Type of conductor and conductor cross-section                                      | solid 6 mm <sup>2</sup>      |
|   |                | Type of conductor and conductor cross-section                                      | stranded 6 mm <sup>2</sup>   |
|   |                | Type of conductor and conductor cross-section                                      | AWG 24/1                     |
|   |                | Type of conductor and conductor cross-section                                      | AWG 24/19                    |
|   |                | Type of conductor and conductor cross-section                                      | AWG 14/1                     |
|   |                | Type of conductor and conductor cross-section                                      | AWG 14/19                    |
| Evaluation  | passed         |  |                              |
| Test for damage to and accidental loosening of conductors | Standard       | DIN EN 60999-1 section 9.4 / 12.00   |                              |
|   | Requirement    | 0.3 kg   |                              |
|   | Conductor type | Type of conductor and conductor cross-section                                      | H05V-U0.5                    |
|   |                | Type of conductor and conductor cross-section                                      | H05V-K0.5                    |
|   |                | Type of conductor and conductor cross-section                                      | AWG 20/1                     |
|   |                | Type of conductor and conductor cross-section                                      | AWG 20/19                    |
|   | Evaluation     | passed   |                              |
|   | Requirement    | 1.4 kg   |                              |
|   | Conductor type | Type of conductor and conductor cross-section                                      | H07V-U6                      |
|   |                | Type of conductor and conductor cross-section                                      | H07V-K6                      |
|   |                | Type of conductor and conductor cross-section                                      | AWG 10/1                     |
|   |                | Type of conductor and conductor cross-section                                      | AWG 10/19                    |
|   | Evaluation     | passed   |                              |

## SVF 7.62HP/03/180G SN BK BX

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

|   |                |   |           |  |
|---|----------------|---|-----------|--|
| Pull-out test                                 | Standard       | DIN EN 60999-1 section 9.5 / 12.00            |           |  |
|   | Requirement    | ≥20 N   |           |  |
|   | Conductor type | Type of conductor and conductor cross-section | H05V-U0.5 |  |
|   |                | Type of conductor and conductor cross-section | H05V-K0.5 |  |
|   |                | Type of conductor and conductor cross-section | AWG 20/1  |  |
|   |                | Type of conductor and conductor cross-section | AWG 20/19 |  |
|   | Evaluation     | passed  |           |  |
|   | Requirement    | ≥80 N   |           |  |
|   | Conductor type | Type of conductor and conductor cross-section | H07V-U6   |  |
|   |                | Type of conductor and conductor cross-section | H07V-K6   |  |
| Type of conductor and conductor cross-section |                | AWG 10/1                                      |           |  |
| Type of conductor and conductor cross-section |                | AWG 10/19                                     |           |  |
| Evaluation                                    | passed         |   |           |  |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002638    | ETIM 7.0    | EC002638    |
| ETIM 8.0    | EC002638    | ECLASS 9.0  | 27-44-03-09 |
| ECLASS 9.1  | 27-44-03-09 | ECLASS 10.0 | 27-44-03-09 |
| ECLASS 11.0 | 27-46-02-02 |             |             |

### Important note

IPC conformity      Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.

- Notes
- Additional colours on request
  - Rated current related to rated cross-section & min. No. of poles.
  - Wire end ferrule without plastic collar to DIN 46228/1
  - Wire end ferrule with plastic collar to DIN 46228/4
  - P on drawing = pitch
  - Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.

## SVF 7.62HP/03/180G SN BK BX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



|                       |         |
|-----------------------|---------|
| ROHS                  | Conform |
| UL File Number Search | E60693  |

### Downloads

|   |  |
|---|--|
| Approval/Certificate/Document of Conformity | <a href="#">Declaration of the Manufacturer</a>  |
| Engineering Data                            | <a href="#">CAD data – STEP</a>  |
| Engineering Data                            | <a href="#">EPLAN, WSCAD</a>   |
| User Documentation                          | <a href="#">QR-Code product handling video</a>   |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>   |
| Brochures                                   | <a href="#">FL DRIVES EN</a><br><a href="#">MB DEVICE MANUF. EN</a><br><a href="#">FL DRIVES DE</a><br><a href="#">FL HEATING ELECTR EN</a><br><a href="#">FL APPL INVERTER EN</a><br><a href="#">FL_BASE_STATION_EN</a><br><a href="#">FL ELEVATOR EN</a><br><a href="#">FL POWER SUPPLY EN</a><br><a href="#">FL 72H SAMPLE SER EN</a><br><a href="#">PO OMNIMATE EN</a><br><a href="#">PO OMNIMATE EN</a> |


**SVF 7.62HP/03/180G SN BK BX**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com


**Drawings**

**Dimensional drawing**




Similar to illustration

**Graph**



**Graph**






**SVF 7.62HP/03/180G SN BK BX**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Accessories**

**Slotted screwdriver**



Slotted screwdriver with rounded blade SD DIN 5265, ISO 2380/2, output to DIN 5264, ISO 2380/1. ChromTop tip, SoftFinish grip

**General ordering data**

|            |                            |                          |
|------------|----------------------------|--------------------------|
| Type       | SDS 0.8X4.5X125            | Version                  |
| Order No.  | <a href="#">9009020000</a> | Screwdriver, Screwdriver |
| GTIN (EAN) | 4032248266883              |                          |
| Qty.       | 1 pc(s).                   |                          |

**Crimping tools**



**Crimping tools for wire end ferrules, with and without plastic collars**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

**General ordering data**

|            |                            |  |
|------------|----------------------------|--|
| Type       | PZ 6/5                     | Version  |
| Order No.  | <a href="#">9011460000</a> | Pressing tool, Crimping tool for wire-end ferrules, 0.25mm <sup>2</sup> , 6mm <sup>2</sup> , |
| GTIN (EAN) | 4008190165352              | Trapezoidal indentation crimp  |
| Qty.       | 1 pc(s).                   |  |

**SVF 7.62HP/03/180G SN BK BX**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Accessories**

**Coding elements**



**The pluggable connections for power electronics - optimised for modern drive technologies, e.g. motor starters, frequency converters and servo-controllers.**

OMNIMATE Power sets the new standard – with increased safety and innovative solutions such as the pluggable shield, integrated signal contacts and one-handed operation.

The three product lines offer you further advantages:

- Application-oriented scalability: from the compact 4 mm<sup>2</sup> connector for 29 A (IEC) or 20 A (UL) up to the sturdy 16 mm<sup>2</sup> connector for 76 A (IEC) or 54 A (UL)
- Unlimited usage up to 1,000 V (IEC) or 600 V (UL)
- A variety of application optimised mounting options

Our Service:

Design your individual connectors simply by using the

**General ordering data**

| Type       | BV/SV 7.62HP KO            | Version   | Product data | Packaging |
|------------|----------------------------|---|--------------|-----------|
| Order No.  | <a href="#">1937590000</a> | PCB plug-in connector, Accessories, Coding element, black, Number |              | Box       |
| GTIN (EAN) | 4032248608881              | of poles: 1   |              |           |
| Qty.       | 50 pc(s).                  |   |              |           |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1060840000](#)