

## KLIPPON STB 1 SS E

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

### Similar to illustration



Abbildung ähnlich

Ideally suited for the energy, process and transportation industries, the Klippon® STB enclosure series is the perfect complement to our existing Klippon® enclosure portfolio. Enclosures in this series are approved according to international standards such as e.g. EN62208 and EN60079-0/7 (ATEX).

- Mirror-polished or electropolished stainless steel 1.4404 (316L), 1.5 mm
- High-temperature-resistant seal as standard - extended temperature range of -60°C to +100°C for Ex application (+120°C only for industrial application)
- Approved according to ATEX, IECEx, cULus, Lloyds Register, Germanischer Lloyd, GL DNV and INMETRO
- Flexible options for fastening the internal mounting rail
- IP66 protection
- Secure, permanent function of the seal is ensured by seal compression protection
- Earthing stud in the cover and base of the enclosure
- Laser cut weld seams for increased quality
- Already welded-on mounting feet guarantee optimum enclosure installation

Weidmüller can manufacture and supply this enclosure - according to customer specifications - fitted with all necessary terminals and cable glands.



### General ordering data

Version	Klippon STB (Small Terminal Box), Empty enclosure, stainless steel enclosure, Height: 120 mm, Width: 120 mm, Depth: 80 mm, Material: Stainless steel 1.4404 (316L), electropolished, silver
Order No.	<a href="#">1058810000</a>
Type	KLIPPON STB 1 SS E
GTIN (EAN)	4032248800681
Qty.	1 pc(s).

## KLIPPON STB 1 SS E

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

Depth	80 mm	Depth (inches)	3.15 inch
Height	120 mm	Height (inches)	4.724 inch
Width	120 mm	Width (inches)	4.724 inch
Mounting dimension - width	145 mm	Weight	1.34 g
Net weight	1,220 g		

### Temperatures

Operating temperature	-60 °C...100 °C
-----------------------	-----------------

### Cable glands, left

M12	10	M16	6
M20	6	M25	3
M32	2	M40	2

### Cable glands, right

M12	8	M16	4
M20	4	M25	2
M32	1	M40	1

### Cable glands, top/bottom

M12	10	M16	6
M20	6	M25	3
M32	2	M40	2

### Certificate numbers enclosure

Approval conditions	ATEX, DNV, EAC, IECEX, INMETRO, LR, RMRS, UL AEx Class Div., UL AEx Class Zone, cULus, KC, CCC	Attestation of Conformatiy No. (AoC)	DE PS2620 160308 001ISS02
Certificate No. (ATEX)	IBEXU07ATEX1147U	Certificate No. (EAC)	C-DE.HB07.B.00089-20
Certificate No. (IECEX)	IECEXIBE09.0019	Certificate No. (LLOYDSREG)	08_20032
Certificate no. (INMETRO)	IEX13.0003	Certificate no. (cULus)	E197061
Certificate no. Terminal Box (AEx)	E223792	Certificate no. Terminal Box (ATEX)	IBEXU07ATEX1148
Certificate no. Terminal Box (EAC)	C-DE.HB07.B.00089/20 Ex Terminal Box; C-DE.AJ54.B.00251/19 Ind. Terminal Box	Certificate no. Terminal Box (IECEX)	IECEX IBE 09.0019
Certificate no. Terminal Box (INMETRO)	LMP 21.0018	Certificate no. Terminal Box (KOSHA)	16-AV4BO-0247X
Certificate no. empty enclosure (ATEX)	IBEXU 07ATEX1147U	Certificate no. empty enclosure (IECEX)	IECEX IBE 09.0018U
Certificate no. empty enclosure (INMETRO)	IEx 13.0002U	Certificate no., empty enclosure (EAC)	C-DE.HB07.B.00089/20
Declaration of Conformatiy No. (DoC LVD)	DE PS2620 160412 001ISS01		

## KLIPPON STB 1 SS E

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

### General information

Access opening: height	100 mm	Access opening: width	102 mm
Areas of use	Explosive risk zone, Packaging industry, Transportation, Process industry, Marine engineering	Enclosure attachment	Welded-on mounting foot with 8-mm holes
Flange plate	No	Halogen	No
Impact resistance	10 J version standard, 7 J ATEX version	Integral fixing	TAS 20 rail welded to floor
Lid	Yes	Lid attachment	M5 hexagonal screw with slot and 10mm distance across flats
Material	Stainless steel 1.4404 (316L)	Material thickness of cover	1.5 mm
Material thickness of enclosure	1.5 mm	Number of lid screws	4
Operating temperature, max.	100 °C	Operating temperature, min.	-60 °C
Protection class (UL)	Type 4, Type 4x	Protection degree	IP66
Seal material	Silicone	Surface finish	electropolished
Torque for lid screws	2.5 Nm		

### Housing earth

Cross-section , max.	25 mm <sup>2</sup>	Earth, enclosure, cover	Welded-on M6 x 10 stainless-steel earth stud
Earth, enclosure, external	Welded-on M6 x 16 stainless-steel bolts	Earth, enclosure, internal	Welded-on M6 x 16 stainless-steel bolts

### vertical assembly

WDU 10 / ZDU 10	1x8	WDU 16 / ZDU 16	1x7
WDU 2,5 / ZDU 2,5 / IDU 2,5	1x17	WDU 4 / ZDU 4	1x14
WDU 6 / ZDU 6	1x11		

### Classifications

ETIM 6.0	EC002503	ETIM 7.0	EC002503
ETIM 8.0	EC002503	ECLASS 9.0	27-18-05-02
ECLASS 9.1	27-18-05-02	ECLASS 10.0	27-18-05-02
ECLASS 11.0	27-18-05-02		

### Important note

Product information	The ambient temperature for the assembly will be reduced to +60°C and the surface temperature to +100°C.
---------------------	--

## KLIPPON STB 1 SS E

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS	Conform
UL File Number Search	E197061

## Downloads

Approval/Certificate/Document of Conformity	<a href="#">C-DE.HB07.B.00089-Empty Enclosures and Ex. Terminal Box</a> <a href="#">C-DE.AJ54.B.00251.19 Ind. Terminal Box</a> <a href="#">CCC 2020322303002356 STB Assembly Enclosure</a> <a href="#">Attestation of Conformity - Klippon STB Empty Enclosures - AoC DE PS2620 160308 001ISS04 RUC-DE.BE02.B.00173</a> <a href="#">08_20032</a> <a href="#">IBEXU07ATEX1148</a> <a href="#">IECEXIBE09.0018U</a> <a href="#">IECEXIBE09.0019</a> <a href="#">IEX13.0002U</a> <a href="#">IEX13.0003</a> <a href="#">15.40041.250</a> <a href="#">16-AV4BO-247X</a> <a href="#">59358-08</a> <a href="#">IBEXU07ATEX1147U</a> <a href="#">INMETRO Certificado LMP 21.0018 KLIPPON STB</a> <a href="#">EU Declaration of Conformity - Klippon STB Empty Enclosures Ex - DoC DE PS2620 160412 001ISS01</a>
Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">EPLAN, WSCAD</a>
Tender specification	<a href="#">Klippon STB 1 SS E_1058810000_DE</a> <a href="#">Klippon STB 1 SS E_1058810000_EN</a>
User Documentation	<a href="#">Assembly guidelines - empty enclosures</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">MB OVERV. PROCESS WD DE</a> <a href="#">MB KLIPPON ENCL.TECN EN</a> <a href="#">MB PROCESS EN</a> <a href="#">FL KLIPPON STB EN</a> <a href="#">FL SHIPBUILDING 2016 EN</a> <a href="#">FL SHIPBUILDING 2016 EN</a>


**KLIPPON STB 1 SS E**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)

**Dimensioned drawing**



## KLIPPON STB 1 SS E

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

## Ventilation plugs - DAE



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

## General ordering data

Type	DAE M12 SS	Version
Order No.	<a href="#">1868550000</a>	DAE (ventilation element), Compensating element, M 12, 10 mm,
GTIN (EAN)	4032248440405	IP66, IP68, IP69K, Stainless steel 1.4305 (303)
Qty.	10 pc(s).	
Type	DAE M12 PA LONG	Version
Order No.	<a href="#">1868570000</a>	DAE (ventilation element), Compensating element, M 12, 10 mm,
GTIN (EAN)	4032248440429	IP66, IP68, IP69K, Polyamide 6
Qty.	10 pc(s).	

## Installation material

**Integrate, expand and customise - the perfect supplement to every application**

The fully structured range of system accessories for the new Klippon® TB enclosure series allows you to easily adapt the enclosures to meet the specific requirements of every application.

**Mounting hardware kits**

Mounting hardware kits are available for quick and easy installation of type label holders, document holders and rain hoods.

The **label fastening set – SD** is required to install a plastic (Trafolyte) ID or type label. With the aid of this set can you mount the ID or type label directly on the enclosure cover. The label fastening set has been specially developed for this purpose. Only by using this fastening set can you ensure that there will be no leaks into the enclosure or damage to the label.

The **universal fastening set – TPSD** has been developed to enable secure and quick installation of type label holders, rain covers or document holders, for example. By using this fastening set, the risk of leaks can be minimised, if not avoided.

## General ordering data

Type	SD FIXING SET	Version
Order No.	<a href="#">1285200000</a>	Klippon TB (Terminal Box), Identification plate fixing set, Material:
GTIN (EAN)	4050118075472	Stainless steel, rust-proof, untreated, silver
Qty.	1 pc(s).	

## KLIPPON STB 1 SS E

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

Type	TPSD FIXING SET KTB	Version
Order No.	<a href="#">1252190000</a>	Klippon TB (Terminal Box), Type plate fixings set, Material: Stainless
GTIN (EAN)	4050118043969	steel, rust-proof, untreated, silver
Qty.	1 pc(s).	

## Grounding strap

The fully structured range of system accessories for the new Klippon® TB enclosure series allows you to easily adapt the enclosures to meet the specific requirements of every application. The following options are available:

- Closure Elements
- Document holders
- Earthing stud
- Gland plates
- Installation material
- Mounting plates
- Rain hoods
- Spacer
- Terminal rails
- Type label holder

## General ordering data

Type	PECD WIRE 6/200/D6 SET	Version
Order No.	<a href="#">2475490000</a>	Klippon TB (Terminal Box), Grounding strap, Sscrewed, Material: Steel,
GTIN (EAN)	4050118487206	Green/yellow
Qty.	1 pc(s).	

## Terminal rails - TS35



The system accessories for the Klippon® STB enclosure series allows you to easily adapt the enclosures to meet the specific requirements of every application.

- DIN Rails TS 35
- Mounting screws

Weidmüller can manufacture and supply this enclosure - according to customer specifications - fitted with all necessary terminals and cable glands.

## General ordering data

Type	SFNS5 VKMU M5 SW15	Version
Order No.	<a href="#">0433500000</a>	Klippon STB (Small Terminal Box), Fixing nut, Material: Steel,
GTIN (EAN)	4008190494520	galvanised, silver
Qty.	20 pc(s).	
Type	TS35X15 ST STB 1	Version
Order No.	<a href="#">8000073217</a>	Rail, TS 35, TS 35 x 15, Width: 80 mm, Steel, galvanic zinc plated and
GTIN (EAN)	4064675356745	passivated
Qty.	20 pc(s).	

**Data sheet****KLIPPON STB 1 SS E**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Accessories**

Type	TS35X7.5 ST STB 1	Version
Order No.	<a href="#">8410510000</a>	Rail, TS 35, TS 35 x 7.5, Width: 80 mm, without slot, Steel, galvanic
GTIN (EAN)	4050118652758	zinc plated and passivated
Qty.	20 pc(s).	



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1058810000](#)